$\sim R \rightarrow S \rightarrow$						
to the second se	4					
Keying Shown as example CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III Connector dimension Dim Nominal						
-Shell Material : Aluminium A 49.2±0.3 -Shell Plating : Olive drab Cadmium B 33.32+0.1/-0.15 -Shell Plating : Olive drab Cadmium R 32.5Max -Insulator : Thermoplastic S 46±0.4 -Contact S : Copper Alloy W 3+0.9/-0.1 -Seals & Grommet : Silicon Elastomer : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8µm minimum W	2					
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories PN: 8D719W35BA -Temperature Range : -65°C to +175°C -Salt Spray : 500 hours						
-Mass : 44.09 g ± 10% ISS DATE Latest modification - by MOD N Designed By: Date: CUSTOMER DRAWING ISS Aluminium Receptacle 8D series ISS						
BASIC SERIES: 8D 7 - 19 W 35 B A SCALE SCALE Tolerances: B59 SHELL TYPE : Standard Crimp Contact .	1					
SHELL SIZE : 19 CONTACT TYPE : SOCKET(500 Matings) communicated without permission PLATING : W = Olive drab Cadmium CONTACT LAYOUT : 19-35 FORMAT SOURIAU DRG N° SHEET H G F E D C B A	_					

ſ	Т	۵	г	п		0	ω	A	_	
4	Contact Layout				_		4			
	2357 (9.07) + 3357 (9.07) + 4279 (7.09) + 5279 (7.09) + 6279 (7.09) + 7279 (7.09) - 8279 (7.09) - 9279 (7.09) - 10201 (5.11) +	Contacts (Insert arrangement 19-35) Interpret to the second				ØC	V			
ω	12 201 (5.11) + 13 201 (5.11) + 14 201 (5.11) + 15 201 (5.11) + 16 201 (5.11) + 17 123 (3.12) +	.090 (2.29) 45 +.123 (3.12) +.135 (3.43) .000 (0.00) 46 +.123 (3.12) +.045 (1.14) .090 (2.29) 47 +.123 (3.12) 045 (1.14) .180 (4.57) 48 +.123 (3.12) 136 (3.43) .270 (6.86) 49 +.123 (3.12) 255 (5.72) .315 (8.00) 50 +.123 (3.12) 315 (8.00) Contacts (Insert arrangement 19-35)				Dim Nominal B 33.91+0/-0 ØC 35.18+0.25	.25		3	
	Contact position X-axis (mm) 10 (mm) 18 123 (3.12) 19 123 (3.12) 20 .123 (3.12) 21 123 (3.12) 22 .123 (3.12) 23 .123 (3.12) 24 .123 (3.12) 25 .045 (1.14) 26 .045 (1.14) 27 .045 (1.14) 28 .045 (1.14) 29 .045 (1.14) 30 .045 (1.14) 31 .045 (1.14)	Y-axis (mm) Contact position ID X-axis (mm) Y-axis (mm) Y-axis (mm) +225 (5.72) 51 +201 (5.11) +270 (6.86) +135 (3.43) 52 +201 (5.11) +180 (4.57) -045 (1.14) 53 +201 (5.11) +000 (0.20) -135 (3.43) 55 +201 (5.11) +000 (0.20) -235 (5.72) 56 +201 (5.11) +000 (0.20) -045 (1.14) 54 +201 (5.11) +000 (0.20) -135 (3.43) 55 +201 (5.11) -000 (0.20) -245 (5.72) 56 +201 (5.11) -000 (0.20) -316 (8.00) 67 +201 (5.11) -000 (0.20) -225 (5.72) 56 +201 (5.11) -100 (4.57) -316 (8.00) 67 +201 (5.11) -200 (6.86) +300 (9.14) 58 +279 (7.09) +135 (3.43) +270 (6.86) 59 +279 (7.09) -045 (1.14) +000 (0.00) 62 +279 (7.09) -135 (3.43) -090 (2.29) 63 +279 (7.09) -135 (3.4				due to a use of the Pro the Specifications issued by	ole for any non-conformity or o oducts which does not comply y either of the Parties or by a th mmendation, technical notice.	with hird party		
2	Shell Arrangement Nu size no. C	Size Service Contact Superse ontacts contacts rating location 66 22D M All MS27530			Country Jurisdiction & Control List 2					
		PN: 8D719W35BA A 30-09-2016 First Release								
					ISS DATE	ISS DATE Latest modification - by MOD N°				
					Designed By:	Date:		STOMER DRAWING	_	
					SCALE					
_					NA		annean p ances: ±	NPRDS / PROJECT 859	1	
					SOURIAL	WWW.SOURIAU.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission				
					FORMAT A3		RIAU DRG N° 19W35BA-C	SHEET 2/2		
L	Н	G	F	E	D	C	190055DA-C B	A		
					/					