

9038CG36N4N5

Mechanical alternator, Square D Pumptrol,
mech closed tank, NEMA 1, screw in bushing,
4 NC DPST DB contacts



Main

Range of Product	Square D Pumptrol
Product or Component Type	Mechanical alternator
Device Application	Closed tank with bushing
Device short name	9038C
Product Specific Application	Mechanically alternating the operation of two pumps or motors
Electrical circuit type	Power circuit with control duty alarm
Quantity per Set	Set of 1
Type of Packing	Individual

Complementary

Product destination	For closed tank
Device mounting	Screw-in bushing
Cable entry number	8 knock-outs for 1/2" or 3/4" conduit UL 508
Contacts type and composition	4 NC, snap action, DPST-DB, Form YY
Controlled fluid	Fresh water specific gravity of 0.85 in or higher 0...220 °F (-18...104 °C) Sea water specific gravity of 0.85 in or higher 0...220 °F (-18...104 °C) Hydraulic oil specific gravity of 0.85 in or higher 0...220 °F (-18...104 °C) Corrosive fluid specific gravity of 0.85 in or higher 0...220 °F (-18...104 °C)
Motor power kW	1.5 KW 2 hp)115 V AC, 1 phase 2.2 KW 3 hp)115 V AC, 3 phase 2.2 KW 3 hp)230 V AC, 1 phase 3.7 KW 5 hp)230 V AC, 3 phase 0.75 KW 1 hp)460 V AC, 3 phase 0.75 KW 1 hp)475 V AC, 3 phase 0.18 KW 0.25 hp)32 V DC 0.37 KW 0.5 hp)115 V DC 0.37 kW 0.5 hp)230 V DC
Electrical connection	Screw-clamp terminals 10 AWG
Contact operation	Contacts close on liquid rise
Float movement	4.75...9.25 in adjustable
Float position	Left
Float rod angle	90° (offset)
Short-circuit protection	20 A cartridge fuse gG
Local signalling	With external pointer
Materials in contact with fluid	Stainless steel 304 Yellow brass Stainless steel 316 Nitrile (Buna-N) or equivalent rubber Cast iron
Enclosure Material	Painted cold-rolled steel
Operating position	Vertical position only
Electrical durability	100 cycles 60 cyc/mn
Mechanical durability	300 cycles
Terminal block type	8 terminals
Maximum operating rate	60 cyc/mn
[Ui] rated insulation voltage	575 V UL 508
Net Weight	7 lb(US) (3.18 kg)
Terminals description ISO n°1	Line-load-load-line

Factory modification	Two-level non-alternating unit, high level alarm
Kit composition	Float Float switch Rod

Environment

Standards	UL 508 CE
Ambient Air Temperature for Operation	-22...220 °F (-30...104 °C)
Ambient Air Temperature for Storage	-22...220 °F (-30...104 °C)
NEMA degree of protection	NEMA 1 UL 50
Product Certifications	CSA file LR25490 UL listed file E12158


Ordering and shipping details

Category	21601-9037,9038 COMMERCIAL FLOAT SWITCHES
Discount Schedule	CP7G
GTIN	785901284338
Nbr. of units in pkg.	1
Package weight(Lbs)	7.00 lb(US) (3.175 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.76 in (29.871 cm)
Package 1 width	4.63 in (11.76 cm)
Package 1 Length	29.87 in (75.872 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------