

T	G	т	m	D	0







Keying Shown as example

CHARACTERISTICS

ω

 \sim

-Mass

BASIC SERIES:

SHELL SIZE : 13

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : W = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material	: Aluminium					
-Shell Plating	: Olive drab Cadmium					
-Insulator	: Thermoplastic					
-Contacts	: Copper Alloy					
-Seals & Grommet	: Silicon Elastomer					
-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum					
-Durability	: 500 Mating cycles					
-Delivered with Souriau contacts and Accessories						
-Temperature Range	- 65°C to +175°C					
-Salt Spray	: 500 hours					

: 16.46 g ± 10%

8D 0

G

13

-

W

26

А

F

D

Connector dimension				
Dim	Nominal			
Р	3.25±0.2			
PP	4.93±0.2			
R1	23.01			
R2	20.62			
S	28.6±0.3			
V	20.83+0/-1.25			
W	2.1/2.5			
Z	31.5 Max			
VV THREAD	M18x1-6g			

1								
т	C	2		0		Φ		
								4
				LAY	OUT SHOWN A	S EXAMPLE		3
nector dimension Nominal 3.25±0.2 4.93±0.2 23.01 20.62 28.6±0.3 20.83+0/-1.25				due to a use the Specifications	of the Products issued by eithe	any non-conformit which does not cor r of the Parties or b dation, technical no	mply with by a third party	
2.1/2.5 31.5 Max			Country Jurisdiction & Control List FR Not Listed					2
AD M18x1-6g		PN: 8D013W26AD						
		A 16	6-10-2016	First Release				
	-	ISS Designed E	DATE By:	Latest modificatio Date:	n - by		CUSTOMER DRAWING	MOD N°
	TI	TITLE Aluminium Receptacle 8D series						
		SCALE	-{	$\exists \bigoplus$	General linea Tolerances: ±	r	NPRDS / PROJECT 859	
ORIENTATION : D CONTACT TYPE : PIN(500 Matings)		SOU	DURIAU This document is the proper SOURIAU WWW.SOURIAU.COM it must not be reproduced communicated without permittion		uced or			
CONTACT LAYOUT : 13-26		FORMAT	SOURIAU DRG N		SHEET 1/2			
E	.)		С		B	A	
V								

-	Ŧ	۵	п –	m		0
		Contact Layout				Panel Cutou
4		26			۲ ۲	SQUARE FLANGE RECEPTACLE (TYPE 0) REAR MOUNTING
		6#22D	1		v	
cσ	Ctc A B C D E F 1 2	13-26 X Y 0 3.47 2.47 4.34 2.47 -4.34 0 -3.47 -2.47 -4.34 -2.47 4.34 3.25 0 -3.25 0				Dim ØA ØA R1 ØT
	-					SOURIAU shall not be liable for any
						due to a use of the Products wh the Specifications issued by either of (professional recommendat
N					[Countr FR
					A 16-10-20	PN: 8D013V
_					ISS DATE	Latest modification - by
					Designed By:	Date: Aluminium
<u> </u>					SCALE NA	General linear Tolerances:
					SOURIA	U WWW.SOURIAU.C
				_	FORMAT A3	SOURIAU 8D013W
	Н	G	F	E	D	C

