	Ŧ	G	П	m		D	0	D.	A		_
4	R 22.6 Max	N Thread						OWN AS EXAMPLE			4
	CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Se	eries III	Keying Shown as	Connector dimension Dim Nominal]						
2	-Shell Material: Aluminium-Shell Plating: Black Zinc Nic-Insulator: Thermoplasti-Contacts: Copper Alloy-Seals & Grommet: Silicon Elastor	c mer		A 34.9±0.3 B 19.07+0.1/-0.15 R 32.5Max S 31.8±0.4 W 2.2+0.9/-0.1 VV THREAD M15x1-6g			due to a use of the Pr the Specifications issued b		oly with a third party ce.) ion & Control List		0
	-Durability : 500 Mating contacts		m				PN: 80	FR 0711Z22SNL	Not Listed		2
	-Temperature Range <u>:</u> -65°C to +17 -Salt Spray : 500 hours -Mass : 19.08 g ± 10%					A 01-10-20 ISS DATE Designed By:	16 First Release Latest modification - by Date:		CUSTOMER DRAWING	MOD N°	
	BASIC SERIES: 8	3D 7 - 11	Z 22 S N L			SCALE	Gene	minium Receptacle	8D series NPRDS / PROJECT 859		
<u> </u>	SHELL TYPE : Jam nut Receptacle CONTACT TYPE : Standard Crimp Con SHELL SIZE : 11	itact		Delivered W, ORIEN CONTACT TYPE : SOCKET(50	ITATION : N	SOURIA		± RIAU.COM	This document is the prop SOURIAU it must not be reproduc communicated without pe	ced or	1
	PLATING : Z = Black Zinc Nickel	G	F			FORMAT A3		IRIAU DRG N° 711Z22SNL-C B	A	SHEET 1/2	

ſ	۵ ت	ш (г		_
4	Contact Layout 22* b o b o b o b c o b d f f f f f f f f f f f f f f f f f f		Panel cutout JAM NUT RECEPTACLE (TYPE 7)	4
ω	11-22 Ctc X Y A 1.905 1.905 B 1.905 -1.905 C -1.905 -1.905 D -1.905 1.905		Dim Nominal B 19.59+0/-0.25 ØC 20.96+0.25/-0	3
2			SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) $\frac{Country \qquad Jurisdiction \& Control List \\ \hline FR \qquad Not Listed}$ PN: 8D711Z22SNL	2
			A 01-10-2016 First Release ISS DATE Latest modification - by MOD N° Designed By: Date: Date: CUSTOMER DRAWING	
_			TITLE Aluminium Receptacle 8D series SCALE General linear NA Tolerances: ± 859 This document is the property of SOURIAU	1
	H G	FE	SOURIAUWWW.SOURIAU.COMSouriau it must not be reproduced or communicated without permissionFORMATSOURIAU DRG N° A3SHEET 2/2DCBA	