

APDA1806CGCK

1.8 x 0.6 mm Right Angle SMD Chip LED Lamp



DESCRIPTIONS

- The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- Electrostatic discharge and power surge could damage the LEDs
- . It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- All devices, equipments and machineries must be electrically grounded

FEATURES

- 1.8 x 1.5 x 0.6 mm right angle SMD LED, 0.6 mm thickness
- Low power consumption
- · Ideal for backlight and indicator
- Package: 4000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- · Tinned pads for improved solderability
- RoHS compliant


APPLICATIONS


- Backlight
- Status indicator
- Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications


ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices










RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



Notes

All dimensions are in millimeters (inches).
 Tolerance is ±0.15(0.006") unless otherwise noted

3. The specifications, characteristics and technical data described in the datasheet are subject to

The specifications, characteristics and recrimical data described in the datasheet are subject to change without prior notice.
 The device has a single mounting surface. The device must be mounted according to the specifications.
 For right angle SMD LEDs, the solder stencil should be at least 5mil in thickness, to prevent poor solder wetting due to insufficient solder paste.

SELECTION GUIDE

| Part Number | Emitting Color (Material) | Lens Type | lv (mcd) @ 20mA ^[2] | | Viewing Angle ^[1] | |
|--------------|------------------------------|-------------|--------------------------------|------|------------------------------|--|
| | | | Min. | Тур. | 201/2 | |
| APDA1806CGCK | Green (AlGaInP) | Water Clear | 120 | 400 | 25° | |

Notes

1, 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 Luminous intensity / luminous flux: +/-15%.
 Luminous intensity value is traceable to CIE127-2007 standards.

Kingbright

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

| Parameter | Current of | Ensitétie et Ostan | Value | | Unit |
|---|---------------------------------------|--------------------|-----------|-----|-------|
| Parameter | Symbol | Emitting Color | Typ. Max. | | |
| Wavelength at Peak Emission I_F = 20mA | λ_{peak} | Green | 574 | - | nm |
| Dominant Wavelength I _F = 20mA | λ_{dom} ^[1] | Green | 570 | - | nm |
| Spectral Bandwidth at 50% Φ REL MAX I _F = 20mA | Δλ | Green | 20 | - | nm |
| Capacitance | С | Green | 15 | - | pF |
| Forward Voltage I _F = 20mA | V _F ^[2] | Green | 2.1 | 2.5 | V |
| Reverse Current (V _R = 5V) | I _R | Green | - | 10 | μΑ |
| Temperature Coefficient of λ_{peak} I _F = 20mA, -10°C ≤ T ≤ 85°C | TC _{λpeak} | Green | 0.12 | - | nm/°C |
| Temperature Coefficient of λ_{dom} I _F = 20mA, -10°C ≤ T ≤ 85°C | $TC_{\lambda dom}$ | Green | 0.08 | - | nm/°C |
| Temperature Coefficient of V _F $I_F = 20mA, -10^{\circ}C \le T \le 85^{\circ}C$ | TCv | Green | -1.9 | - | mV/°C |

Notes: 1. The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.) 2. Forward voltage: ±0.1V. 3. Wavelength value is traceable to CIE127-2007 standards. 4. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

ABSOLUTE MAXIMUM RATINGS at T_A=25°C


| Parameter | Symbol | Value | Unit |
|--|-----------------------------------|------------|------|
| Power Dissipation | P _D | 75 | mW |
| Reverse Voltage | V _R | 5 | V |
| Junction Temperature | Tj | 115 | °C |
| Operating Temperature | T _{op} | -40 to +85 | °C |
| Storage Temperature | T _{stg} | -40 to +85 | °C |
| DC Forward Current | I _F | 30 | mA |
| Peak Forward Current | I _{FM} ^[1] | 150 | mA |
| Electrostatic Discharge Threshold (HBM) | - | 3000 | V |
| Thermal Resistance (Junction / Ambient) | R _{th JA} ^[2] | 700 | °C/W |
| Thermal Resistance (Junction / Solder point) | R _{th JS} ^[2] | 560 | °C/W |

Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. R_{m,A}, R_m, R_{m,S} Results from mounting on PC board FR4 (pad size≥ 16 mm² per pad). 3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.


Kingbright

APDA1806CGCK


TECHNICAL DATA




SPATIAL DISTRIBUTION




GREEN



Luminous Intensity vs. Ambient Temperature




REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS






- Don't cause stress to the LEDs while it is exposed to high temperature.
 The maximum number of reflow soldering passes is 2 times.
 Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

TAPE SPECIFICATIONS (units : mm)



REEL DIMENSION (units : mm)




Kingbright

APDA1806CGCK

PACKING & LABEL SPECIFICATIONS

CEABILITY: XXXXXXXXXXXXXXXX

(SP) XXXXXXXXXXX



PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. 2.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening 3.
- 4. Itabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 5. 6. iahtUSA.
- All design applications should refer to Kingbright application notes available at https://www.Ki Notes