

## **REVISION C** NOTES: -2.196 [55.78] REI 1. STANDARD PART SET UP AS ASP. LIKE PART: SEAM-40-02.0-STL-14-1-A-K-TR 1.9500 49.530 REPRESENTS A CRITICAL DIMENSION. DO NOT 3. MINIMUM PUSHOUT FORCE: 0.50 LBS. ((40 POS - 1) X .050[1.27]) SCALE FROM THIS PRINT 4. MEASURED FIRST & LAST POSITIONS ONLY, ALL ROWS. .123[3.12] REF 5. DIMENSION MUST BE MEASURED IN THE FOUR OUTSIDE CORNERS USING INSPECTION FIXTURE AT-1817-836-2, USE CO-AU-WI-2003-M FOR PROCESS. .778 19.76 6. PARTS TO BE PACKAGED IN TAPE & REEL. -.0500 [1.270] (TYP) ATTACH LABEL "SEAX-0001" TO EACH TAPE & REEL PACKAGE. 7. FOR QUANTITIES UP TO 49 PIECES, NO LEADER, TRAILER, OR REEL WILL BE SUPPLIED. ,vvvvvvvvvvi FOR QUANTITIES 50-124, NO LEADER OR TRAILER WILL BE SUPPLIED. .060 [1.52] REF-SOME CENTER FEATURES .500 12.70 .652 16.56 NOT SHOWN FOR CLARITY نىسىسىسىسىن .035 0.89 ''A''**-VOIDED AT SAMTEC'S REF** DISCRETION -2.122[53.90] REF − Ø.404[10.26] REF .931±.020 23.65±0.51 POS 1 INDICATOR-.040[1.02] **REF** .221 5.61 ► .050 [1.27] (TYP) .040[1.02] .073[1.85] REF-**REF** 01 ·1.9500 49.530 (TYP) .050 [1.27] REF-A A A СД 444 <u>wwwwwwww</u> G **~ ↑ ↑ ↑** ·.120[3.05] REF W W W 000 Μ -.044 [1.12] REF Ν $\emptyset.044[1.12]$ -.034[0.86] REF -14 ROW DETAIL **REF** -2.141 [54.38] REI PROPRIETARY NOTE UNLESS OTHERWISE SPECIFIED. THIS DOCUMENT CONTAINS CONFIDENTIAL AND DIMENSIONS ARE IN INCHES. TOLERANCES ARE: MANUFACTURING REPRODUCTION USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, **DECIMALS ANGLES** INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR .XX: ±.01 [0.3] .XXX: ±.005 [0.13] 520 PARK EAST BLVD, NEW ALBANY, IN 47150 REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY PHONE: 812-944-6733 FAX: 812-948-5047 OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS ITEM NO PART NUMBER QUANTITY MATERIAL .XXXX: ±.0020 [0.051] e-Mail info@SAMTEC.com WRITTEN CONSENT OF SAMTEC INC DO NOT SCALE DRAWING SHEET SCALE: 3:2 DESCRIPTION SEAM-40-02.0-14-A 1.0000 LCP, UL 94 VO, COLOR: BLACK MODIFIED SEAM ASSEMBLY CONTACT AREA: .000030 GOLD OVER .000050 NICKEL 560.00 NEW-SUB-T-1M36-02.0-STL-1 COPPER ALLOY / LEADED SOLDER DWG. NO REMAINDER: .000200 REF TIN/LEAD (90/10) OVER .000050 NICKEL ASP-208521-01 3 K-DOT-.404-.500-.005 1.0000 POLYMIDE FILM SOLDER COMP: 63% TIN / 37% LEAD BY: J. BROWNING 01/21/2019 | SHEET 1 OF 4 CT-SEAM185MS .00571 CONDUCTIVE POLYMER F:\DWG\MISC\MKTG\ASP-208521-01-MKT.SLDDRW

## REVISION C





## PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, U.S., PATENT RIGHTS AND SALES RIGHTS ARE EPRESSLY RESERVED BY SAMTEC, MC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNALUTHORIZED PRESON OR ENTITY NOR PROPROJUCED. TRANSFERRED OR INCORPORATE IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, IN

DO NOT SCALE DRAWING

SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322


DESCRIPTION:


MODIFIED SEAM ASSEMBLY

DWG NO


ASP-208521-01

F:\DWG\MISC\MKTG\ASP-208521-01-MKT.SLDDRW BY: J. BROWNING 01/21/2019 SHEET 2 OF 4





USER DIRECTION OF UN-REELING POCKET NOT DETAILED



PACKAGING VIEW

## PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, U.S., PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEL, THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PRESON OR ENTITY NOR PERPODUCED. THANSFERRED OR INCORPORATE IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEL, IN

SAM EC

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

SHEET SCALE: 3:1

DESCRIPTION:

MODIFIED SEAM ASSEMBLY

DWG. NO.

ASP-208521-01

F:\DWG\MISC\MKTG\ASP-208521-01-MKT.SLDDRW

BY: J. BROWNING 01/21/2019 SHEET 4 OF 4