
工	۵	П	т	0







LAYOUT SHOWN AS

Keying Shown as example

## CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 19

PLATING : F = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ယ

-Standard : Based on MIL-DTL-38999 Series III

	-Shell Material	: Aluminium			
	-Shell Plating	: Nickel			
	-Insulator	: Thermoplastic			
	-Contacts	: Copper Alloy			
	-Seals & Grommet	: Silicon Elastomer			
N	-Contact Plating	: Gold over copper Alloy 0.8µm minimum			
	-Durability	: 500 Mating cycles			
	-Delivered with Souriau contacts and Accessories				
	-Temperature Range	65°C to +200°C			
	-Salt Spray	: 48 hours			
_	-Mass	: 30.59 g ± 10%			

8D 0

G

19

F

35

А

F

А


Dim	Nominal
Р	3.25±0.2
PP	4.93±0.2
R1	29.36
R2	26.97
S	36.5±0.3
V	20.83+0/-1.25
W	2.1/2.5
Z	31.5 Max
/V THREAD	M28x1-6g


**ORIENTATION : A** 

CONTACT TYPE : PIN(500 Matings)

Е

CONTACT LAYOUT : 19-35





σ		Þ				
				4		
AS EXAMPLE				3		
any non-conformi s which does not co er of the Parties or ndation, technical r untry Juriso FR 9F35AA	omply with by a third part			2		
			MOD N°			
um Receptac	CUSTOMER DRAWING   Receptacle 8D series   NPRDS / PROJECT   859   This document is the property of SOURIAU   it must not be reproduced or communicated without permission					
F35AA-C B		A	1/2			

