SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH26-0UF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rate	ed data	
Input		
Number of phases	3 AC	
Line voltage	500 690 V +1	0 % -20 %
Line frequency	47 63 Hz	
Rated voltage	690V IEC	600V NEC
Rated current (LO)	14.00 A	14.00 A
Rated current (HO)	12.10 A	12.10 A
Output		
Number of phases	3 AC	
Rated voltage	690V IEC	600V NEC ¹⁾
Rated power (LO)	11.00 kW	10.00 hp
Rated power (HO)	7.50 kW	10.00 hp
Rated current (LO)	14.00 A	14.00 A
Rated current (HO)	11.00 A	11.00 A
Rated current (IN)	15.00 A	
Max. output current	19.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Over all and the set billing		

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	70 dB	
Power loss 3)	0.360 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
$1 \rightarrow 0$	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		
Closed-loop control techniques		

Closed-loop col	ittoi techniques
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

SIEMENS


Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH26-0UF0

Ambie	nt conditions
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.055 m³/s (1.942 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Со	nnections
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)
Motor end	
Version	Screw-type terminals
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)
DC link (for braking resistor)	
PE connection	Screw-type terminals
Max. motor cable length	
Shielded	200 m (656.17 ft)
Unshielded	300 m (984.25 ft)

ical data IP20 / UL open type FSD 16.6 kg (36.60 lb) 200 mm (7.87 in) 472 mm (18.58 in)
FSD 16.6 kg (36.60 lb) 200 mm (7.87 in)
16.6 kg (36.60 lb) 200 mm (7.87 in)
200 mm (7.87 in)
472 mm (18.58 in)
248 mm (9.76 in)
lards
UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH
EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC
to IEC61800-9-2*
IE2
41.5 %
.0 W (2.0 %) 359.0 W (2.2 %)



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.