
			о Ш	
Z'	ØS			
	Keying Shown as example		LAYOUT SHOWN AS EXAMPLE	
<ul> <li>CHARACTERISTICS</li> <li>-Standard : Based on MIL-DTL-38999 Series III</li> <li>-Shell Material : Composite</li> <li>-Shell Plating : Olive drab Cadmium</li> <li>-Insulator : Thermoplastic</li> <li>-Contacts : Copper Alloy</li> <li>-Seals &amp; Grommet : Silicon Elastomer</li> <li>-Contact Plating : Gold over copper Alloy 0.8µm minimum</li> </ul>	Connector dimension         Dim       Nominal         ØS       48 Max         Z'       31.5 Max         VV THREAD       M37x1-6g	d	RIAU shall not be liable for any non-conformi ue to a use of the Products which does not co ecifications issued by either of the Parties or (professional recommendation, technical r Country Jurise FR	omply with by a third party
-Durability: 500 Mating cycles-Delivered with Souriau contacts and Accessories-Temperature Range: -65°C to +175°C-Salt Spray: 2000 hours		A 07-10-2016 First Rele ISS DATE Latest Designed By:	PN: 8D525J41AN ease modification - by Date:	MOD N° CUSTOMER DRAWING
BASIC SERIES: 8D 5 - 25	J 41 A N		General linear Tolerances:	SD series NPRDS / PROJECT 859
SHELL TYPE : Plug with RFI Shielding     CONTACT TYPE : Standard Crimp Contact     SHELL SIZE : 25	ORIENTATIC CONTACT TYPE : PIN(500 Ma		WWW.SOURIAU.COM	This document is the property of SOURIAU it must not be reproduced or communicated without permission

	т	۵	н т.	m		0
4		Contact Layout 41			•	
		22#22D, 3#20 11#16, 2#12 3#8 Triax	_			
	Ctc         X           A         0           B         7.09           C         10.77           D         12.94           E         13.27           F         8.17           G         4.67           H         0           J         -4.67           K         -8.17           L         -13.27           M         -12.94	25-41           Y         Ctc         X         Y           10.79         Y         -5.37         7.92           11.34         Z         3.32         5.72           7.92         a         7.96         -0.42           3.39         b         0         -6.6           -1.62         c         -7.96         -0.42           -6.44         d         -3.32         5.72           -12.53         e         0         4.48           -13.37         f         3.02         3.07           -12.53         g         5.32         0.005           -6.44         h         3.7         -2.43           -1.62         i         2.38         -4.74           3.39         j         -2.38         -4.74				
ى ب	N         -10.77           P         -7.09           R         5.37           S         7.32           T         10.39           U         1.77           V         -1.77           W         -10.39           X         -7.32	7.92         k         -3.7         -2.43           11.34         m         -5.32         0.005           7.92         n         -3.02         3.07           3.91         p         0         1.81           0.67         q         2.59         -0.01           -9.66         r         0         -3.53           -9.66         s         -2.59         -0.01           0.67         t         0         -3.53           -9.66         s         -2.59         -0.01           0.67         t         0         -0.86           3.91            -0.01				
						SOURIAU shall not be liable for any due to a use of the Products whi the Specifications issued by either of (professional recommendati
N						PN: 8D525J
					A 07-10-2	016 First Release
_					ISS DATI Designed By:	Date:
					SCALE	General linear Tolerances:
<u> </u>					SOURIA	U WWW.SOURIAU.C
				_	FORMAT A3	SOURIAU 8D525J4
	Н	G	F	E	D	C



Þ

σ