SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-3YH20-0AF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	500 690 V +10 °	% -20 %
Line frequency	47 63 Hz	
Rated voltage	690V IEC	600V NEC
Rated current (LO)	6.00 A	6.00 A
Rated current (HO)	5.20 A	5.20 A
Output		
Number of phases	3 AC	
Rated voltage	690V IEC	600V NEC ¹⁾
Rated power (LO)	4.00 kW	5.00 hp
Rated power (HO)	3.00 kW	4.00 hp
Rated current (LO)	6.30 A	6.30 A
Rated current (HO)	5.00 A	5.00 A
Rated current (IN)	7.00 A	
Max. output current	9.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	70 dB	
Power loss ³⁾	0.191 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load) DC 30 V, 5.0 A		
Number as transistor	0	
Analog / digital inputs		
Number 2 (Differential input)		
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number 1 (Non-isolated output)		
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm5~^\circ\text{C}$		
Closed-loop co	ntrol techniques	

Closed-loop cor	itroi techniques
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-3YH20-0AF0

Ambien	t conditions
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.055 m³/s (1.942 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 $^\circ\text{C}$ (104 $^\circ\text{F}$), condensation and icing not permissible
Coni	nections
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)
Motor end	
Version	Screw-type terminals
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)
DC link (for braking resistor)	
PE connection	Screw-type terminals
Max. motor cable length	

Degree of protection IP20 / UL open type Frame size FSD It weight 18.3 kg (40.34 lb) Dimensions Width 200 mm (7.87 in) Height 472 mm (18.58 in) Depth 248 mm (9.76 in) Depth 248 mm (9.76 in) Standards Standards UL, CUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH Converter losses IEC61800-9-2* Efficiency class IE2 177.0 W (2.4 %) 177.0 W (2.4 %) 153.0 W (2.0 %) 153.0 W (2.0 %) 153.0 W (2.0 %) 142.0 W (1.9 %)	Me	echanical data	
Net weight 18.3 kg (40.34 lb) Dimensions 200 mm (7.87 in) Width 472 mm (18.58 in) Depth 248 mm (9.76 in) Depth 248 mm (9.76 in) Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH CE marking EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC Efficiency class IE2 Comparison with the reference converter (90% / 100%) 183.0 W (2.4 %) 191.0 W (2.5 %) 100 h 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %)	Degree of protection	IP20 / UL open	type
Dimensions Width 200 mm (7.87 in) Height 472 mm (18.58 in) Depth 248 mm (9.76 in) Depth Standards Compliance with standards COnverter losses to LEC61800-9-2* Efficiency class IE2 Comparison with the reference converter (90% / 100%) 42.1 % 100% 177.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 50% 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %)	Frame size	FSD	
Width 200 mm (7.87 in) Height 472 mm (18.58 in) Depth 248 mm (9.76 in) Standards Standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH Converter losses to IEC61800-9-2* Efficiency class IE2 Converter losses to IEC61800-9-2* ID0% 177.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %)	Net weight	18.3 kg (40.34	1 lb)
Height 472 mm (18.58 in) Depth 248 mm (9.76 in) Standards Compliance with standards Compliance with standards Converter losses Converter losses to IEC61800-9-2* Efficiency class IE2 Comparison with the reference converter (90% / 100%) 100% 177.0 W (2.4 %) 1177.0 W (2.4 %) 183.0 W (2.4 %) 100% 153.0 W (2.0 %) 153.0 W (2.0 %) 155.0 W (2.1 %) 142.0 W (1.9 %) 143.0 W (1.9 %)	Dimensions		
Depth 248 mm (9.76 in) Standards Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH Comperitor 2004/108/EC, Low-Voltage Directive 2006/95/EC Converter losses to IEC61800-9-2* Efficiency class IE2 Comparison with the reference converter (90% / 100%) 183.0 W (2.4 %) 191.0 W (2.5 %) 100% 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %) 50% 142.0 W (1.9 %) 143.0 W (1.9 %) 159.0 W (2.1 %)	Width	200 mm (7.87	in)
Standards Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH CE marking EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC Converter losses to IEC61800-9-2* Efficiency class IE2 Comparison with the reference converter (90% / 100%) 183.0 W (2.4 %) 191.0 W (2.5 %) 100% 177.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 191.0 W (2.5 %) 159.0 W (2.1 %) 150.0 W (2.1 %) 150.0 W (2.1	Height	472 mm (18.5	8 in)
Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH CE marking EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC EMC Directive 2006/95/EC Converter losses to IEC61800-9-2* Efficiency class IE2 Comparison with the reference converter (90% / 100%) 42.1 % 100% 177.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 50% 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %)	Depth	248 mm (9.76	in)
Compliance with standards SEMI F47, REACH CE marking EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC Converter losses to IEC61800-9-2* Efficiency class IE2 Comparison with the reference converter (90% / 100%) 42.1 % 100% 177.0 W (2.4 %) 153.0 W (2.0 %) 155.0 W (2.1 %) 153.0 W (2.0 %) 155.0 W (2.1 %) 142.0 W (1.9 %) 143.0 W (1.9 %)		Standards	
Cernarking Voltage Directive 2006/95/EC Converter losses to IEC61800-9-2* Efficiency class IE2 Comparison with the reference converter (90% / 100%) 42.1 % 100% 177.0 W (2.4 %) 100% 183.0 W (2.4 %) 100% 155.0 W (2.1 %) 153.0 W (2.0 %) 155.0 W (2.1 %) 142.0 W (1.9 %) 143.0 W (1.9 %)	Compliance with standards		
Efficiency class IE2 Comparison with the reference converter (90% / 100%) 42.1 % 100% 177.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 100% 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %) 142.0 W (1.9 %) 143.0 W (1.9 %)	CE marking		
Comparison with the reference 42.1 % 100% 177.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 100% 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %) 142.0 W (1.9 %) 143.0 W (1.9 %)	Converter le	osses to IEC61800-	9-2*
I 177.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 100% 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %) 50% 142.0 W (1.9 %) 143.0 W (1.9 %) 159.0 W (2.1 %)	Efficiency class	IE2	
100% 153.0 W (2.4 %) 183.0 W (2.4 %) 191.0 W (2.5 %) 100% 153.0 W (2.0 %) 155.0 W (2.1 %) 159.0 W (2.1 %) 142.0 W (1.9 %) 143.0 W (1.9 %)		42.1 %	
50% •	• 🗕 1/7.0 W (2.4 %)	183.0 W (2.4 %)	191.0 W (2.5 %)
50% •			
		155.0 W (2.1 %)	159.0 W (2.1 %)
		143.0 W (1.9 %)	

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-3YH20-0AF0

	Operator panel: Intell	igent
Screen]
Display design	LCD color	_
Screen resolution	320 x 240 Pixel	
	Mechanical data]
Degree of protection	IP55 / UL type 12	_
Net weight	0.134 kg (0.30 lb)	
Dimensions		
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	

Arr	bient conditions	
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
	55 °C only with door installation kit	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C durir	ıg	
Max. operation	95 %	
	Approvals	
Certificate of suitability	CE, cULus, EAC, KCC, RCM	