



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn98%, Cu2%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
⑥E D.C. RESISTANCE 1-2	@20°C	0.35 ohms max.
⑥E D.C. RESISTANCE 4-3	@20°C	0.36 ohms max.
⑥E⑥C INDUCTANCE 1-2	10kHz, 100mVAC, Ls	70uH min.
⑥E⑥C INDUCTANCE 4-3	10kHz, 100mVAC, Ls	80uH min.
⑥E⑥B DIELECTRIC 1-4	5000VDC, 1 second	-
⑥F TURNS RATIO	(4-3):(1-2)	1.08:1, ±1%



⑥B GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -20°C to +85°C.

STORAGE TEMPERATURE RANGE: -40°C to +105°C.

⑥F COPLANARITY: All 4 terminals must lie on a plane within .004 [.10] of Surface A after lead tinning.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
6G	9/19	Method: Tape & Reel		Angles: ±1°	TRANSFORMER	750110056
6F	2/19	PKG-0548		Decimals: ±.005 [.13]		
6E	8/18	www.we-online.com/midcom		Fractions: ±1/64	Footprint: ±.005 [.13]	
6D	10/15	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750110056

