

# ABC401 Series

## 400 W AC-DC Power Supplies

The ABC401 Series of AC-DC power supplies provides up to 400 W of regulated output power through wide input voltage range 90 – 264 VAC in single outputs of 12, 24, 28, 36 or 48 VDC.

The ABC401 Series comes in five different low-profile packages, offering 12 and 5 VSB standby outputs and a full set of protection features. Available control signals include Power Good (P\_OK), Remote On/Off (PS\_ON) and remote sense compensation on the (+) load line.

The ABC401 Series complies with the latest international safety standards for IT equipment and displays the CE-Mark for the European Low Voltage Directive (LVD).

### Key Features & Benefits

- Universal input voltage range (90 – 264 VAC)
- Active PFC, EN 61000-3-2 Class C, D compliant
- Steady 400 W output power (440 W peak)
- High efficiency (94% typical)
- Low stand by power consumption (<0.5 W)
- 12, 24, 28, 36, 48 VDC standard output voltages
- +5V stand by, 2 A and 12 V auxiliary, 1 A outputs
- Low earth/touch leakage currents (<300/100  $\mu$ A)
- Fan speed control function (Off at <50 W)
- Over temperature protection
- Input under voltage, output over voltage protections
- Over current and short circuit protection
- Remote On/Off and power good signal
- 5 available packages all fit 1U installation
- UL 60950-1 and 62368-1 compliance
- EN 55032, FCC Class B, conducted radiated emissions.
- EN 55024 immunity
- 4000 m operation without de-rating
- RoHS 3 compliant (Directive EU 2015/863)

### Applications

- Video Wall Display & Entertainment
- Industrial Process Control
- Telecommunications
- Test & Measurement Equipment
- Industrial Laser applications
- 3D Printing and ATM



## 1. MODEL SELECTION

MODEL NUMBER	PACKAGE & COOLING	INPUT VOLTAGE RANGE [VAC]	NOM. OUTPUT VOLTAGE [VDC]	MAX. OUTPUT POWER [W]	MAX. OUTPUT CURRENT [A]	DIMENSIONS
ABC401-1012	Open Frame Convection / Forced Air	90 - 264	12	400	33.3	76.0 x 164.2 x 37.7 mm (2.99 x 6.46 x 1.48 in)
ABC401-1012-UC	U-Chassis Convection / Forced Air	90 - 264	12	400	33.3	84.4 x 166.5 x 40.0 mm (3.32 x 6.55 x 1.57 in)
ABC401-1012-PC	Perforated Cover Convection / Forced Air	90 - 264	12	400	33.3	84.4 x 166.5 x 41.0 mm (3.32 x 6.55 x 1.61 in)
ABC401-1012-T	Vented Cover Top Fan	90 - 264	12	400	33.3	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)
ABC401-1012-S	Enclosed Front Mounted Fan	90 - 264	12	400	33.3	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)
ABC401-1024	Open Frame Convection / Forced Air	90 - 264	24	400	16.7	76.0 x 164.2 x 37.7 mm (2.99 x 6.46 x 1.48 in)
ABC401-1024-UC	U-Chassis Convection / Forced Air	90 - 264	24	400	16.7	84.4 x 166.5 x 40.0 mm (3.32 x 6.55 x 1.57 in)
ABC401-1024-PC	Perforated Cover Convection / Forced Air	90 - 264	24	400	16.7	84.4 x 166.5 x 41.0 mm (3.32 x 6.55 x 1.61 in)
ABC401-1024-T	Vented Cover Top Fan	90 - 264	24	400	16.7	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)
ABC401-1024-S	Enclosed Front Mounted Fan	90 - 264	24	400	16.7	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)
ABC401-1028-UC	U-Chassis Convection / Forced Air	90 - 264	28	400	14.3	84.4 x 166.5 x 40.0 mm (3.32 x 6.55 x 1.57 in)
ABC401-1036	Open Frame Convection / Forced Air	90 - 264	36	400	11.1	76.0 x 164.2 x 37.7 mm (2.99 x 6.46 x 1.48 in)
ABC401-1036-UC	U-Chassis Convection / Forced Air	90 - 264	36	400	11.1	84.4 x 166.5 x 40.0 mm (3.32 x 6.55 x 1.57 in)
ABC401-1036-PC	Perforated Cover Convection / Forced Air	90 - 264	36	400	11.1	84.4 x 166.5 x 41.0 mm (3.32 x 6.55 x 1.61 in)
ABC401-1036-T	Vented Cover Top Fan	90 - 264	36	400	11.1	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)
ABC401-1036-S	Enclosed Front Mounted Fan	90 - 264	36	400	11.1	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)
ABC401-1048	Open Frame Convection / Forced Air	90 - 264	48	400	8.3	76.0 x 164.2 x 37.7 mm (2.99 x 6.46 x 1.48 in)
ABC401-1048-UC	U-Chassis Convection / Forced Air	90 - 264	48	400	8.3	84.4 x 166.5 x 40.0 mm (3.32 x 6.55 x 1.57 in)
ABC401-1048-PC	Perforated Cover Convection / Forced Air	90 - 264	48	400	8.3	84.4 x 166.5 x 41.0 mm (3.32 x 6.55 x 1.61 in)
ABC401-1048-T	Vented Cover Top Fan	90 - 264	48	400	8.3	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)
ABC401-1048-S	Enclosed Front Mounted Fan	90 - 264	48	400	8.3	84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)

## 2. INPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
AC Input Voltage	PS starts and operates at 90 V <sub>AC</sub> at all load conditions	90	100-240	264	V <sub>RMS</sub>
DC Input Voltage		170	-	270	V <sub>DC</sub>
Input Frequency		47	50/60	440	Hz
Input Current	RMS at 180 V <sub>AC</sub> , maximum load, 50 / 60 Hz RMS at 90 V <sub>AC</sub> , maximum load, 50 / 60 Hz	-	-	2.5 5.0	A
Inrush Current	265 V <sub>AC</sub> , 25 °C ambient, cold start. 24, 28, 36, 48 V, no damage 12 V	- -	- -	- 20	A
Fusing	2x Time Lag 6.3 A, 250 V on both L and N	-	-	6.3	A
Efficiency	At 115 V <sub>AC</sub>				
		20% rated load	90	-	-
		50 – 100 % rated load	92	-	-
	At 230 V <sub>AC</sub>				
		20% rated load	90	-	-
		50 – 100 % rated load	94	-	-
Input Power Consumption	Power on, 115-230 V <sub>RMS</sub> , no load Stand by, 115-230 V <sub>RMS</sub> , no load	- -	1 0.4	1.5 0.5	W
Power Factor	At full rated load, 115 VAC, 60 Hz and 230 VAC, 50 Hz input voltages	0.95	-	-	-
Harmonic Current Fluctuations and Flicker	Complies with EN-61000-3-2 Class C at 230 VAC 50 Hz, load >50 W. Complies with EN-61000-3-3 at nominal voltages and full load.				
Earth Leakage Current	Normal conditions, 240 V <sub>RMS</sub> , 60 Hz.			300	μA

### 3. OUTPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
V1 Output Voltage	0.5% set point accuracy for all voltage variants	-	12	-	V
		-	24	-	
		-	28	-	
		-	36	-	
		-	48	-	
V1 Output Power Rating	All voltages, convection cooled models, All voltages, fan cooled + forced air cooled (> 400 LFM) models All models, peak power ( $\leq 10$ s)			250	W
				400	
				440	
V1 Output Current			V1: 12 V <sub>DC</sub>	33.3	A
			V1: 24 V <sub>DC</sub>	16.7	
			V1: 28 V <sub>DC</sub>	14.3	
			V1: 36 V <sub>DC</sub>	11.1	
			V1: 48 V <sub>DC</sub>	8.3	
V1 Voltage Adjustment Range		-	-	$\pm 5$	%V1
V1 Load-Line-Cross Regulation	V <sub>AC</sub> : 90 – 264 V <sub>RMS</sub>	V1 Load: 0 – 33.3 A (12 V)		-2	%V1
		0 – 16.7 A (24 V)			
		0 – 14.3 A (28 V)			
		0 – 13.9 A (36 V)			
		0 – 8.3 A (48 V)			
		V2 Load: 0 – 1 A			
		5V <sub>SB</sub> Load: 0 – 2 A			
V1 Line Regulation	V <sub>AC</sub> : 90 – 264 V <sub>RMS</sub>	-	-	$\pm 0.1$	%V1
Transient Response (Voltage Deviation) V1, 5V <sub>SB</sub>	25% load changes at 1 A/ $\mu$ s 12V at 2200 $\mu$ F Load / I <sub>OUT</sub> > 0.5 A 24 V at 1000 $\mu$ F Load / I <sub>OUT</sub> > 0.5 A 28 V at 1000 $\mu$ F Load / I <sub>OUT</sub> > 0.5 A 36 V at 820 $\mu$ F Load / I <sub>OUT</sub> > 0.5 A 48V at 560 $\mu$ F Load / I <sub>OUT</sub> > 0.5 A 5V <sub>SB</sub> at 560 $\mu$ F Load / I <sub>OUT</sub> > 0.1 A	-	-	$\pm 5$	%V1 %5V <sub>SB</sub>
V1 Ripple and Noise	All models, Peak-to-peak, 20 MHz BW. 100 nF ceramic and 10 $\mu$ F tantalum caps at the load.	-	-	1	%V1
Start-up Rise Time	90<V <sub>IN</sub> <264, any load conditions.	5	-	85	ms
Start-up Delay	V1 in regulation after PS_ON is asserted V1 in regulation after AC is applied 5V <sub>SB</sub> in regulation after AC is applied			200	ms
				750	
				500	
Turn-on Overshoot	At I <sub>1</sub> = 500 mA, V1 in regulation within 50 ms.		10	-	%V1
			10	-	%V2
			10	-	%V <sub>SB</sub>
Hold-up Time	At nominal V <sub>IN</sub> , 400 W, for all models At nominal V <sub>IN</sub> , 365 W, for all models At nominal V <sub>IN</sub> , 200 W, for all models		16	-	ms
			20	-	
			35	-	
Minimum Load *	All models; V1, V2 and 5 V <sub>SB</sub>	0	-	-	A
Maximum Load Capacitance	At nominal V <sub>IN</sub> , 25 °C ambient	12 V	-	33000	$\mu$ F
		24 V	-	16000	
		28 V	-	14300	
		36 V	-	10000	
		48 V	-	7000	
Temperature Drift		-1.2	-	+1.2	mV/°C
V2 Output Voltage (*)	All models. Load on V2: from 5 to 1000 mA Load on V1: from 0.1 to I <sub>1</sub> rated	11.35	11.5	12.65	V
V2 Output Current (I <sub>2</sub> )	Convection / forced air cooling	-	-	1	A
5V <sub>SB</sub> Output Voltage	3% set point accuracy	-	5	-	V
5V <sub>SB</sub> Output Current (I <sub>5V<sub>SB</sub></sub> )	Convection cooled models	-	-	1.5	A
	Fan cooled + forced air cooled (> 400 LFM) models	-	-	2	
5V <sub>SB</sub> Load-Line-Cross regulation	V <sub>AC</sub> : 90 – 264 V <sub>RMS</sub>	V1 Load: 0 – 33.3 A (12 V)		-2	%5V <sub>SB</sub>
		0 – 16.7 A (24 V)			
		0 – 14.3 A (28 V)			
		0 – 13.9 A (36 V)			
		0 – 8.3 A (48 V)			
		V2 Load: 0 – 1 A			
		5V <sub>SB</sub> Load: 0 – 2 A			

## 3.1 OUTPUT POWER DE-RATING CURVES




Figure 1. Power Derating Curves for Open Frame, U-Chassis and Perforated Cover Models




Figure 2. Power Derating Curves for Top Fan and Front Mounted Fan Models

## 4. SIGNALS, CONTROLS & TIMING SPECIFICATIONS

Base signals and controls are accessible from signal connector P204.


SIGNAL	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
<b>PS_ON</b>	Active low, +5 V TTL signal compatible. Input low voltage	0	-	2.0	V
	Input high voltage (I <sub>IN</sub> = 200 μA)	3.0	-	-	V
	V1 and V2 disabled when PS_ON is open				
	5 V <sub>SB</sub> not affected by PS_ON				
	V1 and V2 enabled with PS_ON connected to RTN				
<b>P_OK</b>	+5 V TTL compatible				
	Logic level low (<10 mA sinking)	-	-	0.7	V
	Logic level high (100μA sourcing)	2.4	-	5	V
	Low to high time after V1 in regulation	0.05	-	0.1	s
	Power down warning time	1	-	-	ms
<b>5V<sub>SB</sub> output</b>	Active and in regulation after a 90<V <sub>AC</sub> <264 is applied	-	-	200	ms
	5 V <sub>SB</sub> not affected by PS_ON				



Asia-Pacific  
+86 755 298 85888


Europe, Middle East  
+353 61 49 8941

North America  
+353 61 49 8941



Above waveforms are expected with AC Input ON/OFF:

Standby on - Main outputs on	$50 \text{ ms} \leq T1 \leq 250 \text{ ms}$
Main output Rise Time	$5 \text{ ms} \leq T2 \leq 85 \text{ ms}$
5 VSB rise time	$4 \text{ ms} \leq T10 \leq 20 \text{ ms}$
Main outputs On - P_OK delay	$40 \text{ ms} \leq T3 \leq 100 \text{ ms}$
Power down warning <sup>1</sup>	$T4 \geq 1 \text{ ms}$
Main Output off - Standby off <sup>2</sup>	$T5 \geq 1.2 \text{ s}$
Hold-up time (AC off - P_OK low)	$T6 \geq 15 \text{ ms (115/ 230 VAC)}$
AC_ON - Standby turn on time	$T7 \leq 500 \text{ ms}$



Above waveforms are expected with PS\_ON Signal ON/OFF state change:

Main Output Rise Time	$5 \text{ ms} \leq T2 \leq 85 \text{ ms}$
Main Outputs on - P_OK delay	$50 \text{ ms} \leq T3 \leq 100 \text{ ms}$
Power down warning <sup>1</sup>	$1 \text{ ms} \leq T4 \leq 5 \text{ ms}$
PS_ON - Main Output (off) Timing	$T8 \leq 1 \text{ ms}$
PS_ON - Main Output (on) Timin	$T9 \leq 200 \text{ ms}$

<sup>1</sup> T4 parameter measurement setup will assume at least 10% of the maximum load on each output.

<sup>2</sup> T5 parameter measurement setup will assume at least 50% of the maximum load on main output.

## 5. PROTECTION SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
Input Under Voltage Lockout	Auto recovery, Hiccup Mode	60	75	-	V <sub>AC</sub>
Input Fuse	2x Time Lag 6.3 A, 250 V on L1 and L2	-	-	6.3	A
Over Current	At nominal input voltages. V1: Hiccup mode, auto-recovering. V2: PTC limiting, auto-recovering. 5 V <sub>SB</sub> : Hiccup mode, auto-recovering.	110	-	150	%I <sub>1MAX</sub>
Short Circuit	At nominal input voltages. V1: Hiccup mode, auto-recovering. V2: PTC limiting, auto-recovering. 5 V <sub>SB</sub> : Hiccup mode, auto-recovering.	-	-	-	
Over Voltage	12 V 24 V 28 V 36 V 48 V 5 V <sub>SB</sub>  Unit shut down and latch off	110	-	136	%V <sub>NOM</sub>
Over Temperature (on primary stage)	Shut down, latch off.	-	-	-	
Over Temperature (on secondary side)	Hiccup mode, auto-recovering.	-	-	-	
Isolation Primary-to- Secondary	Reinforced	4000	-	-	V <sub>AC</sub>
Isolation Input-to-PE	Basic	1500	-	-	V <sub>AC</sub>
Isolation V1-to-V2		100	-	-	V <sub>DC</sub>
Isolation Output-to-PE	Basic	1500	-	-	V <sub>AC</sub>

## 6. ENVIRONMENTAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
Operating Temperature Range	No de-rating up to 50 °C PS starts up at -30 °C	-20	-	50	°C
De-rated Operating Temperature Range	Natural convection cooling: Linearly de-rate from 250 W at 50 °C, to 100 W at 70 °C Forced air cooling: Linearly de-rate from 400 W at 50 °C, to 280 W at 70 °C. See graphs below.	-	-	70	°C
Storage Temperature Range		-40	-	85	°C
Humidity	RH, Non-condensing Operating Non-operating	-	-	90 95	% %
Operating Altitude		-	-	4000	m
Shock	<b>EN 60068-2-27</b> Operating: Half sine, 30 g, 18 ms, 3 axes, 6x each (3 positive and 3 negative). Non-Operating: Half sine, 50 g, 11 ms, 3 axes, 6x each (3 positive and 3 negative).				
Vibration	<b>EN 60068-2-64</b> Operating: Sine, 10 – 500 Hz, 1 g, 3 axes, 1 oct/min., 60 min. Random, 5 – 500 Hz, 0.02 g <sup>2</sup> /Hz, 1 g <sub>RMS</sub> , 3 axes, 30 min. Non-Operating: 5 – 500 Hz, 2.46 g <sub>RMS</sub> (0.0122 g <sup>2</sup> /Hz), 3 axes, 30 min.				
MTBF	Full Load, 120 V <sub>AC</sub> , 40 °C ambient 80% Duty cycle, Telcordia SR-332 Issue 2	400000	-	-	Hours
Useful Life	Low line range, 200 W, 40 °C ambient, natural convention.	-	4	-	Years
Thermal Considerations	The output power de-rating curves are herein provided. These curves can be used as a guideline to assess the limit in performance of a power supply once installed in a system providing controlled air flow at a certain input voltage and ambient temperature.				



Asia-Pacific  
+86 755 298 85888

Europe, Middle East  
+353 61 49 8941

North America  
+353 61 49 8941

## 7. ELECTROMAGNETIC COMPATIBILITY (EMC) – EMISSIONS

PARAMETER	DESCRIPTION / CONDITION	STANDARD	PERFORMANCE CLASS
Conducted	115 V <sub>RMS</sub> , 230 V <sub>RMS</sub> . Maximum load 4 dB minimum margin	EN 55032 (ITE)	B
Radiated	At 10 m distance	EN 55032 (ITE)	B
Line Voltage Fluctuation and Flicker	At 20%, 50% and 100% maximum load Nominal input voltages	EN 61000-3-3	
Harmonic Current Emission	Nominal input voltages Output load > 50 W	EN 61000-3-2	C

## 8. ELECTROMAGNETIC COMPATIBILITY (EMC) – IMMUNITY

PARAMETER	DESCRIPTION / CONDITION	STANDARD	TEST LEVEL	CRITERIA
	Reference standards for ITE equipment	EN 55024		
ESD	15 kV air discharge, 8 kV contact, at any point of the system.	EN 61000-4-2	4	A
Radiated Field	3 V/m, 80-1000 MHz, 1 KHz 80% AM. Dwell time is 3 sec for 2 Hz modulation Dwell time is 1 sec for 1KHz modulation	EN 61000-4-3	3	A
Electric Fast Transient	±2 kV on AC power port for 1 minute; ±1 kV on signal/control lines	EN 61000-4-4	3	A
Surge	±2 kV line to line; ± 4 kV line to earth on AC power port	EN 61000-4-5	4	A
Conducted RF Immunity	3 V <sub>RMS</sub> , 0,15-80 MHz, 1 KHz/2 Hz 80% AM	EN 61000-4-6	3	A
Dips and Interruptions	100 - 240V <sub>AC</sub> Drop-out to 5% for 0.5 cycles (10 ms) Dip to 70% for 25 cycles (500 ms) Interruptions > 95% for 5 s	EN61000-4-11 EN61000-4-11 EN61000-4-11		A A B

## 9. SAFETY AGENCIES APPROVALS

CERTIFICATION BODY	SAFETY STANDARDS	CATEGORY
CSA/UL	CSA C22.2 No. 60950-1, UL 60950-1 and UL 62368-1	Audio Video and IT equipment
IEC IECEE CB Certification	IEC/EN 62368-1	Audio Video and IT equipment
CE	Directive 2014/35/EU: Electrical Safety: Low Voltage electrical equipment (LVD) Directive 2014/30/EU: Electromagnetic Compatibility (EMC) Directive EU 2015/863: RoHS 3	Audio Video and IT equipment


## 10. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION
Weight	410 g (0.90 lb) 525 g (1.16 lb) – UC model 575 g (1.43 lb) – PC model 670 g (1.48 lb) – T model 525 g (1.16 lb) – S model
Overall Dimensions	76.0 x 164.2 x 37.7 mm (2.99 x 6.46 x 1.48 in) 84.4 x 166.5 x 40.0 mm (3.32 x 6.55 x 1.57 in) – UC model 84.4 x 170.5 x 41.0 mm (3.32 x 6.71 x 1.61 in) – PC model 84.4 x 166.5 x 41.0 mm (3.32 x 6.55 x 1.61 in) – T model 84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in) – S model




## 10.1 OUTLINE DRAWING & CONNECTIONS – OPEN FRAME MODEL

Overall Dimensions: 76.0 x 164.2 x 37.7 mm (2.99 x 6.46 x 1.48 in)  
 Weight: 410 g (0.90 lb)




**10.2 OUTLINE DRAWING & CONNECTIONS – U-CHASSIS MODEL (-UC)**

Overall Dimensions: 84.4 x 166.5 x 40.0 mm (3.32 x 6.55 x 1.57 in)  
 Weight: 525 g (1.16 lb)




## 10.3 OUTLINE DRAWING & CONNECTIONS – PERFORATED MODEL (-PC)

Overall Dimensions: 84.4 x 170.5 x 41.0 mm (3.32 x 6.71 x 1.61 in)  
 Weight: 575 g (1.43 lb)




**10.2 OUTLINE DRAWING & CONNECTIONS – VENTED COVER MODEL (-T)**

Overall Dimensions: 84.4 x 166.5 x 41.0 mm (3.32 x 6.55 x 1.61 in)  
 Weight: 670 g (1.48 lb)



## 10.2 OUTLINE DRAWING & CONNECTIONS – FRONT FAN MODEL (-S)

Overall Dimensions: 84.4 x 183.0 x 41.0 mm (3.32 x 7.20 x 1.61 in)  
 Weight: 625 g (1.416lb)



## 11. CONNECTIONS AND PIN DESCRIPTION

### AC INPUT CONNECTOR – P1

**Molex 26-60-4030** or equivalent

Mating Connector:  
Molex 09-93-0300 (Crimp Terminal Housing)  
Molex 08-50-0105 (Crimp Terminal, 18-24 AWG)

### PROTECTION EARTH CONNECTOR - P5

**Tyco 63849-1** equivalent

Mating Connector:  
Any tin finished 6.35 x 0.81 mm receptacle

### DC OUTPUT CONNECTOR – P4


**Molex 39-28-8120** or equivalent

Mating Connector:  
Molex 39-01-2120 (Crimp Terminal Housing)  
Molex 39-00-0039 (Crimp Terminal, 18-24 AWG)

### SIGNAL CONNECTOR – P6


**Molex 90130-1108** or equivalent

Mating Connector  
Molex 90142-0008 (Crimp Terminal Housing)  
Molex 90119-0109 (Crimp Terminal, 22-24 AWG)



PIN REF.	FUNCTION
1	Line 1
2	Not Present
3	Line 2

PIN REF.	FUNCTION
GDN	AC Ground



PIN REF.	FUNCTION
1 – 6	V1
7 – 12	DC Return

PIN REF.	FUNCTION
1	+5V <sub>SB</sub>
2	P_OK
3	-V2
4	PS_ON
5	RS+
6	RTN
7	+V2
8	RTN

**For more information on these products consult: [tech.support@psbel.com](mailto:tech.support@psbel.com)**

**NUCLEAR AND MEDICAL APPLICATIONS** - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

**TECHNICAL REVISIONS** - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.