

- 2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); REDUCED DIA. WIRE SEAL.
- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);


IP69K (MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-19S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND WIRE RANGE:


CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
12	2.46 mm (.097in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS
16	1.35 mm (.053 in)	3.05 mm (.120 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS

7. RECEPTACLE IS SUPPLIED WITH DUST CAP.



RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



	AHDP04-24-19PR-BRA		REF:HDP24-24-19PE-L017						
QUANTITY	PART NUMBER		DESCRIPTION						
MATERIALS LIST									
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metrio(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		SIGNATURE	S DATE	Amphenol					
		DRAWN: VITO.LI	01MAR22						
2 PL DEC ±0.15 3 PL DEC ±0.08	2 PL DEC ±0.15 Angles ±1*		02MAR22	Sine Systems - www.amphenol-sine.com 44724 Morley Drive					
3) Note reference = X		ENGINEER:							
MATERIAL SPECIFICA	TIONS:	APPROVAL: TOMMYXIE	03MAR22	Clinton Township, MI 48036					
WEIGH	WEIGHT: 48.6g			19POS, RECEPTACLE, PIN, SIZE 24,					
0		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL		RD SEAL, BRA, DURAMATE AHDP					
PROCESS SPECIFICATIONS: NEXT ASS'Y:				B C- AHDP04-24-19PI	R-BRA A1				
				SCALE: NONE DURAMATE SHEE	T 1 OF 1				

읶