



Specifications

Electrical Ratings	50mA @ 50VDC	Dielectric Strength	250Vrms min
Electrical Life	100,000 cycles typical	Insulation Resistance	>100MΩ min
Contact Resistance	<50mΩ initial	Operating Temperature	-40°C to 85°C
Actuation Force	180 ± 50gF	Storage Temperature	-40°C to 85°C
Acutation Travel	.30 ± .1mm		

Materials

Actuator	6/6 Nylon	
Housing	6/6 Nylon	
Cover	er Stainless Steel	
Contacts	Phosphor Bronze, Silver Plated	
Terminals	Brass, Silver Plated	


Ordering Information

1. Series	CT1103	G	F180	C141
CT1103				
2. Actuator Options A B C T G E				
3. Actuation Force: F180 = 180gF				
4. Cap C11 C12 C13 C16 C18	C19 C22 C26	Cap Colors: **See Cap Options for color availability **Caps available with G actuator only		





12mm Square Through-Hole Tactile

Dimensions




Schematic & PC Layout









Cap Options for G Actuator




C11_ 1 = White, 2 = Black, 3 = Red, 9 = Light Gray Contact Factory for other available colors




C16_ 1 = White, 2 = Black, 3 = Red, 7 = Blue Contact Factory for other available colors




C22_ 2 = Black, 8 = Dark Gray, 9 = Light Gray Contact Factory for other available colors




C12_ 1 = White, 2 = Black, 3 = Red, 9 = Light Gray Contact Factory for other available colors




C18_ 1 = White, 2 = Black, 3 = Red, 9 = Light Gray Contact Factory for other available colors



C13_ 1 = White, 2 = Black, 3 = Red, 9 = Light Gray Contact Factory for other available colors



C19_ 1 = White, 2 = Black, 3 = Red, 8 = Dark Gray Contact Factory for other available colors



C26_ 1 = White, 2 = Black, 3 = Red, 9 = Light Gray Contact Factory for other available colors

1 = White, 2 = Black, 3 = Red, 9 = Light Gray Contact Factory for other available colors