# CTMPC100804F Series

## From 0.24 μH to 2.2 μH



### **CHARACTERISTICS**

**Description:** SMD Shielded Molded Power Inductor

Applications: Smartphone, Tablet PC, Hard Disk for Ultrabook,

LTE Module, Portable Devices, etc.

Operating Temperature: -40°C to 125°C (including self-

temperature rise)

Inductance Tolerance: ±20%

Testing: Inductance is tested on an E4991A/HP4287A+16197A,

2MHz, 0.2V.

Packaging: Tape and Reel.

Miscellaneous: RoHS Compliant.

Additional Information: Additional electrical & physical

information available upon request.

Samples available. See website for ordering information.


### **SPECIFICATIONS**

Isat: DC current (A) that will cause L to drop approximately 30%. Irms: DC current (A) that will cause an approximate  $\Delta T$  of 40°C.

Part Number	Inductance (µH)	L Test Freq. (MHz)	DCR Max. (mΩ)	Isat Max. (A)	Irms Max. (A)
CTMPC100804F-R24M	0.24	2.0	40	7.5	4.5
CTMPC100804F-R47M	0.47	2.0	46	5.2	3.1
CTMPC100804F-R68M	0.68	2.0	65	3.8	2.9
CTMPC100804F-1R0M	1.0	2.0	78	3.4	2.5
CTMPC100804F-1R5M	1.5	2.0	105	3.2	2.2
CTMPC100804F-2R2M	2.2	2.0	156	2.6	1.4

### PHYSICAL DIMENSIONS

Size	A	В	C	D
			Max.	
mm	$2.5 \pm 0.2$	$2.0 \pm 0.2$	1.0	$0.6 \pm 0.2$
inches	$0.098 \pm 0.008$	$0.079 \pm 0.008$	0.039	$0.024 \pm 0.008$



### **PAD LAYOUT**

