
т	ם D	п –		0







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

ယ

 \sim

-Mass

BASIC SERIES:

SHELL SIZE : 19

SHELL TYPE : Square Flange Receptacle

PLATING : Z = Black Zinc Nickel

Н

CONTACT TYPE : Standard Crimp Contact

-Standard : Based on MIL-DTL-38999 Series III

ł	-Shell Material	: Aluminium		
	-Shell Plating	: Black Zinc Nickel		
	-Insulator	: Thermoplastic		
	-Contacts	: Copper Alloy		
	-Seals & Grommet	: Silicon Elastomer		
	-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum		
	-Durability	: 500 Mating cycles		
	-Delivered with Souriau	a contacts and Accessories		
	-Temperature Range	: -65℃ to +175℃		
	-Salt Spray	: 500 hours		

: 44.66 g ± 10%

8D 0

G

19

Ζ

11

В

F

Ν


Connector dimension				
Dim	Nominal			
Р	3.25±0.2			
РР	4.93±0.2			
R1	29.36			
R2	26.97			
S	36.5±0.3			
V	20.83+0/-1.25			
W	2.1/2.5			
Z	31.5 Max			
VV THREAD	M28x1-6g			


ORIENTATION : N

CONTACT LAYOUT : 19-11

CONTACT TYPE : SOCKET(500 Matings)

Е





Φ		۵						
			4					
6/2	A STATE							
-								
	1							
1								
-								
AS EXAMPLE			3					
r any non-conform	ity or damage							
s which does not c	omply with							
er of the Parties or by a third party ndation, technical notice.)								
	diction & Control List							
FR	Not Listed		2					
9Z11BN								
		MOD N°						
	CUSTOMER DRAWING							
um Receptad	cle 8D series							
	n Receptacle 8D series							
ar :	NPRDS / PROJECT 859		1					
This document is the property of								
J.COM	SOURIAU it must not be repro							
U DRG N°	communicated withou	SHEET						
Z11BN-C		1/2						
В		A	J					

