
REVISIONS								
REV	ECO	DESCRIPTION	DATE	BY	APPR			
A1	-	RELEASE NEW DRAWING	29/MAR/22	MILO	TOMMY			



44.8±0.50 **⊸** 12.6 → Ø33.8 Ø35.6 1 1/2-18 UNEF THREAD

SIZE 16 CONTACTS /6 <sup>\</sup> (14 PLACES) 15004-18-145N-BR

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); STANDARD DIA. WIRE SEAL

- 3. SPECIFICATIONS:
  - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
  - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
  - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
  - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);

IP69K(MATED CONDITION).

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-18-14P\* (\* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.


## /6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
16	2.54 mm (.100in)	3.40 mm (.134 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS



MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



AHDP04-18-14SN-BRA REF:HDP24-18-14SN-L017 DESCRIPTION QUANTITY PART NUMBER ITEM **MATERIALS LIST** UNLESS OTHERWISE SPECIFIED SIGNATURES DATE **Amphenol**  All dimensions are in metric
 Tolerances are as follows: MILO 29/MAR/22 SULLEN 30/MAR/22

Clinton Township, MI 48036 TOMMY 31/MAR/22 MATERIAL SPECIFICATIONS 14POS, RECEPTACLE, SOCKET, SIZE 18, WEIGHT: 41.3g THIS DRAWING IS SUPPLIED FOR
INFORMATION ONLY. DESIGN FEATURES,
SPECIFICATIONS AND PERFORMANCE DAT.
SHOWN HEREON ARE THE PROPERTY OF
THE AMPHENOL CORPORATION. NO RIGHT
OF REPRODUCTION ARE IMPLIED. ALL
DIMENSIONS ARE SUBJECT TO NORMAL
MANUFACTURING VARIATIONS.

PROCESS SPECIFICATIONS

NEXT ASS'Y:

NORMAL SEAL, BRA, DURAMATE AHDP

44724 Morley Drive

AHDP04-18-14SN-BRA

REV:

AHDP04-18-14SN-BRA A 1 В SCALE: NONE DURAMATE SHEET 1 OF 1