
REV	ECO	
A1	-	



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL: HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER

AMDD

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); STANDARD DIA. WIRE SEAL

10.06-18-08PN-BP

## 3. SPECIFICATIONS:

3.1 OPERATING TEMPERATURE: -55°C TO +125°C. 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC. 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.

SIZE 12 CONTACTS


"pher

(8 PLACES)

6 \

- 3.4 MOISTURE RESISTANCE: IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION); IP69K(MATED CONDITION). 3.5 MATING CYCLE DURABILITY: 100 CYCLES 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP02-18-08S\* & AHDP04-18-08S\* (\* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT	
SIZE	O.D.	O.D.	WIRE RANGE	RATING	
12	3.40 mm	4.32 mm	10-14 AWG	25 AMPS	
12	(.135 in)	(.170 in)	(6.0-2.0mm <sup>2</sup> )		



BACKSHELL RING ADAPTER - GREEN

	AHDP06-18-08PN-BRA				
QUANTITY	PART NUMBER				
MAT					
UNLESS OTHERWISE SPECIFIED		SIGNATURES			
<ol> <li>All dimensions are in metric(mm).</li> <li>Tolerances are as follows:</li> <li>PL DEC ±0.30   Fractions ±1/64</li> </ol>		DRAWN:	MILO		
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	SULLEN		
3) Note reference	= <u>x</u>	ENGINEER:			
MATERIAL SPECIFICA	ECIFICATIONS:	APPROVAL:	TOMMY		
WEIGH	T: 44.3a	CUSTOMER:			
PROCESS SPECIFICA	•	THIS DRAWING IS SUPPI INFORMATION ONLY. DE SPECIFICATIONS AND PI SHOWN HEREON ARE TI THE AMPHENOL CORPO OF REPRODUCTION ARE DIMENSIONS ARE SUBJE MANUFACTURING VARIA		SIGN FI RFORI E PRO RATION IMPLIE CT TO	

