



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
J2	REVISED PER	ECN-22-155500	25MAY2022	RK	MF



RECOMMENDED HOLE LAYOUT

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4 SINGLE TUBING PACKAGING
- 5 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 6 FINISH: POSTS- .000015 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 7 FINISH: POSTS- .000015 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 8 HIGH TEMPERATURE CONFIGURATION

REMARKS	PLATING	EXCEPT	C	B	A	NO OF POSN	PART NUMBER
△8	△7	△4	.384	.300	3	4	9-103325-1
△8	△7		3.984	3.900	39	40	9-103325-0
△8	△7		3.884	3.800	38	39	8-103325-9
△8	△7		3.784	3.700	37	38	8-103325-8
△8	△7		3.684	3.600	36	37	8-103325-7
△8	△7		3.584	3.500	35	36	8-103325-6
△8	△7		3.484	3.400	34	35	8-103325-5
△8	△7		3.384	3.300	33	34	8-103325-4
△8	△7		3.284	3.200	32	33	8-103325-3
△8	△7		3.184	3.100	31	32	8-103325-2
△8	△7		3.084	3.000	30	31	8-103325-1
△8	△7		2.984	2.900	29	30	8-103325-0
△8	△7		2.884	2.800	28	29	7-103325-9
△8	△7		2.784	2.700	27	28	7-103325-8
△8	△7		2.684	2.600	26	27	7-103325-7
△8	△7		2.584	2.500	25	26	7-103325-6
△8	△7		2.484	2.400	24	25	7-103325-5
△8	△7		2.384	2.300	23	24	7-103325-4
△8	△7		2.284	2.200	22	23	7-103325-3
△8	△7		2.184	2.100	21	22	7-103325-2
△8	△7		2.084	2.000	20	21	7-103325-1
△8	△7		1.984	1.900	19	20	7-103325-0
△8	△7		1.884	1.800	18	19	6-103325-9
△8	△7		1.784	1.700	17	18	6-103325-8
△8	△7		1.684	1.600	16	17	6-103325-7
△8	△7		1.584	1.500	15	16	6-103325-6
△8	△7		1.484	1.400	14	15	6-103325-5
△8	△7		1.384	1.300	13	14	6-103325-4
△8	△7		1.284	1.200	12	13	6-103325-3
△8	△7		1.184	1.100	11	12	6-103325-2
△8	△7		1.084	1.000	10	11	6-103325-1
△8	△7		.984	.900	9	10	6-103325-0
△8	△7		.884	.800	8	9	5-103325-9
△8	△7		.784	.700	7	8	5-103325-8
△8	△7		.684	.600	6	7	5-103325-7
△8	△7		.584	.500	5	6	5-103325-6
△8	△7		.484	.400	4	5	5-103325-5
△8	△7		.384	.300	3	4	5-103325-4
△8	△7		.284	.200	2	3	5-103325-3
△8	△7		.184	.100	1	2	5-103325-2
△8	△7		.084	—	—	1	5-103325-1

OBSOLETE	△6	△4	.384	.300	3	4	—4-103325-1
OBSOLETE	△6		3.984	3.900	39	40	—4-103325-0
OBSOLETE	△6		3.884	3.800	38	39	—3-103325-9
OBSOLETE	△6		3.784	3.700	37	38	—3-103325-8
OBSOLETE	△6		3.684	3.600	36	37	—3-103325-7
OBSOLETE	△6		3.584	3.500	35	36	—3-103325-6
OBSOLETE	△6		3.484	3.400	34	35	—3-103325-5
OBSOLETE	△6		3.384	3.300	33	34	—3-103325-4
OBSOLETE	△6		3.284	3.200	32	33	—3-103325-3
OBSOLETE	△6		3.184	3.100	31	32	—3-103325-2
OBSOLETE	△6		3.084	3.000	30	31	—3-103325-1
OBSOLETE	△6		2.984	2.900	29	30	—3-103325-0
OBSOLETE	△6		2.884	2.800	28	29	—2-103325-9
OBSOLETE	△6		2.784	2.700	27	28	—2-103325-8
OBSOLETE	△6		2.684	2.600	26	27	—2-103325-7
OBSOLETE	△6		2.584	2.500	25	26	—2-103325-6
OBSOLETE	△6		2.484	2.400	24	25	—2-103325-5
OBSOLETE	△6		2.384	2.300	23	24	—2-103325-4
OBSOLETE	△6		2.284	2.200	22	23	—2-103325-3
OBSOLETE	△6		2.184	2.100	21	22	—2-103325-2
OBSOLETE	△6		2.084	2.000	20	21	—2-103325-1
OBSOLETE	△6		1.984	1.900	19	20	—2-103325-0
OBSOLETE	△6		1.884	1.800	18	19	—1-103325-9
OBSOLETE	△6		1.784	1.700	17	18	—1-103325-8
OBSOLETE	△6		1.684	1.600	16	17	—1-103325-7
SUPERSEDED	△6		1.584	1.500	15	16	—1-103325-6
SUPERSEDED	△6		1.484	1.400	14	15	—1-103325-5
OBSOLETE	△6		1.384	1.300	13	14	—1-103325-4
OBSOLETE	△6		1.284	1.200	12	13	—1-103325-3
OBSOLETE	△6		1.184	1.100	11	12	—1-103325-2
OBSOLETE	△6		1.084	1.000	10	11	—1-103325-1
OBSOLETE	△6		.984	.900	9	10	—1-103325-0
OBSOLETE	△6		.884	.800	8	9	—103325-9
OBSOLETE	△6		.784	.700	7	8	—103325-8
OBSOLETE	△6		.684	.600	6	7	—103325-7
OBSOLETE	△6		.584	.500	5	6	—103325-6
SUPERSEDED	△6		.484	.400	4	5	—103325-5
OBSOLETE	△6		.384	.300	3	4	—103325-4
OBSOLETE	△6		.284	.200	2	3	—103325-3
OBSOLETE	△6		.184	.100	1	2	—103325-2
OBSOLETE	△6		.084	—	—	1	—103325-1

REMARKS	PLATING	EXCEPT	C	B	A	NO OF POSN	PART NUMBER
---------	---------	--------	---	---	---	------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIN H MOLL 22OCT87
 CHK 23OCT87
 THOMAS C CLARK
 APVD THOMAS C CLARK 23OCT87
 NAME

TE Connectivity

HDR ASSY, MOD II, BREAKAWAY, SR, .100, RIGHT ANGLE, WITH .025 SQ POSTS

SIZE: A1 CAGE CODE: 00779 DRAWING NO: 103325
 WEIGHT: — RESTRICTED TO: —
 MATERIAL: HOUSING: PLATE RETAINER; THERMOPLASTIC; COLOR: BLACK; POSTS: COPPER ALLOY
 FINISH: SEE TABLE
 WEIGHT: —
 CUSTOMER DRAWING

SCALE: 4:1 SHEET 1 of 1 REV J2