Product data sheet Characteristics

ATS48D75Y

soft starter for asynchronous motor, ATS48, 65 A, 208..690 V, 15..55 KW





Main Range of Product Altistart 48 Product or Component Soft starter Type Product destination Asynchronous motors **Product Specific** Heavy duty industry and pumps Application Device short name ATS48 Power supply voltage 208...690 V - 15...10 % 15 KW 230 V for severe applications Motor power kW 30 KW 400 V for severe applications 30 KW 440 V for severe applications 37 KW 400 V for standard applications 37 KW 440 V for standard applications 37 KW 500 V for severe applications 37 KW 525 V for severe applications 45 KW 500 V for standard applications 45 KW 525 V for standard applications 45 KW 660 V for severe applications 45 KW 690 V for severe applications 55 KW 660 V for standard applications 55 KW 690 V for standard applications 18.5 kW 230 V for standard applications Maximum Horse Power 15 Hp 208 V for severe applications 20 Hp 208 V for standard applications Rating 20 Hp 230 V for severe applications 25 Hp 230 V for standard applications 40 Hp 460 V for severe applications 50 Hp 460 V for standard applications 50 Hp 575 V for severe applications 60 hp 575 V for standard applications Power dissipation in W 201 W for standard applications 245 W for standard applications Utilisation category

applications

applications

Start with torque control (current limited to 5 In)

75 A connection in the motor supply line for severe

75 A connection in the motor supply line for standard

Complementary

Complementary	
Assembly style	With heat sink
Function Available	External bypass (optional)
Power supply frequency	5060 Hz - 55 %
Power supply frequency limits	47.563 Hz
Device connection	In the motor supply line
Discrete output number	2
Discrete output type	LO1) logic output 0 V common configurable LO2) logic output 0 V common configurable R1) relay outputs fault relay NO R2) relay outputs end of starting relay NO R3) relay outputs motor powered NO
Output absolute accuracy precision	+/- 5 %
Minimum switching current	10 mA 6 V DC relay outputs
Maximum switching current	Logic output 0.2 A 30 V DC Relay outputs 1.8 A 230 V AC inductive, cos phi = 0.5 20 ms Relay outputs 1.8 A 30 V DC inductive, cos phi = 0.5 20 ms

Type of start

Icl nominal current

Discrete input number	5
Discrete input type	PTC, 750 Ohm 77 °F (25 °C) Stop, Run, Ll3, Ll4) logic, <= 8 mA 4300 Ohm
Discrete input voltage	24 V <= 30 V
Discrete input logic	Positive logic Stop, Run, LI3, LI4 < 5 V <= 2 mA > 11 V, >= 5 mA
Starting current	0.41.3 lcl adjustable
Analogue output type	Current output AO 0-20 mA or 4-20 mA 500 Ohm
Communication Port Protocol	Modbus
Connector type	1 RJ45
Communication data link	Serial
Physical interface	RS485 multidrop
Transmission Rate	4800, 9600 or 19200 bps
Max nodes number	31
Protection type	Phase failure line Thermal protection motor Thermal protection starter
Marking	CE
Operating position	Vertical +/- 10 degree
Height	11.42 in (290 mm)
Width	7.48 in (190 mm)
Depth	9.25 in (235 mm)
Net Weight	18.30 lb(US) (8.3 kg)
Motor power range AC-3	1525 KW 200240 V 3 phase 3050 KW 380440 V 3 phase 55100 KW 480500 V 3 phase 3050 kW 480500 V 3 phase
Motor starter type	Soft starter

Environment

Electromagnetic compatibility	Conducted and radiated emissions level A IEC 60947-4-2 Conducted and radiated emissions level B IEC 60947-4-2 Damped oscillating waves level 3 IEC 61000-4-12 Electrostatic discharge level 3 IEC 61000-4-2 Immunity to electrical transients level 4 IEC 61000-4-4 Immunity to radiated radio-electrical interference level 3 IEC 61000-4-3 Voltage/current impulse level 3 IEC 61000-4-5	
Standards	EN/IEC 60947-4-2	
Product Certifications	SEPRO TCF CCC CSA UL C-tick NOM 117 DNV GOST	
Noise level	58 dB	
Relative humidity	095 % without condensation or dripping water EN/IEC 60068-2-3	
Ambient air temperature for operation	perature for operation 104140 °F (4060 °C) with current derating of 2 % per °C) 14104 °F (-1040 °C) without derating)	
Ambient Air Temperature for Storage	-13158 °F (-2570 °C)	
Operating altitude	<= 3280.84 ft (1000 m) without derating > 3280.846561.68 ft (> 10002000 m) with current derating of 2.2 % per additional 100 m	

Ordering and shipping details

0 11 0	
Category	22579 - OPEN ATS48 ALTISTART
Discount Schedule	CP1G
GTIN	3389110982305
Nbr. of units in pkg.	1
Package weight(Lbs)	23.47 lb(US) (10.646 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	12.01 in (30.5 cm)	
Package 1 width	14.37 in (36.5 cm)	
Package 1 Length	15.75 in (40 cm)	

Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	☐ China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Contractual warranty		
Warranty	18 months	

ATS48D75Y

Dimensions



- (1) Right View
- (2) Front View

Product data sheet Mounting and Clearance

ATS48D75Y

Clearance

