

CLP6C-RKW/AKW: PLCC6 3 IN 1 SMD LED



PRODUCT DESCRIPTION

These SMD LEDs are packaged in the • industry standard CLPP6 package. These high-reliability and high-brightness LEDs • are designed to work in a wide range of environmental conditions and are ideally suited for use in illumination applications.

Their wide viewing angle makes these LEDs ideally suited for channel letter, or general backlighting and illumination applications. The flat top emitting surface makes it easy for these LEDs to mate with light pipes.

FEATURES

- Size (mm): 6.0 X 5.0
- Color and Typical Dominant Wavelength: Red (618-630nm)
 Amber (584-596nm)
- Luminous Intensity (mcd)
 CLP6C-RKW:(3550-7100)
 CLP6C-AKW:(3550-9000)
- Lead Free
- · RoHS Compliant

APPLICATIONS

- Channel Letter
- Backlight



ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C)

Items	Symbol	Absolute Maximum Rating	Unit	
		Red/Amber		
Forward Current	l _F	3 x 80	mA	
Peak Forward Current Note1	I _{FP}	3 x 200	mA	
Reverse Voltage	V_R	5	V	
Power Dissipation	$P_{\scriptscriptstyle D}$	3 x 240	mW	
Operation Temperature	T _{opr}	-40 ~ +100	°C	
Storage Temperature	T_{stg}	-40 ~ +100	°C	
Junction Temperature	T_{J}	110	°C	
Junction/Ambient	R_{THJA}	3 x 250	°C/W	
Junction/Solder Point	R_{THJS}	3 x 150	°C/W	
Electrostatic Discharge Classification (MIL-STD-883E)	ESD	Class 2		

Note:

1. Pulse width ≤0.1 msec, duty ≤1/10.

TYPICAL ELECTRICAL & OPTICAL CHARACTERISTICS ($T_A = 25$ °C)

Characteristics	Color	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	Red/Amber	$V_{_{\rm F}}$	I _F = 50 mA	V		2.4	3.0
Reverse Current	Red/Amber	I _R	V _R = 5 V	μΑ			10
Dominant Wavelength	Red	$\lambda_{_{D}}$	I _F = 3 x 50 mA	nm	618	624	630
	Amber	$\lambda_{_{\mathrm{D}}}$	I _F = 3 x 50 mA	nm	584	591	596
Luminous Intensity	Red	I_{V}	I _F = 3 x 50 mA	mcd	3550	4800	
	Amber	I _v	I _F = 3 x 50 mA	mcd	3550	5000	

^{*} Continuous reverse voltage can cause LED damage.



INTENSITY BIN LIMIT

Red(3 x 50 mA) - CLP6C-RKW			Amber (3 x 50 mA) - CLP6C-AKW				
Bin Code	Min.(mcd)	Max.(mcd)	Bin Code	Min.(mcd)	Max.(mcd)		
Yb	3550	4500	Yb	3550	4500		
Z0	4500	5600	Z0	4500	5600		
A0	5600	7100	A0	5600	7100		
			В0	7100	9000		

^{*} Tolerance of measurement of luminous intensity is ±10%

COLOR BIN LIMIT

Red (3 x 50 mA) - CLP6C-RKW			Amber (3 x 50 mA) - CLP6C-AKW			
Bin Code	Min.(nm) Max.(nm)		Bin Code	Min.(nm)	Max.(nm)	
RA	618	630	AA	584	596	

^{*} Tolerance of measurement of dominant wavelength is ±1 nm



ORDER CODE TABLE

Color Kit Numbe	Via Number	Luminous In	itensity (mcd)	Dominant Wavelength			
	Kit Nullibei	Min.	Max.	Color Bin	Min. (nm)	Color Bin	Max. (nm)
Red	CLP6C-RKW-CYbA0AA3	3550	7100	RA	618	RA	630
Red	CLP6C-RKW-CZ0A0AA3	4500	7100	RA	618	RA	630

Color Kit Number	Via Number	Luminous Intensity (mcd)		Dominant Wavelength			
	Kit Nullibei	Min.	Max.	Color Bin	Min. (nm)	Color Bin	Max. (nm)
Amber	CLP6C-AKW-CYbB0AA3	3550	9000	AA	584	AA	596
Amber	CLP6C-AKW-CZ0B0AA3	4500	9000	AA	584	AA	596

Notes:

- The above kit numbers represent order codes that include multiple intensity-bin and color-bin codes. Only one intensity-bin code and one color-bin code will be shipped on each bulk. Single intensity-bin code and single color-bin codes will not be orderable.
- · Please refer to the HB LED Lamp Reliability Test Standards document for reliability test conditions.
- Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.



GRAPHS

The data below are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.




FIG.1 FORWARD CURRENT VS. FORWARD VOLTAGE.




FIG.3 RED &YELLOW REVERSE CURRENT VS. REVERSE VOLTAGE.




FIG.5 RED &YELLOW MAXIMUM FORWARD DCCURRENT VS AMBIENT TEMPERATURE (Tjmax=110°C)




FIG.2 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




FIG.4 RELATIVE LUMINOUS INTENSITY VS. WAVELENGTH.





FIG.6 FAR FIELD PATTERN



MECHANICAL DIMENSIONS

All dimensions are in mm.



NOTES

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree LED representative or from the Product Ecology section of the Cree LED website.

Vision Advisory


WARNING: Do not look at an exposed lamp in operation. Eye injury can result.



KIT NUMBER SYSTEM

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options.


Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:






REFLOW SOLDERING


- The CLP6C-RKW/AKW is rated as a MSL 5a product.
- · The recommended floor life out of bag is 24hrs.
- · The temperature profile is as below.



Use only with CLP6C-RKW/AKW



- The packaging sizes of these SMD products are very small and the resin is still soft after solidification. Users are required to handle with care. Never touch the resin surface of SMD products.
- To avoid damaging the product's surface and interior device, it is recommended to choose a special nozzle to pick up the SMD
 products during the process of SMT production. If handling is necessary, take special care when picking up these products. The
 following method is necessary:
- Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.





PACKAGING

- · The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- · Cardboard boxes will be used to protect the LEDs from mechanical shock during transportation.
- The boxes are not water resistant, and they must be kept away from water and moisture.
- The reel pack is applied in SMD LED.
- Max 900 pcs per reel.

