

SANYO	No.2001A	2SA1471/2SC3748
		PNP/NPN Epitaxial Planar Silicon Transistors 60V/10A High-Speed Switching Applications

Applications

- . Car-use inductance drivers, lamp drivers
- . Inverters drivers, converters (strobos, flashes, FLT lighting circuits)
- . Power amplifiers (high-power car stereos, motor control)
- . High-speed switching (switching regulators, drivers)

Features

- . Low saturation voltage
- . Excellent dependence of h_{FE} on current
- . Fast switching speed
- . Micaless package facilitating mounting

():2SA1471

Absolute Maximum Ratings at Ta=25°C


			unit
Collector-to-Base Voltage	V_{CB0}	(-)80	V
Collector-to-Emitter Voltage	V_{CEO}	(-)60	V
Emitter-to-Base Voltage	V_{EBO}	(-)5	V
Collector Current	I_C	(-)10	A
Collector Current (Pulse)	I_{CP}	(-)12	A
Collector Dissipation	P_C	2	W
		$T_c=25^\circ C$	30
Junction Temperature	T_j	150	°C
Storage Temperature	T_{stg}	-55 to 150	°C

Electrical Characteristics at Ta=25°C

			min	typ	max	unit
Collector Cutoff Current	I_{CBO}	$V_{CB}=(-)40V, I_E=0$			(-)0.1	mA
Emitter Cutoff Current	I_{EBO}	$V_{EB}=(-)4V, I_C=0$			(-)0.1	mA
DC Current Gain	h_{FE}	$V_{CE}=(-)2V, I_C=(-)1A$	70*		280*	
Gain Bandwidth Product	f_T	$V_{CE}=(-)5V, I_C=(-)1A$		100		MHz
Collector-to-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C=(-)5A, I_B=(-)0.25A$			(-)0.4	V

Continued on next page.

Package Dimensions 2041
(unit:mm)




Continued from preceding page.

			min	typ	max	unit
Collector-to-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = (-) 1mA, I_E = 0$	(-)80			V
Collector-to-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = (-) 1mA, R_{BE} = \infty$	(-)60			V
Emitter-to-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = (-) 1mA, I_C = 0$	(-)5			V
Turn-ON Time	t_{on}	See specified Test Circuit.	0.1			μs
Storage Time	t_{stg}	"	0.5			μs
Fall Time	t_f	"	0.1			μs

*:The 2SA1471/2SC3748 are classified by 1A h_{FE} as follows:





70	Q	140	100	R	200	140	S	280
----	---	-----	-----	---	-----	-----	---	-----








Switching Time Test Circuit



$20I_{b1} = -20I_{b2} = I_C = 5A$

Unit (resistance: Ω , capacitance: F)





- No products described or contained herein are intended for use in surgical implants, life-support systems, aerospace equipment, nuclear power control systems, vehicles, disaster/crime-prevention equipment and the like, the failure of which may directly or indirectly cause injury, death or property loss.
- Anyone purchasing any products described or contained herein for an above-mentioned use shall:
 - ① Accept full responsibility and indemnify and defend SANYO ELECTRIC CO., LTD., its affiliates, subsidiaries and distributors and all their officers and employees, jointly and severally, against any and all claims and litigation and all damages, cost and expenses associated with such use:
 - ② Not impose any responsibility for any fault or negligence which may be cited in any such claim or litigation on SANYO ELECTRIC CO., LTD., its affiliates, subsidiaries and distributors or any of their officers and employees jointly or severally.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. SANYO believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.