

承 认书 DATA SHEET

Customer name	:		
BERYL SERIES	:	KN	TYPE : Snap-in
DESCRIPTION	:	4700uF/100V Φ30*50	
Apply date	:	2023-09-15	

BERYL			CUSTOMER	
P/N:KN100M472SI230*50TA-11	P/N:			
PREPARED	APPROVAL	PREPARED	CHECKED	APPROVAL
董桂茹	张业维			

After approved, please sign back 1 Approval Sheet before order. If not, we will treat it as tacitly acknowledged and accepted our relative standard and technical index.

Zhao Qing Beryl Electronic Technology Co., Ltd.

TEL: (0758) 2862871 FAX: (0758) 2862870

E-mail: master@zq-beryl.com http://www.zq-beryl.com

NO.8 DUANZHOU ROAD, ZHAOQING CITY. GUANGDONG. CHINA

Sheet No.: 20230915A Page : 1/13



Revise record

NO.	Date	Revise reason	Revise content	Prepared
01	2023.09.15	First issue	First issue	董桂茹

Sheet No.: 20230915A Page : 2 / 13



1, Application

This specification applies to Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC 60384.


2. Table of specification and characteristics

Series	Cap(uF)	WV(V)	Size(mm)		Size(mm)		/ 1		Temperature		Capacitance	Life(hours)	
	120Hz/20°C	,	D	L	(°C)	Tolerance		@105(°C)					
KN	4700	100	30	50	-40~ +1	05	±20%	5000					
,	%)(MAX) Hz/20°C	LC(μA)(5min/2		1	Ω)(MAX) KHz/25°C	1	RC (A rms) X)105℃/120Hz	Surge voltage(V)					
	≤21	≤20:	57		-		3.52	115					

Other: /

3. Product Dimensions


Type S(Ф22~Ф35)




Sheet No.: 20230915A Page : 3 / 13



4. Part Number



5, Construction



Material name	Composition	Supplier name
1.Terminal	Copper, tin	ZXH、XH
2.Seal	Bakelite, phenolic, etc.	ZXH、TY、XH、QK
3.Washer	Aluminum, 99.9%	ZXH、TY、XH
4.Tab	Aluminum, 99.9%	JY
5.Sleeve	PET	YL、DS
6. Case	Aluminum, 99.8%	OX、YJ、LY2
7.Element	Aluminum foils, separator, electrolyte, etc.	
7-1.Anode foil	Formed aluminum, 99.99% or 99.98%	HX1、GD、FC、ZH、 HF
7-2.Cathode foil	Etched aluminum, 99.7% or 99.4%	GY、FL、TL
7-3.Separat or	fiber paper	KE、CY、NKK、JLT
7-4.Electrol yte	Ethylene glycol,Ammonium salt,etc.	XZB、JZ2
8.Gasket	PVC/PP/PET	ZXH、XH
9.Adhesive tape	propylene , butyl acrylate	RK、CW


Sheet No.: 20230915A Page: 4/13

BERYL 绿宝石

ALUMINUM ELECTROLYTIC CAPACITORS

6. Product Marking

Marking Sample:



Marking Details:

Capacitor shall be marked the following items:

- 1) Trademark (BERYL)
- 2) working voltage(100V)
- 3) Nominal capacitance(4700uF)
- 4) Cathode marked
- 5) Series symbol & Nominal capacitance tolerance (M: -20% ~ +20%)
- 6) Sleeve material(E: PET)

Maximum operating temperature(105°C)

- 7) Date code (2314)
 - 23: Manufactured year 2023

Code	19	20	21	22	23	24	25	26	
Year	2019	2020	2021	2022	2023	2024	2025	2026	

14: Manufactured week (01, 02, 03, 04......52, 53)

Sheet No.: 20230915A Page : 5 / 13



7. Characteristics

Standard atmospheric conditions

Unless other specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : 15°C to 35°C
Relative humidity : 45% to 85%
Air pressure : 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature : $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ Relative humidity : 60% to 70%Air pressure : 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage is (6.3~100WV) -40°C to +105°C . (160~500WV) -25°C to +105°C

Table

	ITEM	PERFORMANCE
1	Nominal capacitance (Tolerance)	Condition> Measuring Frequency: 120Hz±12Hz Measuring circuit:Series equivalent circuit Measuring Voltage: Not more than 0.5Vrms +1.5~2.0V.DC Measuring Temperature: 20±2°C Criteria> Shall be within the specified capacitance tolerance.
2	Leakage current	$ \begin{array}{c} \textbf{} \\ \textbf{Connecting the capacitor with a protective resistor } (1k\Omega\pm10\Omega) \text{ in series for} \\ \textbf{5 minutes, and then, measure leakage current.} \\ \textbf{} \\ \textbf{I: Leakage current (uA)} \\ \textbf{I (uA)} \leqslant 3\sqrt{CV} \text{ (uA) }, \\ \textbf{measurement circuit refer to right drawing.} \\ \textbf{C: Capacitance } (\mu F) \\ \textbf{V: Rated DC working voltage } (V) \\ \end{array} $
3	Dissipation factor	<condition> Nominal capacitance, for measuring frequency, voltage and temperature. <criteria> Must be within the parameters (See page 3)</criteria></condition>

Sheet No.: 20230915A Page : 6 / 13



	ITEM			PER	FORM	IANCE			
4	Impedance	Condition> Measuring frequency:100kHz; Measuring temperature:20±2°C Measuring point: 2mm max. from the surface of a sealing rubber on the lead wire. Criteria> (20°C) Must be within the parameters (See page 3)							vire.
5	Load life test	Condition> According to IEC6038 Maximum operating to current for Rated life + exceed the rated work recovering time at atm Criteria> The characteristic shal Leakage current Capacitance Change Dissipation Factor Appearance	emperature 48/0hours ing voltag nospheric I meet the Not With	e ±2°C vs. (The sege) Then condition to following more than ±20% more than the segent to the segent	with DC sum of the prons. The ng requirement the so of initian 200%	bias vol DC and duct sho result sho irements pecified al value of the sp	tage plus ripple pea uld be tes nould mea value.	the rated rip ak voltage sh sted after 16 et the followi	ple all not hours
6	Shelf life test	<condition> The capacitors are then temperature±2°C for from the test chamb leakage current <criteria> The characteristic shall range current Capacitance Change Dissipation Factor Appearance</criteria></condition>	r1000+48, er and be meet the for Not me Within	ollowing ore than ore than	Follow to stabilized requires 200% of initia 150% of the stabilized requires 200% of the stabi	ements. If the specific the spe	period, th	ne capacitors perature for	shall be removed
7	Maximum permissible (ripple current, temperature coefficient)	Condition> The maximum permissi applied at maximum op Table-3 The combined value of voltage and shall not result frequency Multipliers: Freq (Hz) Rated Voltage(V) 100 Temperature Coefficient Temperature (Factor	D.C volta D.C volta verse volta 50 0.92	mperatur	re	1k 1.13			

Sheet No.: 20230915A Page: 7 / 13



	ITEM				PER	FORMAN	CE			
8	Terminal strength	Condition> Tensile strength of terminals Fixed the capacitor, applied force to the terminal in lead out direction for 30+ seconds. Bending strength of terminals. Fixed the capacitor, applied force to bent the terminal (1~4 mm from the rule 2~3 seconds, and then bent it for 90° to its original position within 2~3 seconds. Diameter of lead wire				obber) ids.	for 90° within			
9	Temperature characteristics	Criteria> a. At +105 Dissipat The leal b. In step 5 Dissipat The leal 	20 10: 20	0±3 0±2 5±2 0±2 1 pedano e meas 1 be wireasurece measur 1 be wirall not Z) ratio 25	ce shall b ured at +: thin the lid d shall no red at +20 thin the lid more tha	Time to re Time to re Time to re Time to re e measured 20°C shall be mit of Item t more than °C shall be mit of Item n the specifit	be within ± 25 7.3 10 times of i within $\pm 10\%$ 7.3 ied value.	equilibrium equilibrium equilibrium % of its or of its original following	iginal I valu	alue.
10	Surge test	series for 30± 1000 times. T before measur CR: Nomina <criteria> Leakage or Capacitand Dissipation Appearanc Attention: This test si</criteria>	al Capacitance arrent be Change n Factor	Very 5± tors sha (μF) N V N T	Not more vithin ±1. Not more vithin ±1. Not more vithere shal	than the spe chan the spe 5% of initia than the spe 1 be no leak	cified value. l value. cified value. cified value. age of electro	e shall be r for 1-2 hou	epeat	ed

Sheet No.: 20230915A Page: 8 / 13



	ITEM		PERFORMA	NCE					
		<condition> Temperature cycle: According to IEC60384-4 Naccording as below:</condition>	Temperature cycle: According to IEC60384-4 No.4.7 methods, capacitor shall be placed in an oven,						
		Ter	mperature	Time					
		(1) +20°C		3 Minutes					
	Change of	(2) Rated low temperat	ure (-40°C)(-25°C)	30±2 Minutes					
11	temperature test	(3) Rated high tempera	ture (+105°C)	30±2 Minutes					
		(1) to (3) =1 cycle, total	l 5 cycle						
		Criteria> The characteristic shall meet Leakage current	the following requirem Not more than the						
		Dissipation Factor	Not more than the	specified value.					
		Appearance	There shall be no le	leakage of electrolyte.					
12	Damp heat test	According to IEC60384-4 No be exposed for 500±8 hours in 40±2°C, the characteristic chest	n an atmosphere of 90- ange shall meet the foll Not more than the spe Within ±10% of initia	ecified value. al value. of the specified value.					
13	Solderability test	Dipping depth : 2r Dipping speed : 25	25 ±5°C mm 5±2.5mm/s 0.5s Less than 3s	nditions: % of the surface being					

Sheet No.: 20230915A Page: 9 / 13



	ITEM	PERFORMANCE
14	Vibration test	Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range: 10Hz ~ 55Hz each to peak amplitude: 1.5mm Sweep rate: 10Hz ~ 55Hz ~ 10Hz in about 1 minute Mounting method: The capacitor with diameter greater than 12.5mm or longer than 25mm must be fixed in place with a bracket. Within 30°
		<pre> </pre> <pre> </pre> <pre> To be soldered</pre>
		After the test, the following items shall be tested:
		Inner construction No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.
		Appearance No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.
	Resistance	Condition> Terminals of the capacitor shall be immersed into solder bath at 260±5°Cfor10±1seconds or400±10°Cfor3 ⁻⁰ seconds to 1.5~2.0 mm from the body of capacitor. Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement. Criteria>
15	to solder heat	Leakage current Not more than the specified value.
	test	Capacitance Change Within ±5% of initial value.
		Dissipation Factor Not more than the specified value.
		Appearance There shall be no leakage of electrolyte.
16	Vent	Condition> The following test only apply to those products with vent products at diameter ≥∅6.3 with vent. D.C. test The capacitor is connected with its polarity reversed to a DC power source. Then a current selected from Table 2 is applied. Table 2>
10	test	Diameter (mm) DC Current (A)
		22.4 or less 1
		<criteria> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case.</criteria>

Sheet No.: 20230915A Page : 10 / 13




8. Packing Information

Packing Label Marked (the following items shall be marked on the label) (Inside box or bag)

(1)Clint order number (2)Client part number (3)Beryl part number (4)Capacitance (5)Voltage (6)Dimension (7)Packaging quantity (8)Capacitance tolerance (9) QC Marking (10) Lot number (11) Series

LOT Number:



1) Bulk Packing:

		Ltd.		
C.S.R:				B HA HE
C.S.R P/C):			ROHS HE
C.S.R P/N	I:			
S.P.R P/N	l:			QC
SPEC:				
QTY:	PCS	TOL:	%	
L/N:		S.P.R:		

2) Packaging quantity:

Product size	Case/box	PCS/box
22Ф	84	840
25Ф	84	840
30 Ф *20~45	45	450
35 Ф *20~45	45	450
30 Ф *50~90	45	270
35 Ф *50~90	45	270

3) The outer box and the inner Case size



内箱



外箱

* 内盒包装要求: 牛角朝上,每内盒装完后,须放一层锡箔纸或负箔,加垫一层垫板起放 电作用

Sheet No.: 20230915A Page : 11 / 13



9. Prohibition to Use Environment- related Substances

We are hereby to certify the followings:

Our company hereby warrants and guarantees that all or part of products, including, but not limited to, the peripherals, accessories or package, delivered to your company (including your subsidiaries and affiliated companies) directly or indirectly by our company are free from any of the substances listed below.

The latest version of <Substances Prohibited as per RoHS or <Sony-SS-00259>

	Cadmium and cadmium compounds			
Accord with	Lead and lead compounds			
heavy metal	Mercury and mercury compounds			
	Hexavalent chromium compounds			
	Polychlorinated biphenyls (PCB)			
Onconio ablania	Polychlorinated naphthalenes (PCN)			
Organic chlorin compounds	Polychlorinated terphenyls (PCT)			
	Chlorinated paraffins (CP)			
	Other chlorinated organic compounds			
Organic	Polybrominated biphenyls (PBB)			
bromine	Polybrominated diphenylethers (PBDE)			
compounds	Other brominated organic compounds			
Tributyltin compounds				
Triphenyltin compounds				
Asbestos				
Specific azo compounds				
Formaldehyde				
Polyvinyl chloride (PVC) and PVC blends				
F、Cl、Br、I				
REACH				

Sheet No.: 20230915A Page : 12 / 13



Test Report

Series	KN	_ Spec.	4700uF/100V	Size(mm)	30*50
Cap tolerance	±20%	Work _ temperature	105°C	Color of Tube	black
Test date	2023-09-07	Test humidity	61%	Test temperature	25.5℃

Items	Cap (µF)	D.F (%)	L.C (μA)	ESR (Ω)	Appearance		
SPEC NO.	3760~5640 (120Hz)	≤21 (120Hz)	≤2057 (5min)	≤/ (100KHz)	No abnormalities		
1	4110	4.55	51	/	ОК		
2	4079	4.60	42	/	ОК		
3	4099	4.67	49	/	ОК		
4	4117	4.50	47	/	ОК		
5	4096	4.57	43	/	ОК		
6	4160	4.74	48	/	ОК		
Opinion	After 5 minutes application of rated voltage						
Approve: 廖梅君 A		Audit: 董桂	Audit:董桂茹		Test: 赵凯群		

Sheet No.: 20230915A Page : 13 / 13