3A/4A BSI Series







Ultra High Efficiency (90-95%), Minimum Size Step-Down DC-DC Converter

Input: +5V. +12V Input: +6V. +12V. +15V Output: +3.3V (+1.8V to +3.3V) Output: +5.0V (+3.0V to +5.0V)

- Input Voltage Range 4.75V-16.5V
- Output Voltage Range 1.8V-5V
- Latest Technology, Synchronous Rectification Circuit
- Efficiency 90% to 95%
- Adjustable Output Voltage
- Non-Isolated Type Converter
- Short Circuit, Over-Current Protection
- No Electrolytic Capacitor used No Tantalum Capacitor used
- Heat Sink Not Required
- Minimum Size
- Remote ON/OFF Control
- Low Standby Current 100µA (3A output type product)
- MTBF 1,000,000Hrs
- Operating Temp Range -10°C to +70°C

(Temp Derating required)

- High Reliability, High Performance
- RoHS Compliance

- Note!

data sheets

١	Models	Input V	Output V	Output I	Line Reg	Load Reg	Ripple/Noise	Efficiency
l	BSI Series	Vdc	Vdc	Α	%(typ.)	%(typ.)	mVpp(typ.)	%(typ.)
;[BSI-3.3S3R0A	6.0-16.5	3.3	0-3	0.2	0.3	50	91
L	BSI-3.3S3R0FA		(1.8-3.3)					
I	BSI-5.0S3R0A		5.0		0.2	0.2		95
ĺ	BSI-5.0S3R0FA		(3.0-5.0)					


Note 1: The output voltage inside the () indicates the adjustable range.


Note 2: External capacitors are required.

Note 3: Suffix "A" stands for version.

(DIP type) <Outline> (SIP type)

BSI-3.3S3R0A (t=8.8typ.) BSI-3.3S3R0FA (h=9.3typ.) **BSI-5.0S3R0A** (t=8.8typ.) BSI-5.0S3R0FA (h=9.3typ.)






NC

<Standard Connection Diagram>

When designing, be sure to refer to the



- External Capacitors (SH, FA type OS-CON Recommended)
- 3.3V, 5V Output Product

C1=100µF20WVx2pcs or more

C2=220µF10WV×1pcs or more

- ON/OFF Control

ON/OFF control is controlled by opening and shortening between 5pin(ON/OFF) and 3, 4pin (-Vin).

- Adjustable Output Voltage

The output voltage is adjusted by connecting a resistor between 14pin (V.ADJ) and 17, 18pin (+Vout).

When 14pin is open, the rated output voltage is as follows:

 $BSI-3.3S = +3.3V \pm 5\%$

 $BSI-5.0S = +5.0V \pm 5\%$

Open = 2.5V,3.3V,5V - A voltage difference of 0.6V or more between the Input/ Output is required for output current 4A type.