

Model ADP2430SBFRTM

Spring Base Radio Communication Antenna

Key Features



Dipole Element Design



Spring base design to reduce connector and antenna damage



Excellent mechanical integrity and electrical performance



Ruggedized construction for field durability / SB-Spring Base



ADP-ATLC Dipole Portable



2350-2500 MHz. (operating frequency)





Electrical Specifications	ADP2430SBFRTM
Frequency Range	2350-2500 MHz.
Impedance	50 ohm nominal
VSWR	<2.0:1
Gain	<2.5 dBi
Polarization	Vertical

Mechanical Specifications	ADP2430SBFRTM
Connector Style	TNC male
Material	Brass, Polyolefin Adhesive Lined
Operation Temp.	-20c to +65c
Storage Temp.	-30c to +75c