

45.7±0.5 17.7 8.5 6.1 56.2±0.5 Ø43.5 Ø40.1 Ø42.3

NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

THREADED INSERT: STAINLESS STEEL

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); STANDARD DIA. WIRE SEAL SEALED PANEL MOUNT


3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
- 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);

IP69K(MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-23S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6. RECEPTACLE IS SUPPLIED WITH DUST CAP (NOT SHOW)



RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



			TYPICAL WIRE		
SIZE	O.D.	O.D.	RANGE	RATING	
16	2.54 mm (.100 in)	3.40 mm (.134 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS	

BACKSHELL RING ADAPTER
-GREEN

	AHDP02-2	4-23PN-BRA							
	PART NUMBER		DESCRIPTION				ITEM		
QUANTITY		ı	MAT	ERI	٩LS	3 LI	ST		'
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		SIGNATURES DRAWN: MILO		DATE	- Amnnenni				
				01/APR/22					
2 PL DEC ±0.15 3 PL DEC ±0.08	PL DEC ±0.15 Angles ±1°		SULLEN	02/APR/22	Sine Systems - www.amphenol-sine.com				
a) Note reference = \(\times \) MATERIAL SPECIFICATIONS: WEIGHT: 60.2g PROCESS SPECIFICATIONS: NEXT ASS'Y:		ENGINEER:			44724 Morley Drive				
		APPROVAL:	TOMMY	06/APR/22	Clinton Township, MI 48036				
		CUSTOMER:			23 POS, RECEPTACLE, PIN, PANELMATE AHDP SIZE 24, NORMAL SEAL, BRA				
		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL							
					B	C-	AHDP02-24-2	3PN-BRA	A1
		MANUFACTURING VARIATIONS.		SCALE: N	IONE	DURAMATE	SHEET 1 O	F 1	