
# EVERLIGHT

# DATASHEET

# 4 PIN MINI FLAT PACKAGE SOLID STATE RELAY ELM406A-G Series Datasheet



#### Features

- Compliance Halogen Free(Br < 900ppm, Cl < 900ppm, Br+Cl < 1500ppm)
- Normally open signal pole signal throw relay
- Small 4pin SOP package in the 60 V load voltage series
- Lower operation current
- · Low-level off state leakage current
- Low on resistance
- Compliance with EU REACH
- Pb free and RoHS compliant
- UL and cUL (approved)
- VDE (approved)
- SEMKO (approved)
- NEMKO (approved)
- FIMKO (approved)
- CQC (approved)


#### Description

The ELM406A-G is solid state relays containing an AlGaAs infrared LEDs on the light emitting side (input side) optically coupled to a high voltage output detector circuit. The detector consists of a photovoltaic diode array and MOSFETs on the output side. The single channel configuration is equivalent to 1 form A. The devices in a 4-pin small outline SMD package

## Applications

- Exchange equipment
- Measurement and testing equipment
- FA/OA equipment
- Industrial controls
- Security

#### <u>Schematic</u>



Pin Configuration 1,LED Anode 2.LED Cathode 3.4, MOSFET

## Absolute Maximum Ratings (T<sub>A</sub>=25 °C, unless otherwise specified)

	Parameter	Symbol	Rating	Unit
Input	Forward Current	lF	50	mA
	Reverse Voltage	VR	5	V
	Peak Forward Current*1	IFP	1	А
	Power Dissipation	Pin	75	mW
Output	Break Down Voltage*2	VL	60	V
	Continuous Load	۱L		mA
	Current*2	IL	550	IIIA
	Pulse Load Current*3	I <sub>LPeak</sub>	1.2	А
	Power Dissipation	Pout	500	mW
Total Po	wer Dissipation	Ρτ	800	mW
Isolation	۲ Voltage* <sup>4</sup>	V <sub>iso</sub>	3750	Vrms
Storage	Temperature	Tstg	-40 to 125	°C
Operati	ng Temperature	T <sub>OPR</sub>	-40 to 85	٥C
Solderin	ng Temperature*5	T <sub>SOL</sub>	260	°C

#### Notes:

\*1. f =100Hz, Duty Cycle = 0.1%

\*2. Indicate the peak AC and DC values


\*3.A connection: 100ms (1 shot), V<sub>L</sub> = DC or Peak AC

\*4.AC for 1 minute, R.H. = 40 ~ 60% R.H. In this test, pins 1, 2 are shorted together, and pins 3, 4 are shorted together. \*5.For 10 seconds

## Electro-Optical Characteristics (TA=25 °C)


	Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Input	Forward Voltage	VF	I <sub>F</sub> = 10mA	-	1.18	1.5	V
	Reverse Current	I <sub>R</sub>	$V_R = 5V$	-	-	1	μA
Output	Off State leakage Current	lleak	$I_F = 0mA$ , $V_L = Max$ .	-	-	1	μA
	On Resistance	R <sub>d(ON)</sub>	$I_F = 10mA$ , $I_L = Max$ . t = 1s	-	0.7	2.5	Ω
	Output Capacitance	Cout	$V_L = 0V$ , f = 1MHz	-	85	-	pF
Transfer Characteristics	LED turn on Current	I <sub>F(on)</sub>	I∟= Max	-	2.5	5	mA
	LED turn off current	I <sub>F(off)</sub>	$I_L = 1 \ \mu A$	0.4	2.0	-	mA
	Turn On Time	T <sub>on</sub>	I⊧ = 10 mA, I∟ = MAX.		1.5	3	ms
	Turn Off Time	T <sub>off</sub>	$R_{L} = 200\Omega,$		0.15	0.5	ms
	Isolation Resistance	R <sub>I-O</sub>	V I-O = 500V DC	5×10 <sup>10</sup>	-	-	Ω
	Isolation Capacitance	CI-O	V = 0V, f = 1MHz		1.5	-	pF
E	NEF						


## **Typical Electro-Optical Characteristics Curves**




# EVERLIGHT

# **EVERLIGHT**





#### Turn on/Turn off Time



### **Order Information**

#### **Part Number**





#### Note:


- 406A = Part No.
- X = Tape and reel option (TA, TB or none)
- V = VDE (optional)
- G = Halogen free

Option	Description	Packing quantity
None	Standard SMD option	100 units per tube
-V	Standard SMD option + VDE	100 units per tube
(TA)	TA Tape & reel option	3000 units per reel
(TB)	TB Tape & reel option	3000 units per reel
(TA)-V	TA Tape & reel option + VDE	3000 units per reel
(TB)-V	TB Tape & reel option + VDE	3000 units per reel

#### Package Dimension (Dimensions in mm)










#### **Recommended Pad Layout for Surface Mount Leadform**



#### **Device Marking**




#### Notes

Т	denotes Factory
	No code : made in China
	T : made in Taiwan
EL	denotes Everlight
M406A	denotes Part Number
Y	denotes 1 digit Year code
WW	denotes 2 digit Week code
V	denotes VDE approved (optional)

**EVERLIGHT** 


# **Tape & Reel Packing Specifications**



Direction of feed from reele

Direction of feed from reele

#### **Tape dimensions**






Dimension No.	Α	В	Do	D1	Е	F
Dimension (mm)	4.4 ± 0.1	7.4 ± 0.1	1.5 + 0.1/-0	1.5 ± 0.1	1.75± 0.1	7.5 ± 0.05
Dimension No.	Ро	P1	P2	t	w	к



#### **Precautions for Use**

#### 1. Soldering Condition

1.1 (A) Maximum Body Case Temperature Profile for evaluation of Reflow Profile



Note:

#### Preheat

Temperature min (T<sub>smin</sub>) Temperature max (T<sub>smax</sub>) Time (T<sub>smin</sub> to T<sub>smax</sub>) (t<sub>s</sub>) Average ramp-up rate (T<sub>smax</sub> to T<sub>p</sub>)

#### 150 °C 200°C 60-120 seconds 3 °C/second max

Reference: IPC/JEDEC J-STD-020D

Other Liquidus Temperature (TL) Time above Liquidus Temperature (tL) Peak Temperature (TP) Time within 5 °C of Actual Peak Temperature: TP - 5°C Ramp- Down Rate from Peak Temperature Time 25°C to peak temperature Reflow times

217 °C 60-100 sec 260°C 30 s 6°C /second max. 8 minutes max. 3 times

#### DISCLAIMER

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 3. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 4. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.
- 5. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.
- 6. Statements regarding the suitability of products for certain types of applications are based on Everlight's knowledge of typical requirements that are often placed on Everlight products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Everlight's terms and conditions of purchase, including but not limited to the warranty expressed therein.