

承认书 DATA SHEET

Customer name	:			
BERYL SERIES	:	KN	TYPE :	Snap-in
DESCRIPTION	:	560uF/400V Φ35*5	50	
Apply date	:	2023-09-11		

BERYL		CUSTOMER				
P/N:KN400M561SI235*50TA-1I	P/N:					
PREPARED	APPROVAL	PREPARED	CHECKED	APPROVAL		
董桂茹						

After approved, please sign back 1 Approval Sheet before order. If not, we will treat it as tacitly acknowledged and accepted our relative standard and technical index.

Zhao Qing Beryl Electronic Technology Co., Ltd.

TEL: (0758) 2862871 FAX: (0758) 2862870

E-mail: master@zq-beryl.com http://www.zq-beryl.com

NO.8 DUANZHOU ROAD, ZHAOQING CITY. GUANGDONG. CHINA

Sheet No.: 20230911M Page : 1/13



Revise record

NO.	Date	Revise reason	Revise content	Prepared
01	2023.09.11	First issue	First issue	董桂茹

Sheet No.: 20230911M Page : 2 / 13



1, Application

This specification applies to Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC 60384.


2. Table of specification and characteristics

Series	Cap(uF)	WV(V) Size(mm) Temperature Capacitance				· -		Temperature (°C)		·			Life(hours)
	120Hz/20°C	,	D	L	(°C)		(°C)					Tolerance	
KN	560	400	35	50	-25~ +105		- 25∼ +105		-25~ +105		±20%		5000
	6)(MAX) Hz/20°C	LC(µA)(1 5min/2		`	2)(MAX) Hz/25°C	l	C (A rms))105°C/120Hz		Surge voltage(V)				
<	≤15	≤142	20		-		2.14		440				

Other: /

3. Product Dimensions


Туре S(Ф22~Ф35)




Sheet No.: 20230911M Page: 3 / 13



4. Part Number



5, Construction



Material name	Composition	Supplier name
1.Terminal	Copper, tin	ZXH、XH
2.Seal	Bakelite, phenolic, etc.	ZXH、TY、XH、QK
3.Washer	Aluminum, 99.9%	ZXH、TY、XH
4.Tab	Aluminum, 99.9%	JY
5.Sleeve	PET	YL、DS
6. Case	Aluminum, 99.8%	OX、YJ、LY2
7.Element	Aluminum foils, separator, electrolyte, etc.	
7-1.Anode foil	Formed aluminum, 99.99% or 99.98%	HX1、GD、FC、ZH、 HF
7-2.Cathode foil	Etched aluminum, 99.7% or 99.4%	GY、FL、TL
7-3.Separat or	fiber paper	KE、CY、NKK、JLT
7-4.Electrol yte Ethylene glycol,Ammonium salt,etc.		XZB、JZ2
8.Gasket	PVC/PP/PET	ZXH、XH
9.Adhesive tape	propylene , butyl acrylate	RK、CW


Sheet No.: 20230911M Page: 4/13


BERYL 绿宝石

ALUMINUM ELECTROLYTIC CAPACITORS

6. Product Marking

Marking Sample:





Marking Details:

Capacitor shall be marked the following items:

- 1) Trademark (BERYL)
- 2) working voltage(400V)
- 3) Nominal capacitance(560uF)
- 4) Cathode marked
- 5) Series symbol & Nominal capacitance tolerance (M: -20% ~ +20%)
- 6) Sleeve material(E: PET)

Maximum operating temperature(105°C)

7) Date code (2333)

23: Manufactured year 2023

Code	19	20	21	22	23	24	25	26	
Year	2019	2020	2021	2022	2023	2024	2025	2026	

33: Manufactured week (01, 02, 03, 04......52, 53)

Sheet No.: 20230911M Page: 5 / 13



7. Characteristics

Standard atmospheric conditions

Unless other specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : 15°C to 35°C
Relative humidity : 45% to 85%
Air pressure : 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature : $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ Relative humidity : 60% to 70%Air pressure : 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage is (6.3~100WV) -40°C to +105°C . (160~500WV) -25°C to +105°C

Table

	ITEM	PERFORMANCE
1	Nominal capacitance (Tolerance)	Condition> Measuring Frequency: 120Hz±12Hz Measuring circuit:Series equivalent circuit Measuring Voltage: Not more than 0.5Vrms +1.5~2.0V.DC Measuring Temperature: 20±2°C Criteria> Shall be within the specified capacitance tolerance.
2	Leakage current	$ \begin{array}{c} \textbf{} \\ \textbf{Connecting the capacitor with a protective resistor } (1k\Omega\pm10\Omega) \text{ in series for} \\ \textbf{5 minutes, and then, measure leakage current.} \\ \textbf{} \\ \textbf{I: Leakage current (uA)} \\ \textbf{I (uA)} \leqslant 3\sqrt{CV} \text{ (uA) }, \\ \textbf{measurement circuit refer to right drawing.} \\ \textbf{C: Capacitance } (\mu F) \\ \textbf{V: Rated DC working voltage } (V) \\ \end{array} $
3	Dissipation factor	<condition> Nominal capacitance, for measuring frequency, voltage and temperature. <criteria> Must be within the parameters (See page 3)</criteria></condition>

Sheet No.: 20230911M Page : 6 / 13



	ITEM			PEI	RFORM	1ANCE			
4	Impedance	Measuring point: 2mi < Criteria >	Measuring frequency:100kHz; Measuring temperature:20±2°C Measuring point: 2mm max. from the surface of a sealing rubber on the lead wire.						
5	Load life test	Condition> According to IEC60384-4No. 4.13 methods, the capacitor is stored at a temperature of Maximum operating temperature ±2°C with DC bias voltage plus the rated ripple current for Rated life +48/0hours. (The sum of DC and ripple peak voltage shall not exceed the rated working voltage) Then the product should be tested after 16 hours recovering time at atmospheric conditions. The result should meet the following table: *Criteria> The characteristic shall meet the following requirements. Leakage current Not more than the specified value. Capacitance Change Within ±20% of initial value. Dissipation Factor Not more than 200%of the specified value. Appearance There shall be no leakage of electrolyte. *Condition>							
6	Shelf life test	The capacitors are ther temperature±2°C for from the test chamble leakage current <criteria> The characteristic shall Leakage current Capacitance Change Dissipation Factor Appearance</criteria>	meet the Not With	48/0 hours be allowed	requires 200% of initial 150% of the stable	ements. of the sport value. of the sport value.	s period, the room tem	he capacitors nperature for lue.	shall be removed
7	Maximum permissible (ripple current, temperature coefficient)	Condition> The maximum permissible ripple current is the maximum A.C current at 120Hz and can be applied at maximum operating temperature Table-3 The combined value of D.C voltage and the peak A.C voltage shall not exceed the rated voltage and shall not reverse voltage. Frequency Multipliers: Freq (Hz) Rated 50 120 300 1k 10k 50~100k Voltage(V) 400 0.77 1.00 1.16 1.30 1.41 1.43 Temperature Coefficient: Temperature (°C) 60 85 95 105 Factor 2.23 1.70 1.41 1.00							

Sheet No.: 20230911M Page: 7 / 13



	ITEM			PERFORMANCE					
8	Terminal strength	seconds. If Fixed the 6 2~3 seconds. Diam O.: Criteria>	Tensi Tensi 5	the termin its original ple force N (kgf) (0.51) (1.02)	lead out direction to al (1~4 mm from to position within 2~3 Bending force No.25 (0.25) 5 (0.51) or looseness at the	he rubber) seconds.	for 90° within		
9	Temperature characteristics	Criteria> a. At +105 Dissipar The lead b. In step 5 Dissipar The lead 	·	ance shall easured at - within the red shall n sured at +2 within the ot more th	Time to r	be within $\pm 25\%$ of a 7.3 a 10 times of its special within $\pm 10\%$ of it a 7.3 fied value. e value of the following in 100 and 160~250	ibrium ibrium ibrium its original ecified valu s original v	e. alue.	
10	Surge test	series for 30± 1000 times. T before measu CR: Nomin <criteria> Leakage cr Capacitance Dissipation Appearance Attention: This test si</criteria>	al Capacitance (μF) urrent ce Change n Factor	Not more Within ± Not more There sha	than the special than the special be no lead	5°C.Procedure sha nal humidity for 1- ecified value. al value. ecified value. ecage of electrolyte.	all be repeat	ed	

Sheet No.: 20230911M Page: 8 / 13



	ITEM	PERFORMANCE						
		<condition> Temperature cycle: According to IEC60384-4 Naccording as below:</condition>	Io.4.7 methods, capacito	r shall be placed in an oven, the condition				
		Te	emperature	Time				
		(1) +20°C		3 Minutes				
	Change of	(2) Rated low tempera	ture (-25°C)	30±2 Minutes				
11	temperature test	(3) Rated high tempera	ature (+105°C)	30±2 Minutes				
		(1) to $(3) = 1$ cycle, total	al 5 cycle					
		Criteria> The characteristic shall meet Leakage current	t the following requirement Not more than the s					
		Dissipation Factor	Not more than the s	specified value.				
		Appearance	There shall be no le	eakage of electrolyte.				
12	Damp heat test	Humidity test: According to IEC60384-4 N be exposed for 500±8 hours 40±2°C, the characteristic ch <criteria> Leakage current Capacitance Change Dissipation Factor Appearance</criteria>	95%R H .at					
13	Solderability test	Soldering temperature : 2- Dipping depth : 2 Dipping speed : 2 Dipping time : 3- <criteria></criteria>	pacitor shall be tested under the following conditions: ng temperature : 245 ±5°C g depth : 2mm g speed : 25±2.5mm/s g time : 3±0.5s Oldering wetting time Less than 3s					

Sheet No.: 20230911M Page : 9 / 13



	ITEM	PERFORMANCE
14	Vibration test	Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range: 10Hz ~ 55Hz each to peak amplitude: 1.5mm Sweep rate: 10Hz ~ 55Hz ~ 10Hz in about 1 minute Mounting method: The capacitor with diameter greater than 12.5mm or longer than 25mm must be fixed in place with a bracket. Within 30°
		<pre> </pre> <pre> </pre> <pre> To be soldered</pre>
		After the test, the following items shall be tested:
		Inner construction No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.
		Appearance No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.
	Resistance	Condition> Terminals of the capacitor shall be immersed into solder bath at 260±5°Cfor10±1seconds or400±10°Cfor3 ⁻⁰ seconds to 1.5~2.0 mm from the body of capacitor. Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement. Criteria>
15	to solder heat	Leakage current Not more than the specified value.
	test	Capacitance Change Within ±5% of initial value.
		Dissipation Factor Not more than the specified value.
		Appearance There shall be no leakage of electrolyte.
16	Vent	Condition> The following test only apply to those products with vent products at diameter ≥∅6.3 with vent. D.C. test The capacitor is connected with its polarity reversed to a DC power source. Then a current selected from Table 2 is applied. Table 2>
10	test	Diameter (mm) DC Current (A)
		22.4 or less 1
		<criteria> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case.</criteria>

Sheet No.: 20230911M Page: 10 / 13




8. Packing Information

Packing Label Marked (the following items shall be marked on the label) (Inside box or bag)

(1)Clint order number (2)Client part number (3)Beryl part number (4)Capacitance (5)Voltage (6)Dimension (7)Packaging quantity (8)Capacitance tolerance (9) QC Marking (10) Lot number (11) Series

LOT Number:



1) Bulk Packing:

BERYL	Zhao Qin	g Beryl Ele Ltd.	ctronic	Technology Co.,
C.S.R:				- 110 115
C.S.R P/C):			ROHS HE
C.S.R P/N	l:			
S.P.R P/N	l:			QC
SPEC:				
QTY:	PCS	TOL:	%	
L/N:		S.P.R:		8

2) Packaging quantity:

Product size	Case/box	PCS/box
22Ф	84	840
25Ф	84	840
30 Ф *20~45	45	450
35 Ф *20~45	45	450
30 Ф *50~90	45	270
35 Ф *50~90	45	270

3) The outer box and the inner Case size



内箱



* 内盒包装要求: 牛角朝上,每内盒装完后,须放一层锡箔纸或负箔,加垫一层垫板起放电作用

Sheet No.: 20230911M Page: 11 / 13



9. Prohibition to Use Environment- related Substances

We are hereby to certify the followings:

Our company hereby warrants and guarantees that all or part of products, including, but not limited to, the peripherals, accessories or package, delivered to your company (including your subsidiaries and affiliated companies) directly or indirectly by our company are free from any of the substances listed below.

The latest version of <Substances Prohibited as per RoHS or <Sony-SS-00259>

	Cadmium and cadmium compounds			
Accord with	Lead and lead compounds			
heavy metal	Mercury and mercury compounds			
	Hexavalent chromium compounds			
Organic chlorin compounds	Polychlorinated biphenyls (PCB)			
	Polychlorinated naphthalenes (PCN)			
	Polychlorinated terphenyls (PCT)			
	Chlorinated paraffins (CP)			
	Other chlorinated organic compounds			
Organic	Polybrominated biphenyls (PBB)			
bromine	Polybrominated diphenylethers (PBDE)			
compounds	Other brominated organic compounds			
Tributyltin compounds				
Triphenyltin compounds				
Asbestos				
Specific azo compounds				
Formaldehyde				
Polyvinyl chloride (PVC) and PVC blends				
F、Cl、Br、I				
REACH				

Sheet No.: 20230911M Page: 12 / 13



Test Report

Series	KN	_ Spec.	560uF/400V	Size(mm) _	35*50
Cap tolerance _	±20%	Work temperature	105℃	Color of Tube	black
Test date	2023-09-02	Test humidity	56%	Test temperature	25.2°C

Items	Cap (μF)	D.F (%)	L.C (μA)	ESR (Ω)	Appearance
NO. SPEC	448~672 (120Hz)	≤15 (120Hz)	≤1420 (5min)	≤/ (100KHz)	No abnormalities
1	510.9	5.91	52	/	ОК
2	508.2	5.74	49	/	ОК
3	503.9	5.56	59	/	ОК
4	499.9	5.80	57	/	ОК
5	505.6	5.42	52	/	ОК
6	503.7	5.93	50	/	ОК
7	503.8	6.01	48	/	ОК
8	508.8	5.84	58	/	ОК
9	508.0	5.78	48	/	ОК
10	504.3	6.04	56	/	ОК
Opinion	After 5 minutes	application of rate	ed voltage		
Approve: 廖梅君 A		Audit: 董相	Audit:董桂茹		

Sheet No.: 20230911M Page: 13 / 13