



Spec No.: DS30-2001-367Effective Date: 11/01/2001

Revision: -

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

Property of Lite-on Only

FEATURES

- *0.4-INCH (10.0-mm) DIGIT HEIGHT.
- *CONTINUOUS UNIFORM SEGMENTS.
- *LOW POWER REQUIREMENT.
- *EXCELLENT CHARACTERS APPEARANCE.
- *HIGH BRIGHTNESS & HIGH CONTRAST.
- *WIDE VIEWING ANGLE.
- *** SOLID STATE RELIABILITY.**
- *CATEGORIZED FOR LUMINOUS INTENSITY.

DESCRIPTION

The LTS-4301JG is a 0.4-inch (10.0-mm) height single digit seven-segment display. This device utilizes AlInGaP Green LED chips, which are made from AlInGaP on a non-transparent GaAs substrate, and has a gray face and white segments.


DEVICE

| PART NO. | DESCRIPTION | | |
|---------------|------------------|--|--|
| AlInGaP Green | Common Cathode | | |
| LTS-4301JG | Rt. Hand Decimal | | |

PART NO.:LTS-4301JG PAGE: 1 of 5


Property of Lite-on Only

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25mm(0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



of 5 PART NO.:LTS-4301JG PAGE: 2

Property of Lite-on Only

PIN CONNECTION

| No | CONNECTION |
|----|----------------|
| 1 | ANODE G |
| 2 | ANODE F |
| 3 | COMMON CATHODE |
| 4 | ANODE E |
| 5 | ANODE D |
| 6 | ANODE D.P. |
| 7 | ANODE C |
| 8 | COMMON CATHODE |
| 9 | ANODE B |
| 10 | ANODE A |

PAGE: 3 of 5 PART NO.:LTS-4301JG

Property of Lite-on Only

ABSOLUTE MAXIMUM RATING AT Ta=25°C

| PARAMETER | MAXIMUM RATING | UNIT | | | | |
|---|----------------|-------|--|--|--|--|
| Power Dissipation Per Segment | 70 | mW | | | | |
| Peak Forward Current Per Segment | 40 | mA | | | | |
| (1/10 Duty Cycle, 0.1ms Pulse Width) | 60 | | | | | |
| Continuous Forward Current Per Segment | 25 | mA | | | | |
| Derating Linear From 25°C Per Segment | 0.33 | mA/°C | | | | |
| Reverse Voltage Per Segment | 5 | V | | | | |
| Operating Temperature Range | -35°C to +85°C | | | | | |
| Storage Temperature Range | -35°C to +85°C | | | | | |
| Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at 260°C | | | | | | |

ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C


| PARAMETER | SYMBOL | MIN. | TYP. | MAX. | UNIT | TEST CONDITION |
|-----------------------------------|------------------|------|------|------|------|----------------------|
| Average Luminous Intensity | Iv | 320 | 850 | | μcd | I _F =1mA |
| Peak Emission Wavelength | λр | | 571 | | nm | I _F =20mA |
| Spectral Line Half-Width | Δλ | | 15 | | nm | I _F =20mA |
| Dominant Wavelength | λd | | 572 | | nm | I _F =20mA |
| Forward Voltage. Per Segment | V_{F} | | 2.05 | 2.6 | V | I _F =20mA |
| Reverse Current, Per Segment | I_R | | | 100 | μΑ | V _R =5V |
| Luminous Intensity Matching Ratio | Iv-m | | | 2:1 | | I _F =1mA |

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclariage) eye-response curve.

PART NO.:LTS-4301JG PAGE: 4 of 5

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)



Wavelength (\(\lambda\right)\)-nm.
Fig1. RELATIVE INTENSITY VS. WAVELENGTH







Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT





NOTE: JG=AlInGaP Green



VS. FORWARD CURRENT




Fig6. MAX. PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

PART NO.:LTS-4301JG PAGE: 5 5 of