Double-Balanced Mixer 8 - 43 GHz



MAMX-011036

Rev. V4

Features

Low Conversion Loss: 8.5 dBHigh Linearity: 20 dBm IIP3

Wide IF Bandwidth: DC to 10 GHz

High Isolation

Lead-Free 3 mm 12-lead AQFN package

RoHS* Compliant

Applications

Test & Measurement

Microwave Radio & Radar

Description

MAMX-011036 is a double-balanced passive diode mixer housed in a 3 mm, 12-lead AQFN package. The mixer offers low conversion loss, high linearity and a wide IF bandwidth. The double-balanced circuit configuration provides excellent port isolation while internal 50 Ω matching simplifies its application.

This mixer is well suited for applications such as test and measurement, microwave radio and radar.


MAMX-011036 is also available in die form. Refer to datasheet MAMX-011036-DIE.

Ordering Information^{1,2}

Part Number	Package
MAMX-011036	Bulk
MAMX-011036-TR0100	100 Piece Reel
MAMX-011036-TR0500	500 Piece Reel
MAMX-011036-SB1	Sample Board

- 1. Reference Application Note M513 for reel size information.
- 2. All sample boards include 5 loose parts.

Functional Schematic



Pin Configuration³

Pin #	Function		
1, 3, 4, 6, 7, 9	Ground		
2	LO		
5	IF		
8	RF		
10 - 12	No Connection ³		
13	Paddle ⁴		

- MACOM recommends connecting unused package pins to ground.
- The exposed pad centered on the package bottom must be connected to RF, DC and thermal ground.

^{*} Restrictions on Hazardous Substances, compliant to current RoHS EU directive.



Rev. V4

Electrical Specifications⁵: $F_{IF} = 500$ MHz, $P_{LO} = 15$ dBm, $T_A = 25$ °C, $Z_0 = 50$ Ω

Parameter	Test Conditions	Units	Min.	Тур.	Max.
LO and RF Frequency	_	GHz	8	_	43
IF Frequency	_	GHz	0	_	10
LO Power	_	dBm	_	15	_
Conversion Loss	8 - 20 GHz 20 - 34 GHz 34 - 43 GHz	dB	_	8.5 8.5 9.5	10 10.5 13
Input P1dB	_	dBm	_	13	
Input IP3	P _{RF} = -10 dBm/tone, Df = 1 MHz	dBm	_	20	_
Input IP2	P _{RF} = -10 dBm/tone, Df = 1 MHz	dBm	_	45	_
LO-to-RF Isolation	_	dB	_	40	_
LO-to-IF Isolation	8 - 20 GHz 20 - 34 GHz 34 - 43 GHz	dB	_	40 35 40	_
RF-to-IF Isolation	8 - 20 GHz 20 - 34 GHz 34 - 43 GHz	dB	_	9 25 35	_
RF Return Loss	RF = 25 GHz	dB	_	7	_
IF Return Loss	IF = 500 MHz	dB	_	12	_

^{5.} All specifications refer to down-conversion operation, unless otherwise noted.

Absolute Maximum Ratings^{6,7}

Parameter	Absolute Maximum		
LO Power	23 dBm		
RF or IF Power	20 dBm		
Junction Temperature ⁸	+150°C		
Operating Temperature	-55°C to +85°C		
Storage Temperature	-65°C to +150°C		

^{6.} Exceeding any one or combination of these limits may cause permanent damage to this device.

Handling Procedures

Please observe the following precautions to avoid damage:

Static Sensitivity

These electronic devices are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these devices with the following rating:

HBM Class 1B CDM Class C5

Assembly Information

- Do not subject the device to excessive force, especially at elevated temperatures > 60°C.
- No-clean flux is required for assembly. Post SMT washing is not recommended.

MACOM does not recommend sustained operation near these survivability limits.


^{8.} Operating at nominal conditions with $T_J \le +150^{\circ}\text{C}$ will ensure MTTF > 1 x 10^6 hours.




Rev. V4

Typical Performance Curves


Conversion Gain vs. LO Drive




Conversion Gain vs. Temperature



Isolation




RF Return Loss




IF Bandwidth

3



IF Return Loss



MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.


Visit www.macom.com for additional data sheets and product information.




Rev. V4

Typical Performance Curves


Input IP3 vs. LO Drive




Input IP3 vs. Temperature




Input IP2 vs. LO Drive




Input IP2 vs. Temperature



Input P1dB vs. LO Drive



Up Conversion Gain vs. LO Drive



MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit www.macom.com for additional data sheets and product information.




Rev. V4

MxN Spurious Rejection at IF Port (dBc IF)


RF = 17.5 GHz at -10 dBm LO = 18.0 GHz at +15 dBm

	NxLO				
MxRF	0	1	2	3	4
0	x	17	30	x	х
1	3	0	28	41	х
2	60	67	59	68	61
3	х	64	72	76	69
4	х	х	63	71	81

PCB Layout




Application Schematic



DXF available on request based on 10 mil RO4350 substrate.

No external parts required for operation of MAMX-011036.

Lead-Free 3 mm 12-Lead AQFN[†]



Reference Application Note S2083 for lead-free solder reflow recommendations. Meets JEDEC moisture sensitivity level 3 requirements. Plating is NiPdAu.

All dimensions are inches [mm].

Double-Balanced Mixer 8 - 43 GHz



MAMX-011036

Rev. V4

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.