

# **NML Series**

#### Isolated 2W Single Output DC-DC Converters



#### **FEATURES**

- UL 60950 recognised
- Single isolated output
- 1kVDC isolation 'Hi Pot Test'
- Efficiency up to 85%
- Wide temperature performance at full 2 watt load, −40°C to 85°C
- Industry standard pinout
- 5V & 12V inputs
- 5V, 9V, 12V & 15V outputs
- Internal SMD construction
- No external components required
- MTTF up to 2.3 million hours
- Custom solutions available
- Pin compatible with CME, CRE1, CRL2, LME, MEE1, NKE & NME series
- No electrolytic or tantalum capacitors

#### **DESCRIPTION**

The NML series of DC-DC Converters is particularly suited to isolating and/or converting DC power rails. The galvanic isolation allows the device to be configured to provide an isolated negative rail in systems where only positive rails exist. The wide temperature range guarantees startup from  $-40\,^{\circ}\text{C}$  and full 2 watt output at  $85\,^{\circ}\text{C}$ .

SELECTION (	GUIDE							
Order Code	Nominal Input Voltage	Output Voltage	Output Current	Input Current at Rated	Efficiency	Isolation	MTTF <sup>1</sup>	Recommended Alternative
	V	V	mA	mA	%	pF	kHrs	
Recommended In Production								
NML0505SC	5	5	400	513	78	19	2327	
NML0509SC	5	9	222	492	81	27	1393	
NML0512SC	5	12	167	479	84	32	832	
NML0515SC	5	15	133	481	83	27	481	
NML1205SC	12	5	400	207	81	28	716	
NML1212SC	12	12	167	197	85	46	461	
Discontinued								
NML1209SC	12	9	222	198	84	42	593	Contact Murata
NML1215SC	12	15	133	197	85	54	328	Contact Murata

INPUT CHARACTERISTICS							
Parameter	Conditions	Min.	Тур.	Max.	Units		
Voltago rango	Continuous operation, 5V input types	4.5	5.0	5.5	W		
Voltage range	Continuous operation, 12V input types	10.8	12.0	13.2	v		
Deflected ripple ourrent	5V input types		33		m A n n		
Reflected ripple current	12V input types		38		mA p-p		

GENERAL CHARACTERISTICS						
Parameter	Conditions	Min.	Тур.	Max.	Units	
Switching frequency	5V input types		90		Idla	
	12V input types		90		kHz	

<b>OUTPUT CHARACTERIST</b>	rics					
Parameter	Conditions	Min.	Тур.	Max.	Units	
Rated Power	T <sub>A</sub> =-40°C to 85°C			2.0	W	
Voltage Set Point Accuracy	See tolerance envelope					
Line regulation	High V <sub>IN</sub> to low V <sub>IN</sub>		1.0	1.2	%/%	
	10% load to rated load, 5V output types		7.0	8.5		
Load Degulation?	10% load to rated load, 9V output types		4.5	5.2	%	
Load Regulation <sup>2</sup>	10% load to rated load, 12V output types		4.5	5.5	%	
	10% load to rated load, 15V output types		3.7	8.5		
	NML0505SC, BW=DC to 20MHz		96			
	NML0509SC, BW=DC to 20MHz		67			
	NML0512SC, BW=DC to 20MHz		59			
Dinnle and Naice	NML0515SC, BW=DC to 20MHz		53	200	ml/ n n	
Ripple and Noise	NML1205SC, BW=DC to 20MHz		76	200	mV p-p	
	NML1209SC, BW=DC to 20MHz		63			
	NML1212SC, BW=DC to 20MHz		53			
	NML1215SC, BW=DC to 20MHz		45			

ISOLATION CHARACTERISTICS							
Parameter	Conditions	Min.	Тур.	Max.	Units		
Isolation test voltage	Flash tested for 1 second	1000			VDC		
Resistance	Viso= 500VDC	10			GΩ		







<sup>1.</sup> Calculated using MIL-HDBK-217F with nominal input voltage at full load.

All specifications typical at TA=25°C, nominal input voltage and rated output current unless otherwise specified.



# **NML Series**

# Isolated 2W Single Output DC-DC Converters

TEMPERATURE CHARACTERISTICS						
Parameter	Conditions	Min.	Тур.	Max.	Units	
Specification	All output types	-40		85		
Storage		-50		130	°C	
Constitution of the consti	5V output types			45	- 0	
Case Temperature above ambient	All other output types			36		
Cooling	Free air convection					

ABSOLUTE MAXIMUM RATINGS	
Lead temperature 1.5mm from case for 10 seconds	260°C
Wave Solder	Wave Solder profile not to exceed the profile recommended in IEC 61760-1 Section 6.1.3. Please refer to <u>application notes</u> for further information.
Input voltage V <sub>IN</sub> , NML05 types	7V
Input voltage V <sub>IN</sub> , NML12 types	15V



#### **TECHNICAL NOTES**

#### **ISOLATION VOLTAGE**

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions NML series of DC-DC converters are all 100% production tested at their stated isolation voltage. This is 1kVDC for 1 second.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

The NML series has been recognised by Underwriters Laboratory for functional insulation, both input and output should normally be maintained within SELV limits i.e. less than 42.4V peak, or 60VDC. The isolation test voltage represents a measure of immunity to transient voltages and the part should never be used as an element of a safety isolation system. The part could be expected to function correctly with several hundred volts offset applied continuously across the isolation barrier; but then the circuitry on both sides of the barrier must be regarded as operating at an unsafe voltage and further isolation/insulation systems must form a barrier between these circuits and any user-accessible circuitry according to safety standard requirements.

#### REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. The NML series has toroidal isolation transformers, with no additional insulation between primary and secondary windings of enamelled wire. While parts can be expected to withstand several times the stated test voltage, the isolation capability does depend on the wire insulation. Any material, including this enamel (typically polyurethane) is susceptible to eventual chemical degradation when subject to very high applied voltages thus implying that the number of tests should be strictly limited. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

This consideration equally applies to agency recognised parts rated for better than functional isolation where the wire enamel insulation is always supplemented by a further insulation system of physical spacing or barriers.

#### SAFETY APPROVAL

The NML series has been recognised by Underwriters Laboratory (UL) to UL 60950 for functional insulation in a maximum ambient temperature of 85°C and/or case temperature limit of 100°C as measured at any point on the case of the unit (hotspot).

The NML series of converters are not internally fused so to meet the requirements of UL 60950 an anti-surge input line fuse should always be used with ratings as defined below. NML05xxSC: 0.8A

NML12xxSC: 0.315A

All fuses should be UL recognised and rated to 125V. File number E151252 applies.

#### **ROHS COMPLIANCE INFORMATION**



This series is compatible with RoHS soldering systems with a peak wave solder temperature of 260°C for 10 seconds. Please refer to application notes for further information. The pin termination finish on this product series is Tin Plate, Hot Dipped over Matte Tin with Nickel replate. The series is backward compatible with Sn/Pb soldering systems.

For further information, please visit www.murata.com/en-global/products/power/rohs

# Series name Input voltage Output voltage




#### **CHARACTERISATION TEST METHODS**

#### Ripple & Noise Characterisation Method

Ripple and noise measurements are performed with the following test configuration.

C1	1μF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter
C2	$10\mu F$ tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than $100  \text{m}\Omega$ at $100  \text{kHz}$
C3	100nF multilayer ceramic capacitor, general purpose
R1	$450\Omega$ resistor, carbon film, ±1% tolerance
R2	$50\Omega$ BNC termination
T1	3T of the coax cable through a ferrite toroid
RLOAD	Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires
Measured va	lues are multiplied by 10 to obtain the specified values

Measured values are multiplied by 10 to obtain the specified values.



#### **APPLICATION NOTES**


#### Minimum load

The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically double the specified output voltage if the output load falls to less than 5%.

#### Capacitive loading and start up

Typical start up times for this series, with a typical input voltage rise time of  $2.2\mu s$  and output capacitance of  $10\mu F$ , are shown in the table below. The product series will start into a capacitance of  $47\mu F$  with an increased start time, however, the maximum recommended output capacitance is  $10\mu F$ .

	Start-up time
	μs
NML0505SC	790
NML0509SC	1154
NML0512SC	2265
NML0515SC	2998
NML1205SC	396
NML1209SC	880
NML1212SC	1156
NML1215SC	2394





#### **APPLICATION NOTES (Continued)**

#### Output Ripple Reduction


By using the values of inductance and capacitance stated, the output ripple at the rated load is lowered to 5mV p-p max.

#### Component selection

Capacitor: It is required that the ESR (Equivalent Series Resistance) should be as low as possible, ceramic types are recommended.

The voltage rating should be at least twice (except for 15V output), the rated output voltage of the DC-DC converter.


Inductor: The rated current of the inductor should not be less than that of the output of the DC-DC converter. At the rated current, the DC resistance of the inductor should be such that the voltage drop across the inductor is <2% of the rated voltage of the DC-DC converter. The SRF (Self Resonant Frequency) should be >20MHz.




	Inductor			Capacitor
	L, μH	SMD	Through Hole	C, µF
NML0505SC	22	82223	11R223C	2.2uF
NML0509SC	47	82473	11R473C	1uF
NML0512SC	47	82473	11R473C	2.2uF
NML0515SC	68	82683	11R683C	3.3uF
NML1205SC	22	82223	11R223C	2.2uF
NML1209SC	47	82473	11R473C	1uF
NML1212SC	47	82473	11R473C	2.2uF
NML1215SC	68	82683	11R683C	3.3uF

#### **TOLERANCE ENVELOPE**

The voltage tolerance envelope shows typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading.





#### TEMPERATURE DERATING GRAPH







#### PACKAGE SPECIFICATIONS











## **NML Series**

#### Isolated 2W Single Output DC-DC Converters

#### DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>:

Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solutions (Milton Keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the partining of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.