

# FFC.00.250.CTAD52Z

# SUMMARY

#### # Wires

Соах	1
Series	00
Termination type	Male solder
IP rating	50
AWG wire size	0.00 - 0.00
Cable Ø	4.10 - 5.00 mm
Status	Active
Matching parts	ERA.00.250.CTL



Image is for illustrative purpose only

Download
----------

Request a quote Catalog

# **TECHNICAL DETAILS**

#### **Mechanics**

	Shell Style/Model	FFC*: Straight plug with flats on latch sleeve and oversize cable collet and nut for fitting a bend relief
	Keying	Circular, male
	Housing Material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
	Variant	Z : Nut for fitting a bend relief
	Weight	5.37 g
Performance		
	Configuration	00.350 · 1 Carey (50.0km)

Configuration	00.250 : 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated Current	4 Amps

#### Specifications

Contact Type: Coaxial 50 Ohm (Solder) Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.6 mm (0.024in) Test voltage: 2.1 kV (rms) R (max): 6.1 mOhm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Vtest: 2100 V (AC), 3000 V (DC)

Impedance: 50 Ohm VSWR: 1.09 + 0.11 \* f/GHz Cable type: RG 58 C/U

#### Others

Endurance (Shell): 5000 mating cycles F ret (min): 100 N Salt Spray Corrosion: >1000 hr

### DRAWINGS



### **RECOMMENDED BY LEMO**

Tools

Spanner wrench:

DCD.00.ZZZ.PA050

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.