

Parameter	Rating	Units
Blocking Voltage	60	V <sub>P</sub>
Load Current	500	mA <sub>rms</sub> / mA <sub>DC</sub>
On-Resistance (max)	2	Ω

#### **Features**

- $\bullet$  3750V<sub>rms</sub> Input/Output Isolation
- Low Drive Power Requirements
- · Greater Reliability than Electromechanical Relays
- No EMI/RFI Generation
- Small 6-Pin Package
- Flammability Rating UL 94 V-0
- Tape & Reel, Surface Mount Version Available

# **Applications**

- Sensor Circuitry
- Instrumentation
- Multiplexers
- Data Acquisition
- Electronic Switching
- I/O Subsystems
- · Meters (gas, oil, electric and water)
- Medical Equipment-Patient/Equipment Isolation
- Security
- Industrial Controls

## **Description**

LCB716 is a single-pole, normally closed (1-Form-B) solid state relay that uses optically coupled relay technology to provide an enhanced 3750V<sub>rms</sub> isolation barrier between the input and the output of the relay. The efficient MOSFET output switch uses IXYS Integrated Circuits' patented OptoMOS architecture. The optically coupled output is controlled by a highly efficient infrared LED.


## **Approvals**


- UL Recognized Component: File E76270
- TUV EN 62368-1: Certificate # B 082667 0008

# **Ordering Information**


Part #	Description
LCB716	6-Pin DIP (50/Tube)
LCB716S	6-Pin Surface Mount (50/Tube)
LCB716STR	6-Pin Surface Mount (1000/Reel)

# **Pin Configuration**





# **Switching Characteristics** of Normally Closed Devices











# Absolute Maximum Ratings @ 25°C

Parameter	Ratings	Units
Blocking Voltage	60	$V_P$
Reverse Input Voltage	5	V
Input Control Current	50	mA
Peak (10ms)	1	Α
Input Power Dissipation <sup>1</sup>	100	mW
Total Power Dissipation <sup>2</sup>	800	mW
Isolation Voltage, Input to Output	3750	$V_{rms}$
Operational Temperature, Ambient	-40 to +85	°C
Storage Temperature	-40 to +125	°C

<sup>1</sup> Derate linearly 1.33 mW / °C

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Typical values are characteristic of the device at +25°C, and are the result of engineering evaluations. They are provided for information purposes only, and are not part of the manufacturing testing requirements.

## Electrical Characteristics @ 25°C


Parameter	Conditions	Symbol	Min	Тур	Max	Units
Output Characteristics						
Blocking Voltage	I <sub>L</sub> =1μΑ	$V_{DRM}$	60	-	-	V <sub>P</sub>
Load Current						
Continuous, AC/DC Configuration	1 Om A		-	-	500	mA <sub>rms</sub> / mA <sub>DC</sub>
Continuous, DC Configuration	I <sub>F</sub> =0mA	IL	-	-	1000	mA <sub>DC</sub>
Peak	t <u>&lt;</u> 10ms	I <sub>LPK</sub>	-	-	±1.2	A <sub>P</sub>
On-Resistance <sup>1</sup>						
AC/DC Configuration	I <sub>F</sub> =0mA, I <sub>L</sub> =500mA	D	-	1.63	2	Ω
DC Configuration	I <sub>F</sub> =0mA, I <sub>L</sub> =1000mA	- R <sub>ON</sub>	-	0.4	0.5	
Off-State Leakage Current	$I_F=2mA, V_L=60V$	I <sub>LEAK</sub>	-	-	1	μΑ
Output Capacitance	I <sub>F</sub> =2mA, V <sub>L</sub> =50V, f=1MHz	C <sub>OUT</sub>	-	280	-	pF
Switching Speeds						
Turn-On	I <sub>E</sub> =5mA, V <sub>I</sub> =10V	t <sub>on</sub>	-	0.58	3	ms
Turn-Off	1 <sub>F</sub> -3111A, V <sub>L</sub> -10V	t <sub>off</sub>	-	0.76	3	1115
Input Characteristics	,					11
Input Control Current to Activate	I <sub>L</sub> =500mA	I <sub>F</sub>	-	-	2	mA
Input Control Current to Deactivate	-	I <sub>F</sub>	0.1	-	-	mA
Input Voltage Drop	I <sub>F</sub> =5mA	$V_{F}$	0.9	1.36	1.5	V
Reverse Input Current	V <sub>R</sub> =5V	I <sub>R</sub>	-	-	10	μΑ
Common Characteristics				•		
Capacitance, Input to Output	V <sub>IO</sub> =0V, f=1MHz	C <sub>IO</sub>	-	3	-	pF

<sup>&</sup>lt;sup>1</sup> Measurement taken within one second of on-time.

 $<sup>^2~</sup>$  Derate output power linearly 6.67 mW /  $^{\rm o}{\rm C}$ 




#### **PERFORMANCE DATA\***





\*Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C.





## **PERFORMANCE DATA\***
















# **Manufacturing Information**

#### **Moisture Sensitivity**

All plastic encapsulated semiconductor packages are susceptible to moisture ingression. IXYS Integrated Circuits classifies its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, IPC/JEDEC J-STD-020, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a **Moisture Sensitivity Level (MSL)** classification as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

Device	Moisture Sensitivity Level (MSL) Classification	
LCB716S	MSL 1	

#### **ESD Sensitivity**



This product is ESD Sensitive, and should be handled according to the industry standard JESD-625.

#### **Soldering Profile**

Provided in the table below is the **IPC/JEDEC J-STD-020** Classification Temperature  $(T_C)$  and the maximum total dwell time  $(t_p)$  in all reflow processes that the body temperature of these surface mount devices may be  $(T_C - 5)^{\circ}C$  or greater. The device's body temperature must not exceed the Classification Temperature at any time during reflow soldering processes.

Device Classification Temperature (T <sub>c</sub> )		Dwell Time (t <sub>p</sub> )	Max Reflow Cycles	
LCB716S	250°C	30 seconds	3	

For through-hole devices, the maximum pin temperature and maximum dwell time through all solder waves is provided in the table below. Dwell time is the interval beginning when the pins are initially immersed into the solder wave until they exit the solder wave. For multiple waves, the dwell time is from entering the first wave until exiting the last wave. During this time, pin temperatures must not exceed the maximum temperature given in the table below. Body temperature of the device must not exceed the limit shown in the table below at any time during the soldering process.

Device	Maximum Pin Temperature	Maximum Body Temperature	Maximum Dwell Time	Wave Cycles
LCB716	260°C	250°C	10 seconds*	1

<sup>\*</sup>Total cumulative duration of all waves.

#### **Board Wash**

IXYS Integrated Circuits recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include but are not limited to: using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to halide flux or solvents.







2.540±0.127

(0.100±0.005)

7.620±0.127 (0.300±0.005)


**Dimensions** 

(inches)




#### **Mechanical Dimensions**

## **LCB716**




## **LCB716S**





# LCB716STR Tape & Reel



For additional information please visit our website at: https://www.ixysic.com



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at https://www.littelfuse.com/disclaimer-electronics.