



N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	R _{DS(ON)}	Package	I _D T _A = +25°C
30V	0.15Ω @ $V_{GS} = 4.5V$		2A
	0.2Ω @ $V_{GS} = 2.5V$	SOT23	1.6A
	0.25Ω @ $V_{GS} = 1.8V$	30123	1.4A
	0.3Ω @ V _{GS} = 1.5V		1.2A

Description

This new generation MOSFET has been designed to minimize the on-state resistance ($R_{DS(ON)}$) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Applications

- DC-DC Converters
- Power Management Functions
- Battery Operated Systems and Solid-State Relays
- Drivers: Relays, Solenoids, Lamps, Hammers, Displays, Memories, Transistors, etc.

Features

- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Small Surface Mount Package
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen- and Antimony-Free. "Green" Device (Note 3)
- The DMN3300UQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.


https://www.diodes.com/quality/product-definitions/

Mechanical Data


- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram
- Terminals: Finish—Matte Tin Annealed over Copper Lead-Frame. Solderable per MIL-STD-202, Method 208 <a> ®
- Weight: 0.008 grams (Approximate)







Equivalent Circuit



Top View


Ordering Information (Note 4)

Part Number	Case	Packaging
DMN3300UQ-7	SOT23	3,000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



SOT23

33N = Marking Code $\overline{Y}M$ = Date Code Marking \overline{Y} = Year (ex: H = 2020) M = Month (ex: 9 = September)

Date Code Key

Year	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031
Code	Н	I	J	K	L	М	N	0	Р	R	S	T
	1	1		1	1				1			
				_		_		A	O		NI	D
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec



Maximum Ratings (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage	V_{DSS}	30	V		
Gate-Source Voltage			V_{GSS}	±12	V
Continuous Drain Current (Note 5) V _{GS} = 4.5V	Steady State	T _A = +25°C T _A = +70°C	I _D	1.5 1.2	А
Continuous Drain Current (Note 6) V _{GS} = 4.5V	Steady State	$T_A = +25$ °C $T_A = +70$ °C	I _D	2.0 1.6	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I _{DM}	8	Α		
Maximum Body Diode Continuous Current (Note 6)			I _S	1.6	Α

Thermal Characteristics

Characteristic		Symbol	Value	Unit	
Total Power Dissipation	(Note 5)	D-	0.7	W	
Total Power Dissipation	(Note 6)	P _D	1.3		
Thermal Resistance, Junction to Ambient	(Note 5)	Б	176		
Thermal Resistance, Junction to Ambient	(Note 6)	$R_{\theta JA}$	102	°C/W	
Thermal Resistance, Junction to Case	(Note 6)	$R_{ heta JC}$	45		
Operating and Storage Temperature Range	_	T _{J,} T _{STG}	-55 to +150	°C	


Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)	Symbol	IAIIII	тур	WIGA	Oilit	rest condition	
Drain-Source Breakdown Voltage	BV _{DSS}	30	37	_	V	V _{GS} = 0V, I _D = 100μA	
Zero Gate Voltage Drain Current	I _{DSS}	_	_	1	μA	V _{DS} = 30V, V _{GS} = 0V	
Gate-Source Leakage	I _{GSS}	_	_	±10	μA	$V_{GS} = \pm 12V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	V _{GS(TH)}	0.5		1	V	$V_{DS} = V_{GS}, I_D = 250 \mu A$	
			100 140 185 240	150		$V_{GS} = 4.5V, I_D = 4.5A$	
Static Drain-Source On-Resistance	R _{DS(ON)}	_		200 250 300	mΩ	$V_{GS} = 2.5V, I_D = 3.5A$	
Static Dialit-Source Off-Resistance						$V_{GS} = 1.8V, I_D = 1.5A$	
						$V_{GS} = 1.5V, I_D = 0.5A$	
Diode Forward Voltage	V_{SD}	_	0.8	1.1	V	$V_{GS} = 0V, I_S = 0.5A$	
DYNAMIC CHARACTERISTICS (Note 8)							
Input Capacitance	C _{iss}		193		рF	101/11/	
Output Capacitance	Coss	_	35	_	pF	$V_{DS} = 10V, V_{GS} = 0V$ f = 1.0MHz	
Reverse Transfer Capacitance	C _{rss}		23		pF	1 = 1.01/11 12	
Turn-On Delay Time	t _{D(ON)}	_	7	_			
Rise Time	t _R	_	24	_	ns	$V_{DD} = 10V$, $R_L = 10\Omega$	
Turn-Off Delay Time	t _{D(OFF)}	_	24	_	115	$I_D = 1A, V_{GEN} = 4.5V, R_G = 6\Omega$	
Fall Time	t _F	_	12	_			

Notes:

- Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.
 Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper pad layout.
 Short duration pulse test used to minimize self-heating effect.
 Guaranteed by design. Not subject to production testing.








Fig. 3 On-Resistance vs. Drain Current & Gate Voltage





Fig. 5 Gate Threshold Variation vs. Ambient Temperature










Fig. 4 Normalized Static Drain-Source On-Resistance vs. Ambient Temperature














Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT23							
Dim	Min	Max	Тур				
Α	0.37	0.51	0.40				
В	1.20	1.40	1.30				
С	2.30	2.50	2.40				
D	0.89	1.03	0.915				
F	0.45	0.60	0.535				
G	1.78	2.05	1.83				
Н	2.80	3.00	2.90				
7	0.013	0.10	0.05				
K	0.890	1.00	0.975				
K1	0.903	1.10	1.025				
L	0.45	0.61	0.55				
L1	0.25	0.55	0.40				
M	0.085	0.150	0.110				
а	0°	8°					
All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com