

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	TAB SIZE	WIRE RANGE		COLOR	MAX. WIRE INSUL. DIA.	DIMENSIONS in. [mm]			
		ENGLISH	METRIC			L ± .03 [0,8]	H ± .01 [0,3]	W ± .01 [0,3]	D ± .03 [0,8]
DNFR18-250B	.250 X .032 [6,3 X 0,8]	22-18	0,5-1,0	RED	.13 [3,3]	.78 [19,8]	.20 [5,1]	.36 [9,1]	.62 [15,7]
DNFR14-250B	.250 X .032 [6,3 X 0,8]	16-14	1,5-2,5	BLUE	.16 [4,1]				.63 [16,0]
DNFR18-205B	.205 X .032 [5,2 X 0,8] OR .187 X .020 [4,8 X 0,5]	22-18	0,5-1,0	RED	.13 [3,3]				.62 [15,7]
DNFR14-205B		16-14	1,5-2,5	BLUE	.16 [4,1]				.63 [16,0]
DNFR18-206B		22-18	0,5-1,0	RED	.13 [3,3]				.62 [15,7]
DNFR14-206B		16-14	1,5-2,5	BLUE	.16 [4,1]				.63 [16,0]




LISTED
20H3
E78522

CERTIFIED
LR31212

NOTES:

- USED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 - C. 600 V. MAX. VOLTAGE RATING
- MATERIAL:
 - A. STAMPING: .018 [0,46] TIN PLATED BRASS
 - B. HOUSING: NYLON
- INSTALLATION TOOLS: CT-1525, CT-2500 (CT-2525CH)
- WIRE STRIP LENGTH: 9/32 ^{+1/32}/₀ [7,1 ^{+0,8}/₀]
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- FIRST INSERTION FORCE: 12 Lb [53 N] MAXIMUM
FIRST WITHDRAWAL FORCE: 12 Lb [53 N] MAXIMUM
6 Lb [27 N] MINIMUM



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
09	10.18.12	JBN	LSM	VMB	UPDATED DRAWING TO CURRENT STANDARDS	A41329

TITLE RIGHT ANGLE FEMALE DISCONNECT, NYLON INSULATED, FUNNEL ENTRY	
CUSTOMER DRAWING	
ITEM REVISION NAME N41329BA/09	PANDUIT TM
DATASET FILE NAME N41329BA_DC/09A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °	
MATERIAL: SEE NOTES	
DRAWING NUMBER: A41329	
DRAWN BY DAW	DATE -
CHK RLS	SCALE N.T.S.
SHEET 1 OF 1	
SIZE A	

D10100DA/12