




BNC ATTENUATOR 10 DB 4 GHZ 10W



PAGE 1/2 ISSUE 29-11-16A SERIES ATTENUATOR PART NUMBER R415410000







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
5 .		
Body	BRASS	NICKEL 5
Male center contact	BRASS	GOLD 2.5 OVER NICKEL 1
Female center contact	BERYLLIUM COPPER	GOLD 2.5 OVER NICKEL 1
Outer contact	-	-
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINIUM NITRIDE	
Resistor	THIN FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION





BNC ATTENUATOR 10 DB 4 GHZ 10W

PAGE 2/2	ISSUE 29-11-16A	SERIES ATTENUATOR	PART NUMBER R415410000
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 4
V.S.W.R (≤)	1.30
Deviation(±dB)	0.50

Operating Frequency Range	DC - 4	GHz
Impedance	50	Ω
Nominal Attenuation	10	dB
Peak power at 25°C (1µs, 1‰)	250	W
Average power at 25°C	10	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	BNC	Male Female	MIL-C 39012
Weight	38,0000 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C	
Storage temperature range	-55 /+125 °C	

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS