





SMA ATTENUATOR 3 DB 6 GHZ 50W

PAGE 1/2 ISSUE 28-05-20A SERIES PART NUMBER R422203020





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS MATERIALS		PLATING (μm)	
Body	STAINLESS STEEL	PASSIVATED.	
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Outer contact	BERTELIOW COFFER	GOLD 0.3 OVER NICKEL PHOSPHOROS 2	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Substrate	ALUMINIUM NITRIDE		
Resistor	THICK FILM		
Others parts	ALUMINIUM	BLACK ANODIZATION	



Technical Data Sheet

SMA ATTENUATOR 3 DB 6 GHZ 50W

PAGE 2/2	ISSUE 28-05-20A	SERIES ATTENUATOR	PART NUMBER R422203020
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 6
V.S.W.R (≤)	1.25
Deviation(±dB)	0.75


Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
Nominal Attenuation	3	dB
Peak power at 25°C (1µs, 1‰)	2000	W
Average power at 25°C	50	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL C39012
Weight	474,62	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C





SPECIFICATION

OTHER CHARACTERISTICS