



# **RFBLN Series – 1608(0603)- RoHS Compliance**

# MULTILAYER CERAMIC BALUN TRANSFORMER

# 2.4 GHz ISM Band RF Application

# P/N: RGBLN1608070A5T

\*Contents in this sheet are subject to change without prior notice.

## **Approval sheet**




#### **FEATURES**

- 1. Multilayer LTCC ( Low Temperature Cofired Ceramics ) Technology
- 2. Miniatured Size  $1.6 \times 0.8 \times 0.7 \text{ mm}^3$
- 3. Low Insertion Loss reduces power consumption
- 4. Low inband Amplitude and Phase imbalance enable high performance wireless system operation.
- 5. Enable for DC Biasing of PA or Mixer
- 6. Suitable for 2.45 GHz Working Frequency Operation
- 7. Special Balance/ Unbalance impedance is upon requested.


## **APPLICATIONS**

- 1. 2.4GHz ISM Band RF Application
- 2. Bluetooth, Wireless LAN, HomeRF

## CONSTRUCTION



### DIMENSIONS




# BSA 華新科技股份有限公司 Walsin Technology Corporation


### **Approval sheet**

## **ELECTRICAL CHARACTERISTICS**

RGBLN1608070A5T	Specification
Frequency range	2400 ~ 2500 MHz
Insertion Loss	1.2 dB max.
Phase Difference	$180^{\circ} \pm 10^{\circ}$
Amplitude Difference	2.0 dB max.
VSWR	2.0 max.
Impedance (Unbalanced)	<b>50</b> Ω
Impedance (Balanced)	100 Ω
Operating temperature Range	-40°C∼85°C
Moisture sensitivity levels	LEVEL 1 (Refer to : IPC/JEDEC J-STD-020)
Typical Electrical Chart	



### SOLDER LAND PATTERN



# PSA 華新科技股份有限公司 Walsin Technology Corporation

# Approval sheet

## **RELIABILITY TEST**

Test item	Test condition / Test method	Specification
Solderability JIS C 0050-4.6 JESD22-B102D	*Solder bath temperature : 235 ± 5°C *Immersion time : 2 ± 0.5 sec Solder : Sn3Ag0.5Cu for lead-free	At least 95% of a surface of each terminal electrode must be covered by fresh solder.
Leaching (Resistance to dissolution of metallization) IEC 60068-2-58	*Solder bath temperature : $260 \pm 5$ °C *Leaching immersion time : $30 \pm 0.5$ sec Solder : SN63A	Loss of metallization on the edges of each electrode shall not exceed 25%.
Resistance to soldering heat JIS C 0050-5.4	*Preheating temperature : 120~150°C, 1 minute. *Solder temperature : 270±5°C *Immersion time : 10±1 sec Solder : Sn3Ag0.5Cu for lead-free Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C. Loss of metallization on the edges of each electrode shall not exceed 25%.
Drop Test JIS C 0044 Customer's specification.	<ul> <li>*Height : 75 cm</li> <li>*Test Surface : Rigid surface of concrete or steel.</li> <li>*Times : 6 surfaces for each units ; 2 times for each side.</li> </ul>	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Adhesive Strength of Termination JIS C 0051- 7.4.3	*Pressurizing force : 5N(≦0603) ; 10N(>0603) *Test time : 10±1 sec	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Bending test JIS C 0051- 7.4.1	The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm/s per second until the deflection becomes 1mm/s and then pressure shall be maintained for 5±1 sec. Measurement to be made after keeping at room temperature for 24±2 hours	No remarkable damage or removal of the termination.

ľ

# PSA 華新科技股份有限公司 Walsin Technology Corporation

# Approval sheet

Temperature cycle	1. 30±3 minutes at -40°C±3°C,	No mechanical damage.		
JIS C 0025	2. 10~15 minutes at room temperature,	Electrical specification shall satisfy the		
	3. 30±3 minutes at +85°C±3°C,	descriptions in electrical characteristics under		
	4. 10~15 minutes at room temperature,	the operational temperature range within -40		
	Total 100 continuous cycles	~ 85°C.		
	Measurement to be made after keeping at			
	room temperature for $24\pm 2$ hrs			
Vibration	*Frequency:10Hz~55Hz~10Hz(1min)	No mechanical damage.		
JIS C 0040	*Total amplitude:1.5mm	Electrical specification shall satisfy the		
	*Test times : 6hrs.(Two hrs each in three	descriptions in electrical characteristics		
	mutually perpendicular directions)	under the operational temperature range		
		within -40 ~ 85°C.		
High temperature	*Temperature : 85°C±2°C	No mechanical damage.		
JIS C 0021		Electrical specification shall satisfy the		
	*Test duration : 1000+24/-0 hours	descriptions in electrical characteristics under		
	Measurement to be made after keeping at	the operational temperature range within -40		
	room temperature for 24±2 hrs	~ 85°C.		
Humidity	*Humidity : 90% to 95% R.H.	No mechanical damage.		
(steady conditions)	*Temperature : 40±2°C	Electrical specification shall satisfy the		
JIS C 0022	*Time:1000+24/-0 hrs.	descriptions in electrical characteristics under		
	Measurement to be made after keeping at	the operational temperature range within -40		
	room temperature for 24±2 hrs	~ 85°C.		
	st 500hrs measuring the first data then			
	1000hrs data			
Low temperature	*Temperature:-40°C±2°C	No mechanical damage.		
JIS C 0020	*Test duration : 1000+24/-0 hours	Electrical specification shall satisfy the		
	Measurement to be made after keeping at	descriptions in electrical characteristics under		
	room temperature for 24±2 hrs	the operational temperature range within -40 ~ 85°C.		

### SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,





Fig 2. Infrared soldering profile

# **ORDERING CODE**

RG	BLN	160807	0	Α	5	Т
Walsin	Product	Dimension	Unit of	Application	Specification	Packing
RG: RF	Code	code	dimension	A : 2.4GHz ISM	Design Code	T: Reeled
/Pb free	BLN :	Per 2 digits of	0 : 0.1 mm	Band		
device	BALUN	Length, Width,	1 : 1.0 mm			
		Thickness :				
		e.g. :				
		160807 = Length				
		16, Width 08,				
		Thickness 07				


## PACKAGING

Paper Tape specifications (unit :mm)



Index	Ao	Во	ΦD	Т	W
Dimension (mm)	$0.975{\pm}\ 0.05$	1.76 ±0.05	1.55 + 0.05	$0.75{\pm}0.03$	$\textbf{8.0}\pm\textbf{0.10}$
Index	E	F	Po	P1	P2
Dimension (mm)	$1.75\pm0.10$	$3.50\pm0.05$	$4.00\pm0.10$	$4.00\pm0.10$	$2.00\pm0.05$

## **Reel dimensions**



Taping Quantity: 4000 pieces per 7" reel

#### CAUTION OF HANDLING

#### Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

#### Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection, which can be confirmed.
- (2) Storage environment condition.
  - Products should be storage in the warehouse on the following conditions.
  - Temperature : -10 to +40°C
  - Humidity : 30 to 70% relative humidity
  - Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
  - Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
  - Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
  - Products should be storage under the airtight packaged condition.