

SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 1 of 3

H13-12.000-18-2020-TR


SPECIFICATIONS

PARAMETER	VALUE
NOMINAL FREQUENCY	12.000 MHz
MODE OF OSCILLATION	Fundamental
FREQUENCY TOLERANCE AT 25°C	±20 ppm max
FREQUENCY STABILITY OVER TEMPERATURE	±20 ppm max
OPERATING TEMPERATURE RANGE	-10°C to +60°C
STORAGE TEMPERATURE RANGE	-40°C to +85°C
AGING	±5 ppm per year max
LOAD CAPACITANCE	18 pF
EQUIVALENT SERIES RESISTANCE	60Ω max
SHUNT CAPACITANCE	5 pF max
DRIVE LEVEL	300 µW max




Photo is not actual part

MECHANICAL SPECIFICATION



CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS

PACKAGING

255 mm REEL DIAMETER 16 mm TAPE WIDTH, 8 mm PITCH QUANTITY: 1000 PIECES PER REEL


IN ACCORDANCE WITH EIA-481




SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 2 of 3

REFLOW PROFILE





Reflow profile				
Temperature Min Preheat	T _{SMIN}	150°C		
Temperature Max Preheat	T _{SMAX}	200°C		
Time (T _{SMIN} to T _{SMAX})	ts	60-180 sec.		
Temperature	TL	217°C		
Peak Temperature	TP	260°C		
Ramp-up rate	R _{UP}	3°C/sec max.		
Ramp-down rate	R _{DOWN}	6°C/sec max.		
Time within 5°C of Peak Temperature	t _P	10 sec.		
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.		
Time	tL	60-150 sec.		

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au





SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 3 of 3

H13-12.000-18-2020-TR

MARKING

R12.000 xxBDyw

- x Internal Production ID code
- y Year code
- w-Week code

YEAR CODE			
Year	Code		
2015	5		
2016	6		
2017	7		
2018	8		
2019	9		
2020	0		
2021	1		
2022	2		
2023	3		
2024	4		
2025	5		

ALPHA WEEK CODE TABLE					
Week	Code	Week	Code	Week	Code
1	а	19	s	37	K
2	b	20	t	38	L
3	с	21	u	39	М
4	d	22	v	40	Ν
5	e	23	w	41	0
6	f	24	х	42	Р
7	g	25	У	43	Q
8	h	26	z	44	R
9	i	27	А	45	S
10	j	28	В	46	Т
11	k	29	С	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	Х
15	0	33	G	51	Y
16	р	34	Н	52	Z
17	q	35	Ι		
18	r	36	J		

APPROVAL

RALTRON	
DRAWN BY:	XLiu, January 31, 2019
APPROVED BY:	JIvens, January 31, 2019
REVISION:	A, Initial Release

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not guarantee that the information is provided only for an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.