



EK350V-XXP PCB Terminal Blocks > PCB Terminal Blocks

Date:2021-09-07Version:V1







The web catalog is for reference only. Dinkle remains the right of product modification and engineering change of the design. The final product is made according to engineering drawing.

Product Description

Pitch : 3.50mm, 300V, 10A

General information

Short description	PCB Terminal Blocks, Screw Connection
Category	PCB Terminal Blocks
Pitch (mm)	3.50
Color	Green (default)
Connection method	Screw Connection
Type of locking	Without
Length (mm)	3.50*(P-1)+3.8
Width (mm)	7.4
Height (mm)	8.5
Pin demensions (Thickness x Width)(mm)	0.5x0.9
PCB hole diameter (mm)	1.2~1.3
Number of positions	02P~24P
Level	Single level

Material information



Insulation material group	Ι
Flame retardant rating , compliant with UL94	VO
Insulation resistance	0500MΩ at DC 500V
Conductor material	COPPER ALLOY
Plating of conductor surface	Tin PLATED

Connection data-IEC

Rated voltage (V)160Rated current (A)12Rated voltage (II/2)(V)320Rated voltage (II/2) (V)160Rated voltage (III/2) (V)160Rated impulse voltage (II/2)(KV)2.5Rated impulse voltage (III/2)(KV)2.5Rated impulse voltage (III/2)(KV)2.5Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.5Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with0.5
Rated voltage (II/2)(V)320Rated voltage (III/2) (V)160Rated voltage (III/2)(V)160Rated impulse voltage (II/2)(KV)2.5Rated impulse voltage (III/2)(KV)2.5Rated impulse voltage (III/3)(KV)2.5Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.5Conductor cross section flexible, with min ferrule0.5Without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with0.5
Rated voltage (III/2) (V)160Rated voltage (III/2) (V)160Rated impulse voltage (III/2) (KV)2.5Rated impulse voltage (III/2) (KV)2.5Rated impulse voltage (III/3) (KV)2.5Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)0.14Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.5Conductor cross section flexible, with min ferrule0.5Conductor cross section flexible, with min ferrule0.75Conductor cross section flexible, with min ferrule with0.5
Rated voltage (II/3)(V)160Rated impulse voltage (II/2)(KV)2.5Rated impulse voltage (III/2)(KV)2.5Rated impulse voltage (III/3)(KV)2.5Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.5Conductor cross section flexible, with min ferrule0.5Conductor cross section flexible, with max ferrule0.75Conductor cross section flexible, with min ferrule with0.5
Rated impulse voltage (II/2)(KV)2.5Rated impulse voltage (III/2)(KV)2.5Rated impulse voltage (III/3)(KV)2.5Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.5Conductor cross section flexible, with min ferrule0.5Conductor cross section flexible, with max ferrule0.75Conductor cross section flexible, with min ferrule with0.5
Rated impulse voltage (III/2)(KV)2.5Rated impulse voltage (III/3)(KV)2.5Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)0.5Conductor cross section stranded. max (mm²)1.5Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with0.5
Rated impulse voltage (III/3)(KV)2.5Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. min (mm²)1.5Conductor cross section stranded. max (mm²)1.5Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with0.5
Conductor cross section solid. min (mm²)0.14Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. max (mm²)1.5Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.5Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.75
Conductor cross section solid.max (mm²)1.5Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. max (mm²)1.5Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.5Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with0.5
Conductor cross section stranded. min (mm²)0.14Conductor cross section stranded. max (mm²)1.5Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.5Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with 0.750.5
Conductor cross section stranded. max (mm²)1.5Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.5Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with 0.50.5
Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)0.5Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with0.5
without plastic sleeve (mm²)0.75Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)0.75Conductor cross section flexible, with min ferrule with0.5
without plastic sleeve (mm²) Conductor cross section flexible, with min ferrule with 0.5
Conductor cross section flexible, with min ferrule with 0.5
plastic sleeve (mm ²)
Conductor cross section flexible, with max ferrule with plastic sleeve (mm ²) 0.75
2 conductors with same cross section, solid, max (mm ²) 0.5
2 conductors with same cross section, stranded, max 0.5 (mm ²)
Screw thread M2
Slotted screwdriver size (Blade thickness x Width)(mm)0.4x2.5
Rated torque (N.m)0.2
Stripping Length (mm) 5~6

Connection data-UL

Rated voltage (UL/CUL Group B)(V)	300



Rated current (UL/CUL Group B)(A)	10
Rated voltage (UL/CUL Group D)(V)	300
Rated current (UL/CUL Group D)(A)	10
Min. solid wire connection (AWG) acc. to UL/CUL	30
Max. solid wire connection AWG acc. to UL/CUL	16
Min. stranded wire connection AWG acc. to UL/CUL	30
Max. stranded wire connection AWG acc. to UL/CUL	16

Environment & Safety

Finger protection (YES or NO)	YES
Operating temperature. max (°C)	120
Operating temperature. min (°C)	-40

UL Recognized

Wire Range (Group B)(AWG)	30~16
Rated voltage (Group B)(V)	300
Rated current (Group B)(A)	10
Wire Range (Group D)(AWG)	30~16
Rated voltage (Group D)(V)	300
Rated current (Group D)(A)	10

CUL Recognized


Wire Range (Group B)(AWG)	30~16
Rated voltage (Group B)(V)	300
Rated current (Group B)(A)	10
Wire Ranget (Group D)(AWG)	30~16
Rated voltage (Group D)(V)	300
Rated current (Group D)(A)	10

VDE Approval

Wire Range (mm²)	0.14~1.5
Rated voltage (V)	130
Rated current (A)	12

Drawings





Approvals

