

Features

- Single coil latching power relay
- UL F class rated standard
- Heavy contact load, strong shock and vibration resistance
- UL/CUL certified

cUL^{us}
E197852



Contact Data*

Contact Arrangement	1A = SPST 1C = SPDT	Contact Rating N.O.	30A @ 277VAC resistive, 6k cycles 25C ambient 40A @ 277VAC resistive, 6k cycles 25C ambient 50A @ 277VAC resistive, 6k cycles 25C ambient
Contact Resistance	≤ 50 milliohms initial		
Contact Material	AgSnO ₂ , AgSnO ₂ In ₂ O ₃	N.C.	30A @ 277VAC resistive, 6k cycles 25C ambient 40A @ 277VAC resistive, 6k cycles 25C ambient 50A @ 277VAC resistive, 6k cycles 25C ambient
Maximum Switching Power	13850VA, 1500W		
Maximum Switching Voltage	277VAC, 110VDC		
Maximum Switching Current	50A		

Coil Data Single Coil Latching*

Coil Voltage VDC		Coil Resistance Ω +/- 10%		Pick Up Voltage VDC (max)	Pulse Magnitude ms	Coil Power W	Operate Time ms	Reset Time ms
Rated	Max	.9W	1.5W					
5	6.0	28	16.7	80% of rated voltage 4.0	≥100	.9 1.5	15	15
12	14.4	160	96	9.6				
24	288	640	384	19.2				
48	57.6	2560	1536	38.4				

General Data*

Electrical Life @ rated load	50K cycles, average
Mechanical Life	1M cycles, average
Insulation Resistance	1000 Ω min. @ 500VDC initial
Dielectric Strength	Coil to Contact 2500V rms min. @ sea level initial Contact to Contact 1500V rms min. @ sea level initial
Shock Resistance	200m/s ² for 11 ms
Vibration Resistance	1.50mm double amplitude 10~40Hz
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +155°C
Solderability	270°C for 5 s
Weight	28g, 20g (no cover)


* Values can change due to the switching frequency, desired reliability levels, environmental conditions and in-rush load levels. It is recommended to test actual load conditions for the application. It is the user's responsibility to determine the performance suitability for their specific application. The use of any coil voltage less than the rated coil voltage may compromise the operation of the relay.

Ordering Information

1. Series	L115F1	1C	M	12VDC	S	.9
L115F1						
2. Contact Arrangement	1A = SPST 1C = SPDT					
3. Contact Rating	M = 30A K = 40A H = 50A					
4. Coil Voltage	5VDC 12VDC 24VDC 48VDC					
5. Sealing Options	S = Sealed against flux ingress C = Dust Cover N = No Cover *Not available with 48VDC Coil Voltage					
6. Coil Power	.9 = .9W **for 30A and 40A contacts only 1.5 = 1.5W **for 50A contacts only					
7. Contact Material	Blank = AgSnO ₂ U = AgSnO ₂ In ₂ O ₃					

Dimensions




Units = mm



S = Sealed

Dimensions

Units = mm




N = No Cover


Schematics & PC Layouts

Bottom Views


Shown and supplied in the **RESET** position.



1A



1B



1C

