

Sep.1.2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾		
	VOLTAGE	100 V AC		OPERATING HUMIDITY RANGE	40 % TO 80 %		
	CURRENT	0.5 A		STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾		
SPECIFICATIONS							
ITEM	TEST METHOD			REQUIREMENTS	QT	AT	
CONSTRUCTION							
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.	x	x	
MARKING	CONFIRMED VISUALLY.				x	x	
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).			40 mΩ MAX.	x	-	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV MAX, 1 mA(DC OR 1000Hz)			50 mΩ MAX.	x	-	
INSULATION RESISTANCE	250 V DC			100 MΩ MIN.	x	-	
VOLTAGE PROOF	300 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.	x	-	
MECHANICAL CHARACTERISTICS							
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE : 52.8 N MAX. WITHDRAWAL FORCE : 6.0 N MIN.	x	-	
MECHANICAL OPERATION	100 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
VIBRATION	FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
SHOCK	490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				x	-	
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.			① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN.	x	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-55→+15~+35→ +85→+15~+35°C TIME 30 → MAX 5 → 30 → MAX 5 min UNDER 5 CYCLES.			③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			① CONTACT RESISTANCE: 50 mΩ MAX. ② NO HEAVY CORROSION.	x	-	
HYDROGEN SULPHIDE	EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA 38)				x	-	
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s			NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	-	
	2) SOLDERING IRONS : 360 °C, FOR 5 s				x	-	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 240±3°C, FOR IMMERSION DURATION, 3 s.			A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	x	-	
△	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.				APPROVED	HS. OKAWA	08. 07. 23	
				CHECKED	HT. YAMAGUCHI	08. 07. 23	
				DESIGNED	SY. KAMIGA	08. 07. 22	
				DRAWN	HK. SUNADORI	08. 07. 17	
Unless otherwise specified, refer to MIL-STD-1344.				DRAWING NO.		ELC4-084982-21	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test							
HRS	SPECIFICATION SHEET			PART NO.	FX6-60S-0.8SV2(91)		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL576-0125-6-91	△	1/1