

Features

High Surge Capability Type 200 V VRRM Isolation Type Package Electrically Isolation base plate





Maximum Ratings

Operating Temperature : -40 °C to +150 °C Storage Temperature : -40 °C to +150 °C

Part Number	Part Number Maximum Recurrent Peak Reverse Voltage		Maximum DC Blocking Voltage
GSXD080A020S1-D3 200V		140V	200V







	ļ	01	4	
		DIMENS	SIONS	
DIM	INC	HES		

DIMENSIONS				
DIM	INCHES		ММ	
	MIN	MXA	MIN	MXA
Α	.500	.519	12.70	13.20
В	.307	.322	7.80	8.20
С	.029	.033	.75	.84
D	.077	.082	1.95	2.10
Е	1.487	1.502	37.80	38.20
F	1.250	1.258	31.75	32.00
G	.931	.956	23.65	24.30
Н	.996	1.007	25.30	25.60
1	.586	.594	14.90	15.10
J	.492	.516	12.50	13.10
K	.161	.169	4.10	4.30
٦	.161	.169	4.10	4.30
М	.181	.191	4.60	4.95

30.10

0


Electrical Characteristics @ 25 °C Unless Otherwise Specified.


Average Forward Current (Per pkg)	IF(AV)	160A	Tc=110 ℃
Peak Forward Surge Current (Per leg)	İFSM	900A	8.3ms,half sine
Maximum Instantaneous Forward Voltage (Per leg)	VF	0.80V 0.92V	IFM=80A;ТJ=125°С IFM=80A;ТJ=25°С
Maximum NOTE(1) Instantaneous Reverse Current At Rated DC Blocking Voltage (Per leg)	lR	3 mA 10 mA 30 mA	TJ=25°C TJ=100°C TJ=150°C
Isolation Voltage	Viso	2500V	A.C. 1 minute
Maximum Thermal Resistance Junction To Case (Per leg)	Rθjc	0.60°C/W	


NOTE:


(1) Pulse Test: Pulse Width 300 μ sec, Duty < 2%













Data Sheet GSXD080A020S1-D3

Revision History

Date	Revision	Notes
8/10/2014	1.0	Initial release
01/03/2020	1.1	Applied company name change

Notes

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented March, 2013. RoHS Declarations for this product can be obtained from the Product Documentation sections of www.SemiQ.com.

REACh Compliance

REACh substances of high concern (SVHC) information is available for this product. Since the European Chemicals Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact our office at SemiQ Headquarters in Lake Forest, California to insure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

SemiQ Inc., reserves the right to make changes to the product specifications and data in this document without notice. SemiQ products are sold pursuant to SemiQ's terms and conditions of sale in place at the time of order acknowledgement.

This product has not been designed or tested for use in, and is not intended for use in, applications implanted into the human body nor in applications in which failure of the product could lead to death, personal injury or property damage, including but not limited to equipment used in the operation of nuclear facilities, life-support machines, cardiac defibrillators or similar emergency medical equipment, aircraft navigation or communication or control systems, or air traffic control.

SemiQ makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SemiQ assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using SemiQ products.

To obtain additional technical information or to place an order for this product, please contact us. The information in this datasheet is provided by SemiQ. SemiQ reserves the right to make changes, corrections, modifications, and improvements of datasheet without notice.