# **Transformer, 1:1 Transmission Line 45 - 1200 MHz**



MABA-011014 Rev. V5

#### **Features**

- 1:1 Impedance Ratio
- Surface Mount Package
- Excellent Temperature Stability
- Can be used on 50 Ω & 75 Ω Systems
- Available on Tape & Reel
- RoHS\* Compliant


#### **Applications**

• CATV, Broadband and FTTx applications

#### Description

The MABA-011014 has a 1:1 impedance ratio and is available in a surface mount package. This device is well suited for CATV, Broadband, and FTTx applications.

### Schematic



#### **Ordering Information**

Part Number	Description
MABA-011014	Tape & Reel
MABA-011014-TB	Evaluation Board

#### **Pin Configuration**

Pin#	Function	Pin#	Function
1	Primary Dot	3	Secondary
2	Primary	4	Secondary Dot

#### Electrical Specifications: Freq. = 45 - 1200 MHz, $Z_0$ = 75 $\Omega$ , $T_A$ = 25°C, $P_{IN}$ = 0 dBm

Parameter	Conditions	Units	Min.	Тур.	Max.
Impedance Ratio	_	Ratio	_	1:1	_
Insertion Loss (Pin1 - Pin4)	45 - 100 MHz 100 - 600 MHz 600 - 1000 MHz 1000 - 1200 MHz	dB	_	0.9 0.9 1.0 1.0	1.1 1.2 1.3 1.4
Insertion Loss (Pin1 - Pin3)	45 - 100 MHz 100 - 600 MHz 600 - 1000 MHz 1000 - 1200 MHz	dB	_	-0.2 -0.1 0.2 0.35	0.1 0.2 0.5 0.7
Amplitude Balance	45 - 600 MHz 600 - 1000 MHz 1000 - 1200 MHz	dB	_	1.1 0.9 0.9	±1.4 ±1.5 ±1.5
Phase Balance	45 - 600 MHz 600 - 1000 MHz 1000 - 1200 MHz	0	_	2 4 4	±6 ±10 ±10
Input Return Loss (Pin1)	45 - 600 MHz 600 - 1000 MHz 1000 - 1200 MHz	dB	20 20 20	30 31 31	_


MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.


Visit <a href="https://www.macom.com">www.macom.com</a> for additional data sheets and product information.





MABA-011014 Rev. V5


#### Electrical Specifications: $Z_0 = 75 \Omega$ , $T_A = 25$ °C, $P_{IN} = 0 \text{ dBm}$













MABA-011014


Rev. V5

#### **Recommended Maximum Ratings**


Parameter	Units
Input Power	2 W
DC Current	200 mA
Operating Temperature	-40°C to +100°C

Temperature data available on request

#### **Application Circuit**




### **Recommended Footprint**



#### **Tape & Reel Information**

Parameter	Units	Value
Qty per reel	-	2000
Reel size	mm	330
Tape width	mm	12.00
Pitch	mm	8.00
Orientation	-	F51
Reference Application note ANI-019 for orientation		

#### **Carrier Tape Orientation**






MABA-011014

Rev. V5

#### **Outline Drawing**



- 1. Dimensions in mm.
- 2. Tolerance: ±0.2mm unless otherwise noted.
- 3. Model number and lot code printed on reel.
- 4. Plating finish: 96.5 % tin, 3% silver, and 0.5% copper

## Transformer, 1:1 Transmission Line 45 - 1200 MHz



**MABA-011014** 

Rev. V5

#### MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.