
# **Technical Data Sheet**

SMA FEMALE COAXIAL TERMINATION 22GHZ 1W





This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

# **Technical Data Sheet**



SMA FEMALE COAXIAL TERMINATION 22GHZ 1W

	ISSUE 20-07-15		NES NATION	PART NUMB	ER <b>R404215150</b>
			ELECTRICAL	CHARACTERISTICS	
	Frequency (GHz) √.S.W.R (≤)	DC - 2 1.05	2 - 18 1.1	18 - 22 1.15	
				DC - 22	GHz
0	perating Frequency	Range		00-22	OTIZ
	perating Frequency	Range		50	
In		Range			Ω
lm D	pedance			50	Ω Ω±5%
Im Di Pe	npedance C Resistance	1µs, 1%0)		50 50	Ω Ω±5%
Im Di Pe	npedance C Resistance eak power at 25°C (	1µs, 1%0)		50 50 50	$ \begin{array}{c} \Omega \\ \Omega \pm 5\% \\ W \end{array} $
Im Di Pe	npedance C Resistance eak power at 25°C (	1µs, 1%0)		50 50 50	$ \begin{array}{c} \Omega \\ \Omega \pm 5\% \\ W \\ W (Free Air Cooled) \end{array} $


## MECHANICAL CHARACTERISTICS

Connectors	SMA	Female	MIL C 39012
Weight	<b>3,2500</b> g		

## ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

#### Power derating Versus temperature



#### SPECIFICATION

#### OTHER CHARACTERISTICS

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.