






BNC ATTENUATOR 0 DB 3 GHZ 1W

PAGE 1/2 ISSUE 18-12-14B SERIES ATTENUATOR PART NUMBER R412400124







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	BRASS BRASS	NICKEL 2 GOLD 1 OVER NICKEL 2
Female center contact Outer contact	BERYLLIUM COPPER -	GOLD 1 OVER NICKEL 2
Insulator Gasket	PTFE SILICONE RUBBER	
Substrate	ALUMINA	
Resistor Others parts	THICK FILM -	-



Technical Data Sheet

BNC ATTENUATOR 0 DB 3 GHZ 1W

PAGE 2/2	ISSUE 18-12-14B	SERIES ATTENUATOR	PART NUMBER R412400124
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 2	2 - 3
V.S.W.R (≤)	1.20	1.30
Deviation(±dB)	0.30	0.50

DC - 3	GHz
50	Ω
0	dB
100	W
1	W (Free Air Cooled)
	W (Conduction Cooled)
-	50 0


MECHANICAL CHARACTERISTICS

Connectors	BNC	Male Female	MIL-C 39012
Weight	12,8300 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-40 / +85 °C
Storage temperature range	-40 / +85 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS