

# QUICKSWITCH<sup>®</sup> PRODUCTS HIGH-SPEED CMOS 10-BIT BUS EXCHANGE SWITCH

### **FEATURES:**

- Enhanced N channel FET with no inherent diode to Vcc
- 5 $\Omega$  bidirectional switches connect inputs to outputs
- · Zero propagation delay, zero added ground bounce
- · Undershoot clamp diodes on all switch and control inputs
- Bus exchange allows nibble swap
- Available in QSOP package

## **APPLICATIONS:**


- · Hot-swapping, hot-docking
- Voltage translation (5V to 3.3V)
- Resource sharing
- · Crossbar switching

## **DESCRIPTION:**

The QS3383 provides ten high-speed CMOS TTL-compatible bus switches. The low ON resistance of the QS3383 allows inputs to be connected to outputs without adding propagation delay and without generating additional ground bounce noise. The Bus Enable (BE) signal turns the switches on. The Bus Exchange (BX) signal provides nibble swap of the AB and CD pairs of signals. This exchange configuration allows byte swapping of buses in systems. It can also be used as a 5-wide 2-to-1 multiplexer and to create low delay barrel shifters, etc.

The QS3383 is characterized for operation at -40°C to +85°C.


## **FUNCTIONAL BLOCK DIAGRAM**



#### INDUSTRIAL TEMPERATURE RANGE

#### **OCTOBER 2011**

#### **PIN CONFIGURATION**



#### **INDUSTRIAL TEMPERATURE RANGE**

## ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

Symbol	Description	Max	Unit
VTERM <sup>(2)</sup>	Supply Voltage to Ground	–0.5 to +7	V
VTERM <sup>(3)</sup>	DC Switch Voltage Vs	–0.5 to +7	V
VTERM <sup>(3)</sup>	DC Input Voltage VIN	–0.5 to +7	V
VAC	AC Input Voltage (pulse width ≤20ns)	-3	V
Ιουτ	DC Output Current	120	mA
Рмах	Maximum Power Dissipation (T <sub>A</sub> = 85°C)	0.5	W
Tstg	Storage Temperature	–65 to +150	°C

NOTES:

 Stresses greater than those listed under ABSOLUTE MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

2. Vcc terminals.

3. All terminals except Vcc .

#### **CAPACITANCE** (TA = +25°C, f = 1MHz, VIN = 0V, VOUT = 0V)

Pins	Тур.	Max. <sup>(1)</sup>	Unit
Control Inputs	3	5	рF
Quickswitch Channels (Switch OFF)	5	7	pF

NOTE:

1. This parameter is guaranteed but not production tested.

### **PIN DESCRIPTION**

Pin Names	I/O	Description
A0 - A4, B0 - B4	I/O	A and B Buses
C0 - C4, D0 - D4	I/O	C and D Buses
BE		Bus Switch Enable
BX	I	Bus Exchange

### **FUNCTION TABLE(1)**

BE	ΒХ	A0 - A4	B0 - B4	Function
Н	Х	Hi-Z	Hi-Z	Disconnect
L	L	C0 - C4	D0 - D4	Connect
L	Н	D0 - D4	C0 - C4	Exchange

NOTE:

1. H = HIGH Voltage Level

L = LOW Voltage Level

X = Don't Care

Z = High-Impedance

# DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE

Following Conditions Apply Unless Otherwise Specified: Industrial: TA =  $-40^{\circ}$ C to  $+85^{\circ}$ C, Vcc = 5V ± 5%

Symbol	Parameter Test Conditions				Max.	Unit
Vih	Input HIGH Voltage	Guaranteed Logic HIGH for Control Pins	2	—	_	V
Vil	Input LOW Voltage	Guaranteed Logic LOW for Control Pins	—	-	0.8	V
lin	InputLeakageCurrent(ControlInputs)	$0V \le VIN \le VCC$	—	0.01	±1	μA
loz	Off-State Current (Hi-Z)	$0V \le VOUT \le VCC$ , Switches OFF	—	0.01	±1	μA
Ron	Switch ON Resistance <sup>(2)</sup>	Vcc = Min., VIN = 0V, ION = 30mA	—	6	8	Ω
		Vcc = Min., VIN = 2.4V, ION = 15mA	—	12	17	
Vp	Pass Voltage <sup>(3)</sup>	VIN = Vcc = 5V, IOUT = -5µA	3.7	4	4.2	V


NOTES:

1. Typical values are at Vcc = 5V and TA =  $25^{\circ}$ C.

2. RON is guaranteed but not production tested.

3. Pass voltage is guaranteed but not production tested.

# TYPICAL ON RESISTANCE vs VIN AT Vcc = 5V



(Volts)

## **POWER SUPPLY CHARACTERISTICS**

Symbol	Parameter Test Conditions <sup>(1)</sup>		Max.	Unit
ICCQ	Quiescent Power Supply Current	Vcc = Max., Vin = GND or Vcc, f = 0	1.5	mA
$\Delta$ lcc	Power Supply Current per Input HIGH <sup>(2)</sup>	Vcc = Max., Vin = 3.4V, f = 0	2.5	mA
ICCD	Dynamic Power Supply Current per MHz $^{\scriptscriptstyle (3)}$	Vcc = Max., A and B Pins Open, Control Inputs Toggling @ 50% Duty Cycle	0.25	mA/MHz

#### NOTES:

1. For conditions shown as Min. or Max., use the appropriate values specified under DC Electrical Characteristics.

2. Per TTL-driven input (VIN = 3.4V, control inputs only). A, B,C, and D pins do not contribute to △lcc.

3. This current applies to the control inputs only and represents the current required to switch internal capacitance at the specified frequency. The A and B inputs generate no significant AC or DC currents as they transition. This parameter is guaranteed but not production tested.

## SWITCHING CHARACTERISTICS OVER OPERATING RANGE

TA = -40°C to +85°C, Vcc =  $5V \pm 5\%$ 

 $C_{LOAD} = 50 pF$ ,  $R_{LOAD} = 500 \Omega$  unless otherwise noted.

Symbol	Parameter	Min. <sup>(1)</sup>	Тур.	Max.	Unit
<b>t</b> PLH	Data Propagation Delay <sup>(2)</sup>			0.25 <sup>(3)</sup>	ns
<b>t</b> PHL	AxBx to CxDx, CxDx to AxBx				
tPZL	Switch Turn-On Delay	1.5	—	6.5	ns
<b>t</b> PZH	BE to Ax, Bx, Cx, Dx				
tPLZ	Switch Turn-Off Delay <sup>(2)</sup>	1.5	—	5.5	ns
<b>t</b> PHZ	BE to Ax, Bx, Cx, Dx				
tвх	Switch Multiplex Delay BX to Ax, Bx, Cx, Dx	1.5	—	6.5	ns

NOTES:

1. Minimums are guaranteed but not production tested.

2. This parameter is guaranteed but not production tested.

3. The bus switch contributes no propagation delay other than the RC delay of the ON resistance of the switch and the load capacitance. The time constant for the switch alone is of the order of 0.25ns at CL = 50pF. Since this time constant is much smaller than the rise and fall times of typical driving signals, it adds very little propagation delay to the system. Propagation delay of the bus switch, when used in a system, is determined by the driving circuit on the driving side of the switch and its interaction with the load on the driven side.

	S3383 -SPEEDCMOS1	0-BITBUSEX	(CHANGE SV	VITCH		INDUSTRIALTEMPERATURERANGE
OR	DERINGIN	IFORMA	TION			
QS	_XXXXX Device Type	XX Package	<u>X</u> Process	<u>    x                                </u>		
					Blank 8	Tube or Tray Tape and Reel
					Blank	Industrial (-40°C to +85°C)
					-QG	Quarter Size Outline Package - Green
					3383	High Speed CMOS 10-Bit Bus Exchange Switch

#### IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use o any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.0 Mar 2020)

#### **Corporate Headquarters**

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

#### **Trademarks**

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners. **Contact Information** 

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: <u>www.renesas.com/contact/</u>