






COAXIAL ATTENUATOR SMA 2.9 DC-40GHZ 2 W - 3DB



26.5 maxi





Scale 1:1

All dimensions are in mm. Tolerances according ISO 2768 m-H

COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact Female center contact Outer contact	STAINLESS STEEL BERYLLIUM COPPER BERYLLIUM COPPER STAINLESS STEEL	PASSIVATED GOLD 1.3 OVER NICKEL2 GOLD 1.3 OVER NICKEL2 PASSIVATED
Insulator	-	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THIN FILM	
Others parts		





COAXIAL ATTENUATOR SMA 2.9 DC-40GHZ 2 W - 3DB

PAGE 2/2	ISSUE 23-10-19C	SERIES ATTENUATOR	PART NUMBER R413303000
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 40
V.S.W.R (≤)	1.60 (1.4 typ.)
Deviation(±dB)	0.8

Operating Frequency Range	DC - 40	GHz
Impedance	50	Ω
Nominal Attenuation	3	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA 2.9	Male Female	MIL C39012
Weight	6,5900	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS