



Click [here](#) for the 3D model.

| General Information |   |
|---------------------|---|
| Series              | PMR210  |
| Dielectric          | Metallized Paper  |
| Style               | Radial  |
| Features            | RC Unit approved  |
| RoHS                | Yes   |
| Lead                | Wire Leads  |
| Qualifications      | ENEC, UL, cUL   |
| AEC-Q200            | No  |
| Construction        | Molded  |
| Component Weight    | 2.7 g   |
| Miscellaneous       | Resistor= 100 Ohms.   |
| Notes               | Not For New Design, Please Use The New P410 Series @ 300 VAC. |

| Specifications        |           |
|-----------------------|-----------|
| Capacitance           | 0.022 uF  |
| Capacitance Tolerance | 20%       |
| Voltage AC            | 250 VAC   |
| Voltage DC            | 1000 VDC  |
| Temperature Range     | -40/+85°C |
| Rated Temperature     | 85°C      |
| Insulation Resistance | 3 GOhms   |
| Safety Class          | X1        |

| Dimensions |                 |
|------------|-----------------|
| L          | 18.5mm MAX      |
| H          | 13mm MAX        |
| T          | 7.3mm MAX       |
| S          | 15.2mm +/-0.4mm |
| LL         | 30mm +5mm       |
| F          | 0.8mm +/-0.05mm |

| Packaging Specifications |           |
|--------------------------|-----------|
| Packaging                | Bulk, Bag |
| Packaging Quantity       | 400       |