



6 CIRCUITS SHOWN

- NOTES:
1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. PRODUCT SPECIFICATION: NOT REQUIRED
 4. "XX" REFERS TO THE NUMBER OF CIRCUITS
 5. ROHS COMPLIANT

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
4	XX	SCREW, #8-32X.290, BHD PH-SL (OPT-A)	BRASS	NICKEL PLATE
3	XX	SCRW&WSHR,#8-32X.25 PANHD,PH-SL (OPT-A-50)	STEEL	ZN, CLEAR CHROMATE
2	XX	TERMINAL WW, #8-32	BRASS	TIN PLATE
1	1	INSULATOR	POLYESTER (PBT)	BLACK

RELEASED
 EC NO: WINA2010-0720
 DRAWN: ENC INAS 2010/06/07
 CHKD: CLYORK 2010/06/07
 APPR: JMACNEIL 2010/06/15

QUALITY SYMBOLS
 ▼=0
 ▽=0

	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .005
2 PLACES	± 0.13	± .010
1 PLACE	± 0.3	± ---
ANGULAR ± 2 °		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY: JENCINAS
 DATE: 2010/06/07

CHECKED BY: CLYORK
 DATE: 2010/06/07

APPROVED BY: JMACNEIL
 DATE: 2010/06/15

MATERIAL NO.
SEE SHEET 2

SCALE: 2:1

DESIGN UNITS: INCH

THIRD ANGLE PROJECTION

TITLE: 11.11MM [.438"] SR BTS PC, CS, ASSY NO MTG ENDS #8-32 SCREWS

MOLEX INCORPORATED

DOCUMENT NO.: SD-38737-001

SHEET NO.: 1 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

NO. OF CIRCUITS "XX"	DIM. "A"		DIM. "B"		ASSEMBLY MATERIAL NO. OPT -A-C-50	ASSEMBLY MATERIAL NO. STD (OPT -A-C)
	mm	INCH	mm	INCH		
2	24.6	0.97	11.11	0.438	387373902	387373702
3	35.8	1.41	22.23	0.875	387373903	387373703
4	46.9	1.85	33.34	1.313	387373904	387373704
5	58.0	2.28	44.45	1.750	387373905	387373705
6	69.1	2.72	55.56	2.188	387373906	387373706
7	80.2	3.16	66.68	2.625	387373907	387373707
8	91.3	3.60	77.79	3.063	387373908	387373708
9	102.4	4.03	88.90	3.500	387373909	387373709
10	113.5	4.47	100.01	3.938	387373910	387373710
11	124.7	4.91	111.13	4.375	387373911	387373711
12	135.8	5.35	122.24	4.813	387373912	387373712
13	146.9	5.78	133.35	5.250	387373913	387373713
14	158.0	6.22	144.46	5.688	387373914	387373714
15	169.1	6.66	155.58	6.125	387373915	387373715
16	180.2	7.10	166.69	6.563	387373916	387373716
17	191.3	7.53	177.80	7.000	387373917	387373717
18	202.4	7.97	188.91	7.438	387373918	387373718
19	213.6	8.41	200.03	7.875	387373919	387373719
20	224.7	8.85	211.14	8.313	387373920	387373720

RELEASED EC NO: WNA2010-0720 DRAWN: JENCINAS 2010/06/08 CHKD: CLYORK 2010/06/07 APPR: JMACNEIL 2010/06/15 A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .010 1 PLACE ± 0.3 ± --- ANGULAR ± 2 °	DIMENSION STYLE MM/IN DRAWN BY DATE JENCINAS 2010/06/07 CHECKED BY DATE CLYORK 2010/06/07 APPROVED BY DATE JMACNEIL 2010/06/15	SCALE 2:1 DESIGN UNITS INCH THIRD ANGLE PROJECTION	TITLE 11.11MM [.438"] SR BTS PC, CS, ASSY NO MTG ENDS #8-32 SCREWS
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	MATERIAL NO. SEE CHART	MOLEX INCORPORATED DOCUMENT NO. SD-38737-001	SHEET NO. 2 OF 2	
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
		SIZE B				